

MEN POWER SUPPLY 1/2-PHASE, SMOOTHED

IN: 230/400+/-15VAC OUT: 24V/1ADC


Current: 1 A


Output rating: 24 W

This power supply units meet the (EN 61000-3-2) standard for harmonic current.

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

Input voltage	230/400 ±15 V AC
Input fuse (external)	0.4 A (T) (230 V AC); 25 A (T) (400 V AC)
Frequency	50...60 Hz
Input current	0.25 A (230 V AC); 1.45 A (400 V AC)

General data

Standards	(EN 61558-2-6), (EN 62041 category I), (EN 55011 B), (EN 61000-3-2)
Mounting method	Key-hole mounting
Dimensions H × W × D	64×78×120 mm
Fixing centers a × b × c	47.5×56×4.8 mm
Temperature range	-20...+60 °C, no condensation

Output

Output voltage	24 V DC (SELV)
Output current (Ta 60/40 °C)	max. 1 A (230 V AC); 1.5 A (400 V AC)
Ripple	max. 5 %rms
Output fuse	3 A (automotive fuse FKS)
Output filter	LED, VDR and smoothing capacitor

Commercial data

country of origin	CZ
customs tariff number	85044090
minimum order quantity	1