

Product type designation	RUGGEDCOM RX1500PN LM W12 RUGGEDCOM RX1500PN LM W12 LINE MODULE 2 PORT CELL MODEM GSM,EDGE,HSPA
Suitability for operation	RX1500, RX1501, RX1510, RX1511, RX1512
Interfaces	
Number of electrical/optical connections / for network components or terminal equipment / maximum	2
Number of electrical connections <ul style="list-style-type: none"> • for network components or terminal equipment / maximum 	2
Permitted ambient conditions	
Ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport • Note 	-40 ... +85 °C -40 ... +85 °C -40 ... +85 °C A maximum ambient operating temperature of +85 °C is permissible for a duration of 16 hours
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP40
Design, dimensions and weight	
Design	Media module
Width	20 mm
Height	115 mm
Depth	180 mm
Net weight	0.35 kg
Coating	no
Mounting type <ul style="list-style-type: none"> • Installation in media module slot 	screwed Yes
Standards, specifications, approvals	
Standard <ul style="list-style-type: none"> • for EMC • for safety / from CSA and UL • for hazardous zone / from CSA and UL • for emitted interference • for interference immunity 	FCC Part 15 (Class A), EN55022 (CISPR22 Class A) UL 60950-1, CSA C22.2 No. 60950-7 Hazardous Locations: Class 1 Division 2 EN 61000-6-4 (Class A) EN 61000-6-2
Certificate of suitability	EN 61000-6-2, EN 61000-6-10

- CE marking
- C-Tick
- KC approval
- E1 approval
- Railway application in accordance with EN 50155
- Railway application in accordance with EN 50124-1
- IEC 61850-3

Yes
No
No
No
Yes
Yes
Yes

Further Information / Internet Links

Internet-Link

- to website: Industry Mall/RUGGEDCOM selector
- to website: Siemens RUGGEDCOM
- to website: Selector for cables and connectors
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://ruggedcom-selector.automation.siemens.com>

<http://siemens.com/ruggedcom>
<http://www.siemens.com/snst>
<http://www.siemens.com/simatic-net>
<https://mall.industry.siemens.com>
<http://www.siemens.com/automation/net/catalog>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

last modified:

16.03.2015