



Note:
RoHS 2.0 AND REACH Compliant
Test:
Grade Designation: Each to Reference

Type	Multi-Mode
Insertion Loss	≤ 0.2dB
Return Loss	≤ 60dB
Test Wavelength	1310nm

MATERIAL LIST:

NO.	SPECIFICATION STANDARD	QT' Y	REMARK
⑫	LC Dust Cap White	2pcs	
⑪	LC UPC SM Ceramic Ferrule	2pcs	
⑩	LC Blue Duplex Clip	1pcs	
⑨	LC Duplex Connector Blue	2pcs	
⑧	LC 3.0 Boot White	2pcs	
⑦	LSH 3.0 Boot Green	2pcs	
⑥	Fiber Optical Cable Yellow OS2 G657. A2 9/125um Duplex Ø3.0*6.0mm LSZH	L	
⑤	Black Heat Shrink Tube	2pcs	
④	Ring 1、2	4pcs	
③	LSH 3.0 Boot Green	2pcs	
②	LSH Connector Green	2pcs	
①	LSH Metal Dust Cap	2pcs	

ITEM NO.	DESC.
21.15.9510	ROLINE FO Jumper Cable LSH APC-LC UPC, Duplex, 9/125um, OS2, 0.5m
21.15.9511	ROLINE FO Jumper Cable LSH APC-LC UPC, Duplex, 9/125um, OS2, 1m
21.15.9512	ROLINE FO Jumper Cable LSH APC-LC UPC, Duplex, 9/125um, OS2, 2m
21.15.9513	ROLINE FO Jumper Cable LSH APC-LC UPC, Duplex, 9/125um, OS2, 3m
21.15.9515	ROLINE FO Jumper Cable LSH APC-LC UPC, Duplex, 9/125um, OS2, 5m
21.15.9516	ROLINE FO Jumper Cable LSH APC-LC UPC, Duplex, 9/125um, OS2, 7.5m
21.15.9517	ROLINE FO Jumper Cable LSH APC-LC UPC, Duplex, 9/125um, OS2, 10m

SECOMP

BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.
		NEW	2018-05-07	A