

## Accessory

PICO-LPG-660-BOX  
Order Number: 70144888

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-20		40	°C
Storage Temperature	-50		50	°C

## Optical Parameters

LB Rating	180-315 D LB6 + R LB4, >315-400 DR LB4, >615-660 DIR LB3, >660-665 DIR LB4, >665-715 D LB4 + IR LB5, 694 IR LB7
Lens Color	Blaugrün

## Mechanical Parameters

Material	Plastic
Weight	150 g

(\*) Over the complete operating temperature range

## Features



- Laser glasses for ultraviolet and red wavelengths
- Incl. wall holder
- Stickers with mandatory and hazard sign

## Picture



## Safety Label



## Valid Revision

| 28-OCT-2020