

# XTL™ Labels


## All-Purpose Vinyl

- From textured surfaces to cables, vinyl labels are ideal for almost any labeling application
- Vinyl offers moisture, chemical and UV resistance, making it ideal for labeling both indoors and outdoors
- Available in a wide range of colors that fit with OSHA, ANSI, and ISO color standards to enhance workplace communication and safety
- RoHS compliant
- Easy-to-peel split back design makes applying labels quick and easy
- Durable thermal transfer printing technology – label text won't smear or fade
- Labels comply with ANSI/TIA 606-B standards

| Quick Specs           |  |
|-----------------------|--|
| Label Widths          | 12, 19, 24, 38, 54 mm                                  |
| Tape Platform         | XTL  |
| Printer Compatibility | XTL 300: Up to 24 mm wide<br>XTL 500: Up to 54 mm wide |
| Label Length          | 7 m  |
| Printing System       | Thermal Transfer                                       |
| Temperature Rating    | -40°C to 60°C  |
| UL Recognized         | Yes, component to UL969                                |
| Country of Origin     | Belgium  |
| Material              | Vinyl  |

### Dimensions for 12 mm All-Purpose Vinyl

|        | Length (mm) | Width (mm) | Height (mm) | Weight (kg) | QTY |
|--------|-------------|------------|-------------|-------------|-----|
| Unit   | 72          | 35         | 120         | 0.063       | 1   |
| Shelf  | 215         | 76         | 126         | 0.42        | 6   |
| Case   | 400         | 230        | 145         | 2.4         | 30  |
| Pallet | 1200        | 800        | 1165        | 176.2       | 63  |



| Item Number | Width | Color | EAN Unit     | EAN Shelf      | EAN Case       | EAN Pallet |
|-------------|-------|-------|--------------|----------------|----------------|------------|
| 1868741     | 12 mm | A     | 071701001207 | 30071701001208 | 50071701001202 | –          |
| 1868746     | 12 mm | A     | 071701001252 | 30071701001253 | 50071701001257 | –          |
| 1868751     | 12 mm | A     | 071701001306 | 30071701001307 | 50071701001301 | –          |
| 1868756     | 12 mm | A     | 071701001351 | 30071701001352 | 50071701001356 | –          |
| 1868761     | 12 mm | A     | 071701001405 | 30071701001406 | 50071701001400 | –          |
| 1868766     | 12 mm | A     | 071701001405 | 30071701001406 | 50071701001400 | –          |
| 1868771     | 12 mm | A     | 071701001504 | 30071701001505 | 50071701001509 | –          |
| 1868776     | 12 mm | A     | 071701001559 | 30071701001550 | 50071701001554 | –          |
| 1868781     | 12 mm | A     | 071701001603 | 30071701001604 | 50071701001608 | –          |
| 1868786     | 12 mm | A     | 071701001658 | 30071701001659 | 50071701001653 | –          |
| 18687891    | 12 mm | A     | 071701001689 | 30071701001680 | 50071701001684 | –          |
| 1868796     | 12 mm | A     | 071701001757 | 30071701001758 | 50071701001752 | –          |
| 1868801     | 12 mm | A     | 071701001801 | 30071701001802 | 50071701001806 | –          |

**DISTRIBUTED BY:**  
Newell Europe Sàrl  
Chemin de Blandonnet 10  
1214 Vernier – Switzerland  
WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

# XTL™ Labels



## Dimensions for 19 mm All-Purpose Vinyl

|               | Length (mm) | Width (mm) | Height (mm) | Weight (kg) | QTY |
|---------------|-------------|------------|-------------|-------------|-----|
| <b>Unit</b>   | 72          | 35         | 120         | 0.08        | 1   |
| <b>Shelf</b>  | 215         | 76         | 126         | 0.54        | 6   |
| <b>Case</b>   | 400         | 230        | 145         | 2.98        | 30  |
| <b>Pallet</b> | 1200        | 800        | 1165        | 213.05      | 63  |

| Item Number | Width | Color | EAN Unit     | EAN Shelf      | EAN Case       | EAN Pallet |
|-------------|-------|-------|--------------|----------------|----------------|------------|
| 1868742     | 19 mm | A     | 071701001214 | 30071701001215 | 50071701001219 | –          |
| 1868747     | 19 mm | A     | 071701001269 | 30071701001260 | 50071701001264 | –          |
| 1868752     | 19 mm | A     | 071701001313 | 30071701001314 | 50071701001318 | –          |
| 1868757     | 19 mm | A     | 071701001368 | 30071701001369 | 50071701001363 | –          |
| 1868762     | 19 mm | A     | 071701001412 | 30071701001413 | 50071701001417 | –          |
| 1868767     | 19 mm | A     | 071701001412 | 30071701001413 | 50071701001417 | –          |
| 1868772     | 19 mm | A     | 071701001511 | 30071701001512 | 50071701001516 | –          |
| 1868777     | 19 mm | A     | 071701001566 | 30071701001567 | 50071701001561 | –          |
| 1868782     | 19 mm | A     | 071701001610 | 30071701001611 | 50071701001615 | –          |
| 1868787     | 19 mm | A     | 071701001665 | 30071701001666 | 50071701001660 | –          |
| 1868792     | 19 mm | A     | 071701001719 | 30071701001710 | 50071701001714 | –          |
| 1868797     | 19 mm | A     | 071701001719 | 30071701001710 | 50071701001714 | –          |
| 1868802     | 19 mm | A     | 071701001818 | 30071701001819 | 50071701001813 | –          |

## Dimensions for 24 mm All-Purpose Vinyl

|               | Length (mm) | Width (mm) | Height (mm) | Weight (kg) | QTY |
|---------------|-------------|------------|-------------|-------------|-----|
| <b>Unit</b>   | 120         | 35         | 120         | 0.09        | 1   |
| <b>Shelf</b>  | 215         | 76         | 126         | 0.61        | 6   |
| <b>Case</b>   | 400         | 230        | 145         | 3.34        | 30  |
| <b>Pallet</b> | 1200        | 800        | 1165        | 235.73      | 63  |

| Item Number | Width | Color | EAN Unit     | EAN Shelf      | EAN Case       | EAN Pallet |
|-------------|-------|-------|--------------|----------------|----------------|------------|
| 1868743     | 24 mm | A     | 071701001221 | 30071701001222 | 50071701001226 | –          |
| 1868748     | 24 mm | A     | 071701001276 | 30071701001277 | 50071701001271 | –          |
| 1868753     | 24 mm | A     | 071701001320 | 30071701001321 | 50071701001325 | –          |
| 1868758     | 24 mm | A     | 071701001375 | 30071701001376 | 50071701001370 | –          |
| 1868763     | 24 mm | A     | 071701001429 | 30071701001420 | 50071701001424 | –          |
| 1868768     | 24 mm | A     | 071701001474 | 30071701001475 | 50071701001479 | –          |
| 1868773     | 24 mm | A     | 071701001528 | 30071701001529 | 50071701001523 | –          |
| 1868778     | 24 mm | A     | 071701001573 | 30071701001574 | 50071701001578 | –          |
| 1868783     | 24 mm | A     | 071701001627 | 30071701001628 | 50071701001622 | –          |
| 1868788     | 24 mm | A     | 071701001672 | 30071701001673 | 50071701001677 | –          |
| 1868793     | 24 mm | A     | 071701001726 | 30071701001727 | 50071701001721 | –          |
| 1868798     | 24 mm | A     | 071701001771 | 30071701001772 | 50071701001776 | –          |
| 1868803     | 24 mm | A     | 071701001276 | 30071701001277 | 50071701001271 | –          |

**DISTRIBUTED BY:**  
 Newell Europe Sàrl  
 Chemin de Blandonnet 10  
 1214 Vernier – Switzerland  
 WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *Newell Rubbermaid* Brand

©2015 Newell Europe LLC

# XTL™ Labels



## Dimensions for 38 mm All-Purpose Vinyl

|               | Length (mm) | Width (mm) | Height (mm) | Weight (kg) | QTY |
|---------------|-------------|------------|-------------|-------------|-----|
| <b>Unit</b>   | 72          | 65         | 120         | 0.14        | 1   |
| <b>Shelf</b>  | 215         | 76         | 126         | 0.47        | 6   |
| <b>Case</b>   | 400         | 230        | 145         | 2.67        | 15  |
| <b>Pallet</b> | 1200        | 800        | 1165        | 193.21      | 63  |

| Item Number | Width | Color | EAN Unit     | EAN Shelf      | EAN Case       | EAN Pallet |
|-------------|-------|-------|--------------|----------------|----------------|------------|
| 1868744     | 38 mm | A     | 071701001238 | 30071701001239 | 50071701001233 | –          |
| 1868749     | 38 mm | A     | 071701001283 | 30071701001284 | 50071701001288 | –          |
| 1868754     | 38 mm | A     | 071701001337 | 30071701001338 | 50071701001332 | –          |
| 1868759     | 38 mm | A     | 071701001382 | 30071701001383 | 50071701001387 | –          |
| 1868764     | 38 mm | A     | 071701001436 | 30071701001437 | 50071701001431 | –          |
| 1868769     | 38 mm | A     | 071701001481 | 30071701001482 | 50071701001486 | –          |
| 1868774     | 38 mm | A     | 071701001535 | 30071701001536 | 50071701001530 | –          |
| 1868779     | 38 mm | A     | 071701001580 | 30071701001581 | 50071701001585 | –          |
| 1868784     | 38 mm | A     | 071701001634 | 30071701001635 | 50071701001639 | –          |
| 1868789     | 38 mm | A     | 071701001689 | 30071701001680 | 50071701001684 | –          |
| 1868794     | 38 mm | A     | 071701001733 | 30071701001734 | 50071701001738 | –          |
| 1868799     | 38 mm | A     | 071701001788 | 30071701001789 | 50071701001783 | –          |
| 1868804     | 38 mm | A     | 071701001832 | 30071701001833 | 50071701001837 | –          |

## Dimensions for 54 mm All-Purpose Vinyl

|               | Length (mm) | Width (mm) | Height (mm) | Weight (kg) | QTY |
|---------------|-------------|------------|-------------|-------------|-----|
| <b>Unit</b>   | 72          | 65         | 120         | 0.18        | 1   |
| <b>Shelf</b>  | 215         | 76         | 126         | 0.58        | 3   |
| <b>Case</b>   | 400         | 230        | 145         | 3.19        | 6   |
| <b>Pallet</b> | 1200        | 800        | 1165        | 226.28      | 63  |

| Item Number | Width | Color | EAN Unit     | EAN Shelf      | EAN Case       | EAN Pallet |
|-------------|-------|-------|--------------|----------------|----------------|------------|
| 1868745     | 54 mm | A     | 071701001245 | 30071701001246 | 50071701001240 | –          |
| 1868750     | 54 mm | A     | 071701001290 | 30071701001291 | 50071701001295 | –          |
| 1868755     | 54 mm | A     | 071701001344 | 30071701001345 | 50071701001349 | –          |
| 1868760     | 54 mm | A     | 071701001399 | 30071701001390 | 50071701001394 | –          |
| 1868765     | 54 mm | A     | 071701001443 | 30071701001444 | 50071701001448 | –          |
| 1868770     | 54 mm | A     | 071701001498 | 30071701001499 | 50071701001493 | –          |
| 1868775     | 54 mm | A     | 071701001542 | 30071701001543 | 50071701001547 | –          |
| 1868780     | 54 mm | A     | 071701001597 | 30071701001598 | 50071701001592 | –          |
| 1868785     | 54 mm | A     | 071701001641 | 30071701001642 | 50071701001646 | –          |
| 1868790     | 54 mm | A     | 071701001696 | 30071701001697 | 50071701001691 | –          |
| 1868795     | 54 mm | A     | 071701001740 | 30071701001741 | 50071701001745 | –          |
| 1868800     | 54 mm | A     | 071701001795 | 30071701001796 | 50071701001790 | –          |
| 1868805     | 54 mm | A     | 071701001849 | 30071701001840 | 50071701001844 | –          |

**DISTRIBUTED BY:**  
 Newell Europe Sàrl  
 Chemin de Blandonnet 10  
 1214 Vernier – Switzerland  
 WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *Newell Rubbermaid* Brand

©2015 Newell Europe LLC