


B4 Series | Double-pole momentary switch 16A quick connection 6.3 black body

PRODUCT CODE: B417C1100000




sample image

Wiring diagrams



Terminal type



Body colour



Actuator colour



Marking



Rating



16 (6) A / 250 VAC
10 (4) A / 250 VAC - 5E4
T125 / 55 °C

20 A / 125 VAC
16 A / 250 VAC
1 / 3 HP - 125 VAC
3 / 4 HP - 250 VAC
T105 °C


Approvals



Dimensions (mm)



Cut out (mm)



Z	Y	X
0.75-1.25	22.0±0.2	30.0±0.1
1.25-2.0	22.0±0.2	30.2±0.1
2.0-3.0	22.0±0.2	30.6±0.2
3.0-4.0	22.0±0.2	30.8±0.2