

Sylmaster T8 White Louvre - Electronic Ballast

Sylmaster T8 26mmØ 2x36W A2 ballast & 5 way terminal block, with LS optic louvre
0055094



Product features

- Sylmaster T8 White Louvre - Electronic Ballast



PRODUCT OVERVIEW

Product name	Sylmaster T8 26mmØ 2x36W A2 ballast & 5 way terminal block, with LS optic louvre
Technology	Fluorescent
Cap/Base	G13
Housing	Steel
Mount	Ceiling surface mounting
Environment	Interior
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
Warranty	2 years
Fixture luminous flux (lm)	3904
Luminaire efficacy (lm/W)	54
LOR (%)	61
Light colour	N/A
Light source included	Fixture without Lightsource
Total power consumption (W)	72
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Dimmable	No
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5410288550947

DATA TABLE

General data

Product name	Sylmaster T8 26mmØ 2x36W A2 ballast & 5 way terminal block, with LS optic louvre
Technology	Fluorescent
Cap/Base	G13
Housing	Steel

Sylmaster T8 White Louvre - Electronic Ballast

Sylmaster T8 26mmØ 2x36W A2 ballast & 5 way terminal block, with LS optic louvre
0055094

Mount	Ceiling surface mounting
Environment	Interior
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
Warranty	2 years

Optical data

Fixture luminous flux (lm)	3904
Luminaire efficacy (lm/W)	54
LOR (%)	61
Light colour	N/A
Adjustable chromaticity	N

Electrical data

Light source included	Fixture without Lightsource
Total power consumption (W)	72
Mains voltage (V)	220-240V
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Transformer required	Yes
Dimmable	No
Glow Wire Test (°C)	960
Nominal Frequency (Hz)	50/60Hz

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	1250
Nominal Product Width (mm)	202
Nominal Product Height (mm)	85
Weight (kg)	4.65

Packaging

Single packaging type	Carton
Product EAN number	5410288550947
Packaging single length / height (cm)	126.0
Packaging single width (cm)	9.0
Packaging single depth (cm)	21.0
DUN14 (outer)	05410288550947
Units per outer package	1
Packaging outer length / height (cm)	126.0
Packaging outer width (cm)	9.0
Packaging outer depth (cm)	21.0

PHOTOMETRY