

SVHB clamp holder, positive

For copy and longitudinal face turning using VB indexable inserts

ATORN[®]

Application

For copy, longitudinal and face turning with VB indexable insert, 35°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 107.5°, tip angle 35°, clearance angle 5°
- SVHBR 1212 F11

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



Art. no.	17836 306
ISO name	SVHB R/L 2020 K16
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	15.9 mm
Programming size	25 mm
Suitable for indexable inserts	VB.. 1604..
Tool design	Right

EAN-Code

4050293563412