

collet chuck DIN 6343 185 E, round

ORION[®]

Execution:

- hardened and ground
- clamping bridge max. 0.1 mm of the nominal diameter
- concentricity
- \varnothing 1-10 mm \leq 20 μ m
- \varnothing 11-30 mm \leq 30 μ m
- \varnothing 31-60 mm \leq 40 μ m
- up to \varnothing 8 mm smooth bore, from \varnothing 9 mm with crosswise grooves



Art. no.	23354 420
Brand	ORION
Manufacturer Part Number	23354420
Outer diameter	84 mm
Diameter	66 mm
Length	110 mm
Clamping diameter	12 mm
Profile shape	Round with transverse grooves
Diameter 2	66 mm
Gross Weight	1.502 kg
Product Group	2AE

EAN

4053625356317