

Adjustable clamps

Short and infinitely adjustable with U-piece



Application:

For clamping workpieces.

Execution:

- With U-piece
- Suitable for tough conditions, e.g. on presses
- Tempered
- Galvanised and blue passivated
- Infinitely adjustable

Delivery:

With U-piece, though without clamping screw



Art. no.	26225 010
Brand	AMF
Manufacturer Part Number	73932
For table grooves according to DIN 650	12 mm, 14 mm
Min./max. clamping height	0-35 mm
Min./max. clamping height 2	30-55 mm
Clamping shoe length	88 mm
Clamping shoe width	38 mm
Bore diameter	13 mm
Distance 2	48 mm
Distance	23 mm
Distance 1	28 mm
Distance 3	14 mm
Suitable screw DIN 787	M12 x 100 mm
Slot nut width of clamping screw	12 mm, 14 mm
Height	55 mm
Gross Weight	0.264 kg
Product Group	260

EAN

4020772073930