

Micrometer

small measuring faces

Mitutoyo

Application:

For measuring narrow external recesses and grooves.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, setting standard



Art. no.	32016 528
Brand	MITUTOYO
Manufacturer Part Number	111-118
Min./max. length measuring range	75-100 mm
Vernier scale	0.01 mm
Measuring surface diameter	3 mm
Measuring surface depth	10 mm
Measuring spindle increments	0.5 mm
Bracket depth	79 mm
Spindle clamping	Yes
Error limit	4 µm
Display	Nonius
Min./max. measurement force	5-10 N
DIN	863
Calibration Group	D
Gross Weight	0.730 kg
Product Group	3MA

EAN

4946368008844