

Precision scales PNS



Application:

Compact dimensions, advantageous in limited space

Execution:

- CAL calibration program for setting accuracy
- High-quality tuning fork weighing system for fast display of weighing value, precise dosing and high mechanical robustness
- Capacity indicator: an increasing bar graph display shows the remaining available weighing range
- Accurate counting: automatic reference optimisation gradually improves the average part weight
- Compact dimensions, advantageous in limited space
- Large, impact-resistant weighing tray made of stainless steel
- with robust tuning fork weighing system

Delivery:

with power supply unit and work protection hood



Art. no.	49000 051
Brand	KERN
Manufacturer Part Number	PNS 600-3
Type description	PNS 600-3
Max. weight measuring range	620 g
Digit increment, weight	0.001 g
Plate diameter	140 mm
Material of cover panel	Stainless steel
With unit counting	Yes
Min. item weight	10 mg
Reproducibility	0.001 g
Linearity	0.004 g
Settling time scale	3 s
Data transmission type	RS232
Housing dimensions (LxWxH)	196 x 293 x 266 mm
Display type	LCD
Gross Weight	5.100 kg
Product Group	447

EAN

4045761183995