

64617 M117 75W 12V 20/CS 1/SKU



Product features and benefits

- Precise filament alignment with patented quartz pinch technology
- OSRAM HLX lamps provide 10% higher luminous efficacy over standard halogen
- Instant on and nearly constant luminous flux over the life of the lamp
- Dimmable

Areas of application

- Microscopy
- Laboratory & Analysis
- UV Curing
- Fiber Illumination
- Surgical & Dental Overhead
- Club & Disco

Product datasheet

Technical data

General product information

Product Number	54124
Product Name	64617 M117 75W 12V 20/CS 1/SKU
Application	Projector
Product Remark	- p (Operating Position) = Horizontal

Electrical data

Nominal Wattage	75 W
Nominal Voltage	12 V
Type of Current	AC

Light technical data

Working Distance a (in)	1.024 in
Working Distance a (mm)	26 mm
Color Rendering Index	100
Average Rated Life	25 h


Physical attributes

Base	G5.3-4.8 BIPIN
Bulb Shape	MR35
Maximum Overall Length (in)	1.398 in
Maximum Overall Length (mm)	35.5 mm
Length l (in)	1.398 in
Length l (mm)	35.5 mm
Length l max. (in)	1.398 in
Length l max. (mm)	35.5 mm
Diameter d (in)	1.378 in
Diameter d (mm)	35.00 mm

Additional product data

Operating Position	p 90/15
Class	C (gas)

Product datasheet



Packaging Information

Product number	EAN/UPC	Packaging	Quantity	Outside dimensions l x w x h	Gross weight
54124	4050300231211	Folding box (SKU)	1	1.3 in x 1.3 in x 2 in	
54124	4050300664675	Shipping box (Case)	20	7.5 in x 5.2 in x 3.4 in	1 lb

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

OSRAM does not accept liability for errors, changes and omissions.