

3 Pin Screw Connection  
Field Assembly 1in 5 out

## Electrical Splitter


WPA Series

3 pin  
250 VAC  
16A



**1x5**  
1in 5 out

**3 Pin**



**FOBOS**<sup>®</sup>

Waterproof Electrical Splitter Series



### Technical Specifications

Number of Poles  
Voltage Rating  
Current Rating  
Cable Cross Section Area  
Durability Voltage  
Insulation Structure  
Min Wire Size OD  
Max Wire Size OD  
Temperature Rating  
IP Class  
Mold Material  
Contact/Terminal Material  
Seal Material

### Product Code WPA-0306N16

3  
250VAC max.  
16A max.  
0,5mm<sup>2</sup> ~ 2,5mm<sup>2</sup>  
1000VAC@60s.  
500 MΩ at 500VDC  
5,5mm  
8,5mm  
-40°C ~ +85°C  
IP68 (1m/30min.)  
PA6  
Nickel-Plated Brass  
Silicone



Max. conductive  
Ø2.75mm

