

PC2050.C.PV.P

Precision cutters - Cutting angle 50° - Flush. OAL: 130 mm



Flush cutter, cutting angle 50°

Documents

Product Details

Market - ELECTRONICS	yes
Category	Economy cutters
Kit	no
ESD safe	no
Body material	C67
Grip handle material	KPS 85A
Degree of bending	50
Head width (mm - in) - C	10.00 - 0.394
OAL (mm - in) - A	130.00 - 5.118
B (mm - in)	8.00 - 0.315
Head thickness (mm - in) - D	5.00 - 0.197
RoHS compliant	yes