


Data Sheet

90° Cable Glands



- Material: Nickel plated brass
- O-ring: NBR, Silicone rubber
- IP rating: IP66
- Temperature: -40 - 105°C

Item No.	Model No. (AG)	Cable range (Ø)	Spanner size (SW1/SW2/SW3)	GL	D1	D2
2861845	M12*1.5	4-8	20/22/14	10	53	45
2861847	M16*1.5	4-8	20/22/18	10	53	44.5
2861848	M20*1.5	6-12	22/25/22	10	55	47
2861849	M25*1.5	13-18	30/30/27	10	66	54
2861850	M32*1.5	15-22	34/34/35	12	69	60
2861851	M40*1.5	22-32	50/55/43	16	106	93
2861852	M50*1.5	25-32	50/55/55	16	106	92
2861853	M63*1.5	37-44	64/73/68	18	128	116
2861854	PG7	4-8	20/22/14	10	52	44
2861855	PG9	4-8	20/22/18	10	53	45.5
2861856	PG11	6-10	20/22/20	10	53	46.5
2861857	PG13.5	6-12	22/24/22	10	55	47
2861858	PG21	13-18	30/35/31	12	68	60
2861859	PG29	18-25	40/43/40	15	85.5	75
2861860	PG36	25-32	50/55/50	16	105	92