

| | | |
|----------------|-----------------------------|--|
| U.I. Lapp GmbH | <h1>DATASHEET</h1> |  |
| | EPIC® H-B 10 SGRH-LB | 79060400 14.11.2013 |

Housing design H-B. The industry standard.
The smallest housing with single and double lever. The right housing is available for every application



Automation



Industrial machinery and plant engineering




Mechanical resistance



Robust



Waterproof



Info

Universal, robust metal housings size H-B 10

Application range

Plant engineering
Light & sound technology
Plastics industry

Product features

Surface-mount base, high version
Single lever
1 cable entry

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

| | |
|--------------------|--|
| Article: | H-B 10 SGRH-LB M32 |
| M: | 32 |
| Pieces / PU: | 10 |
| Material: | Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR |
| Protection rating: | IP 65 (latched) |
| Temperature range: | -40 °C to +100 °C, short-term up to +125 °C |

| | | |
|--------------------|--------------------------------|-------|
| Product Management | Document: EPIC® H-B 10 SGRH-LB | 1 / 2 |
|--------------------|--------------------------------|-------|

| | | |
|-------------------|-----------------------------|--|
| U.I. Lapp GmbH | <h1>DATASHEET</h1> |  LAPP GROUP |
| | EPIC® H-B 10 SGRH-LB | 79060400 14.11.2013 |



| | | |
|--------------------|--------------------------------|-------|
| Product Management | Document: EPIC® H-B 10 SGRH-LB | 2 / 2 |
|--------------------|--------------------------------|-------|