

SMD Resistor, Thick film, 0603

Thick film SMD Resistors, 0603, RND



FEATURES:

Small size and lightweight

Suitable for both flow and re-flow soldering

Matching with placement machines

SPECIFICATION:

| | |
|----------------------|----------------------|
| Housing type | 0603 |
| Rated output | 0.1 W |
| Resistor type | Thick film |
| Rated voltage | 75 V |
| Temperature range | -55...+155 °C |
| Dimensions L x W x H | 1.60 x 0.8 x 0.45 mm |

PRODUCT RANGE:

| Art. Nr. | Resistance | Tolerance | Temperature coefficient |
|-----------------------|------------|-----------|-------------------------|
| RND 1550603SAJ0000T5E | 0 Ω | 0 % | 0 ppm |
| RND 1550603SAF100KT5E | 1 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAF220KT5E | 2.2 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAF270KT5E | 2.7 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAF330KT5E | 3.3 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAF470KT5E | 4.7 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAJ047JT5E | 4.7 Ω | ±5 % | ±400 ppm/°C |
| RND 1550603SAF560KT5E | 5.6 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAF680KT5E | 6.8 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAF820KT5E | 8.2 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAF100JT5E | 10 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAJ0100T5E | 10 Ω | ±5 % | ±200 ppm/°C |
| RND 1550603SAF120JT5E | 12 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF150JT5E | 15 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF180JT5E | 18 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF220JT5E | 22 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAJ0220T5E | 22 Ω | ±5 % | ±200 ppm/°C |
| RND 1550603SAF240JT5E | 24 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF249JT5E | 24.9 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF270JT5E | 27 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAJ0270T5E | 27 Ω | ±5 % | ±200 ppm/°C |
| RND 1550603SAF300JT5E | 30 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF330JT5E | 33 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAJ0330T5E | 33 Ω | ±5 % | ±200 ppm/°C |
| RND 1550603SAF470JT5E | 47 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAJ0470T5E | 47 Ω | ±5 % | ±200 ppm/°C |
| RND 1550603SAF510JT5E | 51 Ω | ±1 % | ±200 ppm/°C |

| Art. Nr. | Resistance | Tolerance | Temperature coefficient |
|-----------------------|------------|-----------|-------------------------|
| RND 1550603SAF549JT5E | 54.9 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF560JT5E | 56 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAJ0560T5E | 56 Ω | ±5 % | ±200 ppm/°C |
| RND 1550603SAF680JT5E | 68 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAJ0680T5E | 68 Ω | ±5 % | ±200 ppm/°C |
| RND 1550603SAF750JT5E | 75 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF820JT5E | 82 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF1000T5E | 100 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAJ0101T5E | 100 Ω | ±5 % | ±200 ppm/°C |
| RND 1550603SAF1100T5E | 110 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1200T5E | 120 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0121T5E | 120 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF1300T5E | 130 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1500T5E | 150 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0151T5E | 150 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF1800T5E | 180 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2000T5E | 200 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2200T5E | 220 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0221T5E | 220 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF2400T5E | 240 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2700T5E | 270 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0271T5E | 270 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF2800T5E | 280 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3000T5E | 300 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3300T5E | 330 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0331T5E | 330 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF3600T5E | 360 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3900T5E | 390 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4300T5E | 430 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4530T5E | 453 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4700T5E | 470 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0471T5E | 470 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF4990T5E | 499 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5100T5E | 510 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5600T5E | 560 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0561T5E | 560 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF6040T5E | 604 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6200T5E | 620 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6800T5E | 680 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0681T5E | 680 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF7500T5E | 750 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF8200T5E | 820 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0821T5E | 820 Ω | ±5 % | ±100 ppm/°C |
| RND 1550603SAF8660T5E | 866 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF9100T5E | 910 Ω | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1001T5E | 1 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0102T5E | 1 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF1101T5E | 1.1 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1131T5E | 1.13 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1201T5E | 1.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1301T5E | 1.3 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1501T5E | 1.5 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0152T5E | 1.5 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF150KT5E | 1.5 Ω | ±1 % | ±400 ppm/°C |
| RND 1550603SAF1581T5E | 1.58 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1601T5E | 1.6 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1651T5E | 1.65 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1801T5E | 1.8 kΩ | ±1 % | ±100 ppm/°C |

| Art. Nr. | Resistance | Tolerance | Temperature coefficient |
|-----------------------|------------|-----------|-------------------------|
| RND 1550603SAF1911T5E | 1.91 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2201T5E | 2.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0222T5E | 2.2 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF2211T5E | 2.21 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2321T5E | 2.32 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2401T5E | 2.4 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2431T5E | 2.43 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2491T5E | 2.49 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2701T5E | 2.7 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2801T5E | 2.8 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3001T5E | 3 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3091T5E | 3.09 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3161T5E | 3.16 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3241T5E | 3.24 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3301T5E | 3.3 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0332T5E | 3.3 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF3401T5E | 3.4 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3571T5E | 3.57 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3601T5E | 3.6 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3901T5E | 3.9 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3921T5E | 3.92 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4121T5E | 4.12 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4301T5E | 4.3 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4701T5E | 4.7 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0472T5E | 4.7 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF4751T5E | 4.75 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4871T5E | 4.87 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4991T5E | 4.99 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5101T5E | 5.1 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5491T5E | 5.49 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5601T5E | 5.6 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5761T5E | 5.76 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6201T5E | 6.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6491T5E | 6.49 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6801T5E | 6.8 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6981T5E | 6.98 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF7501T5E | 7.5 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF7681T5E | 7.68 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF8061T5E | 8.06 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF8201T5E | 8.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF8451T5E | 8.45 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF8871T5E | 8.87 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF9101T5E | 9.1 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF9531T5E | 9.53 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF9761T5E | 9.76 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1002T5E | 10 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0103T5E | 10 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF1022T5E | 10.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1072T5E | 10.7 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1102T5E | 11 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1132T5E | 11.3 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1182T5E | 11.8 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1203T5E | 120 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1202T5E | 12 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1213T5E | 121 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1212T5E | 12.1 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1242T5E | 12.4 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1302T5E | 13 kΩ | ±1 % | ±100 ppm/°C |

| Art. Nr. | Resistance | Tolerance | Temperature coefficient |
|-----------------------|------------|-----------|-------------------------|
| RND 1550603SAF1373T5E | 137 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1372T5E | 13.7 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1502T5E | 15 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0153T5E | 15 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF1582T5E | 15.8 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1602T5E | 16 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1652T5E | 16.5 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1742T5E | 17.4 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1802T5E | 18 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1822T5E | 18.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1912T5E | 19.1 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2002T5E | 20 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2102T5E | 21 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2202T5E | 22 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0223T5E | 22 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF2212T5E | 22.1 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2402T5E | 24 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2432T5E | 24.3 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2552T5E | 25.5 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2672T5E | 26.7 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2702T5E | 27 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2802T5E | 28 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2942T5E | 29.4 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3002T5E | 30 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3092T5E | 30.9 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3162T5E | 31.6 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3302T5E | 33 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0333T5E | 33 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF3402T5E | 34 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3572T5E | 35.7 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3602T5E | 36 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3742T5E | 37.4 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF374JT5E | 37.4 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF3902T5E | 39 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF390JT5E | 39 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF3922T5E | 39.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4022T5E | 40.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4122T5E | 41.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4302T5E | 43 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4322T5E | 43.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4702T5E | 47 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0473T5E | 47 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF4992T5E | 49.9 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF499JT5E | 49.9 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF5102T5E | 51 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5232T5E | 52.3 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5492T5E | 54.9 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5602T5E | 56 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5902T5E | 59 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6042T5E | 60.4 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF604JT5E | 60.4 Ω | ±1 % | ±200 ppm/°C |
| RND 1550603SAF6202T5E | 62 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6342T5E | 63.4 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6802T5E | 68 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6982T5E | 69.8 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF7322T5E | 73.2 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF7502T5E | 75 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF7682T5E | 76.8 kΩ | ±1 % | ±100 ppm/°C |

| Art. Nr. | Resistance | Tolerance | Temperature coefficient |
|-----------------------|------------|-----------|-------------------------|
| RND 1550603SAF8062T5E | 80.6 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF8202T5E | 82 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF9102T5E | 91 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF9312T5E | 93.1 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1003T5E | 100 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0104T5E | 100 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF1023T5E | 102 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1103T5E | 110 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1183T5E | 118 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1243T5E | 124 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1303T5E | 130 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1403T5E | 140 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1433T5E | 143 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1503T5E | 150 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1583T5E | 158 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1603T5E | 160 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1653T5E | 165 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1743T5E | 174 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1803T5E | 180 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1823T5E | 182 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1913T5E | 191 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2003T5E | 200 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2203T5E | 220 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2323T5E | 232 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2403T5E | 240 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2433T5E | 243 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2673T5E | 267 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2703T5E | 270 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3003T5E | 300 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3013T5E | 301 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3243T5E | 324 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3303T5E | 330 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0334T5E | 330 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF3603T5E | 360 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3743T5E | 374 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF3903T5E | 390 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4123T5E | 412 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4303T5E | 430 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4533T5E | 453 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4703T5E | 470 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0474T5E | 470 kΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF4753T5E | 475 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF4993T5E | 499 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5103T5E | 510 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5603T5E | 560 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF5763T5E | 576 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6043T5E | 604 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF6803T5E | 680 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF7503T5E | 750 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF8203T5E | 820 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF9103T5E | 910 kΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1004T5E | 1 MΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAJ0105T5E | 1 MΩ | ±5 % | ±100 ppm/°C |
| RND 1550603SAF1204T5E | 1.2 MΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1504T5E | 1.5 MΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1804T5E | 1.8 MΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2004T5E | 2 MΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF2204T5E | 2.2 MΩ | ±1 % | ±100 ppm/°C |

| Art. Nr. | Resistance | Tolerance | Temperature coefficient |
|-----------------------|-------------------|------------------|--------------------------------|
| RND 1550603SAF4704T5E | 4.7 MΩ | ±1 % | ±100 ppm/°C |
| RND 1550603SAF1005T5E | 10 MΩ | ±1 % | ±200 ppm/°C |