



SIMATIC DP, ELECTRON. MODULE F. ET200S, 4 F-DI/3 F-DO DC24V/2A PROFISAFE, 30 MM WIDTH UP TO CATEGORY 3 (EN954-1)/ SIL2 (IEC61508)/PLD (ISO13849), ALSO USEABLE IN PROFINET- NETWORK WITH IM151-3 HF

Figure similar

Supply voltage	
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Digital inputs	
Number of digital inputs	4
Input voltage	
• Type of input voltage	DC
Standards, approvals, certificates	
Highest safety class achievable in safety mode	
• SIL according to IEC 61508	2
Dimensions	
Width	30 mm
Height	81 mm
Depth	52 mm
last modified:	12.03.2015