

SIMATIC S7-1200, DIGITAL INPUT SB 1221, 4DI, 5VDC 200KHZ, SOURCE



Figure similar

Input current	
from backplane bus 5 V DC, typ.	50 mA
Output voltage	
Power supply to the transmitters	
• Supply current, max.	4 mA; per channel
Power losses	
Power loss, typ.	1 W
Digital inputs	
Number of digital inputs	4; Current-sourcing
• In groups of	1
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	4
Input voltage	
• Type of input voltage	DC
• Rated value (DC)	5 V
• for signal "0"	0 to 1 V
• for signal "1"	2 to 6 V
Input current	
• for signal "0", max. (permissible quiescent current)	3 mA
• for signal "1", min.	6 mA

Input delay (for rated value of input voltage)	
for standard inputs	
— Parameterizable	Yes; 0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
— at "0" to "1", max.	2 µs
for interrupt inputs	
— Parameterizable	Yes
for counter/technological functions	
— Parameterizable	Yes
Cable length	
• shielded, max.	50 m; shielded, twisted pair
Digital outputs	
Number of digital outputs	0
short-circuit protection	No
Interrupts/diagnostics/status information	
Alarms	
• Alarms	Yes
Diagnostic messages	
• Diagnostic functions	Yes
Diagnostics indication LED	
• for status of the inputs	Yes
Degree and class of protection	
Degree of protection to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
Marine approval	
• Germanischer Lloyd (GL)	Yes
Ambient conditions	
Free fall	
• Drop height, max. (in packaging)	0.3 m; five times, in dispatch package
Ambient temperature in operation	
• Permissible temperature range	0 °C to 55 °C horizontal installation, 0 °C to 45 °C vertical installation
• Min.	0 °C
• max.	55 °C
Storage/transport temperature	
• Min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Storage/transport, min.	660 hPa

• Storage/transport, max. 1 080 hPa

Relative humidity

• Permissible range (without condensation) at 25 °C 95 %

Mechanics/material

Type of housing (front)

• plastic Yes

Dimensions

Width 38 mm

Height 62 mm

Depth 21 mm

Weights

Weight, approx. 40 g

last modified: 12.03.2015