

Product type designation

PROFIBUS bus connector, RS485, Fast Connect, without PG socket, 30°

Product description

PROFIBUS bus connector, RS485, Fast Connect, without PG socket, 30°
SIMATIC DP, BUS CONNECTOR FOR PROFIBUS WITH TILTED CABLE OUTLET, MAX.1.5 MBIT/S, INSUL.PIERCING CONN.DEV., 15 X 57,6 X 39,5 MM (WXHxD), W/O LAN TERMINAT.RESIST. AND.PG CONNECTION SOCKET



Suitability for use

For connecting PROFIBUS nodes to the PROFIBUS bus cable

Transmission rate

Transfer rate / with PROFIBUS DP

9.6 kbit/s ... 1.5 Mbit/s

Interfaces

Number of electrical connections

- for PROFIBUS cables
- for network components or terminal equipment

2
1

Type of electrical connection

- for PROFIBUS cables
- for network components or terminal equipment

Integrated insulation displacement contacts for 2-core PB FC installation cables
Sub-D connector (9-pin)

Type of electrical connection / FastConnect

Yes

Mechanical data

Design of terminating resistor

no integrated terminating resistor

Material / of the enclosure

plastic

Design, dimensions and weight

Type of cable outlet

30° cable outlet

Width

15 mm

Height

57.6 mm

Depth

39.5 mm

Net weight

46 g

Permitted ambient conditions

Ambient temperature	
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
Protection class IP	IP20

Product properties, functions, components / general

Product property	
• silicon-free	Yes
Product component	
• PG connection socket	No
• strain relief	Yes

Standards, specifications, approvals

Certificate of suitability	
• RoHS conformity	Yes
• UL approval	Yes
last modified:	09.03.2015