



Flashni Soudner Beacon, Red Lens, White Body, Deep Base, Tone Select Switch (Separate Conns For Sounder And Beacon)

Part Number: FL/RL/W/D SEP



Technical Specifications:

Voltage:	18-28Vdc
	110-230Vac with Powered Base
Current:	68mA (Typical tone 3)
Sound Output:	101dB(A) (Typical tone 3)
Tones:	Pre-set to tone 3
	Versions are available with tone select switch, or independent operation of the beacon.
Volume Control:	10dB
Light Source:	Xenon
Rating:	0.7j
Flash Rate:	1Hz
Lens Colour:	Red, Amber, Blue, Green & Clear
Monitoring:	Reverse Polarity
Temperature:	-10°C to +55°C
Protection:	Shallow Base - IP54 (product exceeds minimum requirements of IP21C as required by EN54-3)
	Deep & U Base - IP65 (product exceeds minimum requirements of IP21C as required by EN54-3)
Construction:	ABS, PC Lens
Weight:	0.33kg
Colours:	Red or White

Features:

- High output sounder beacon
- Automatic sounder synchronisation
- Volume control
- Choice of lens / sounder colour combinations
- Base compatible with the Roshni and Solex beacons
- Lockable base