



Main

| | |
|-------------------------------|-------------------------|
| Range of product | Harmony Relay |
| Product or component type | Socket |
| Contact terminal arrangement | Mixed |
| Product compatibility | Plug-in relay RPM 4 C/O |
| Shape of pin | Flat |
| Device short name | RPZ |
| Sale per indivisible quantity | 10 |

Complementary

| | |
|--|--|
| [I _{th}] conventional free air thermal current | 16 A |
| [U _e] rated operational voltage | < 250 V |
| Tightening torque | < 1 N.m M3.5 |
| Fixing mode | By screw panel) Clip-on 35 mm symmetrical DIN rail) |
| Marking | CE |
| Maximum Width | 1.97 in (50 mm) |
| Net Weight | 0.21 lb(US) (0.094 kg) |

Environment

| | |
|---------------------------------------|--|
| Connections - terminals | - screw clamp terminals, flexible with cable end 1 x 0.5...2 x 1.5 mm ² / AWG 20...AWG 14 - screw clamp terminals, solid without cable end 1 x 0.5...2 x 1.5 mm ² / AWG 20...AWG 12 |
| Standards | IEC 61984 |
| Product certifications | UL CSA |
| Ambient air temperature for storage | -40...185 °F (-40...85 °C) |
| Ambient air temperature for operation | -40...131 °F (-40...55 °C) |
| IP degree of protection | IP20 EN/IEC 60529 |
| Dielectric strength | 2500 V |

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 21128 - ZELIO ICE CUBE RELAY ACCESSORIES |
| Discount Schedule | CP2 |
| GTIN | 00785901635697 |
| Nbr. of units in pkg. | 10 |
| Package weight(Lbs) | 0.21 lb(US) (0.10 kg) |
| Returnability | Yes |
| Country of origin | CN |

Packing Units

| | |
|------------------------------|--------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.18 in (3 cm) |
| Package 1 width | 1.97 in (5 cm) |
| Package 1 Length | 3.35 in (8.5 cm) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 2.23 lb(US) (1.01 kg) |
| Package 2 Height | 2.52 in (6.4 cm) |
| Package 2 width | 3.35 in (8.5 cm) |
| Package 2 Length | 10.00 in (25.4 cm) |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 110 |
| Package 3 Weight | 26.23 lb(US) (11.898 kg) |
| Package 3 Height | 11.81 in (30 cm) |
| Package 3 width | 11.81 in (30 cm) |
| Package 3 Length | 15.75 in (40 cm) |


Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty


| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions



- (1) Relays
- (2) Protection module
- (3) Maintaining clamp

Wiring Diagram



Symbols shown in blue correspond to Nema marking.