

15 Amp Horizontal Rackmount Outlet Strip *1582 Series*

Front Mounted Receptacles

Features



- Designed for power distribution from the front of the unit.
- 1U horizontal 19" rackmount installation.
- Available with lighted on/off switch or red pilot light to indicate power on.
- Available in ASA 61 grey or black powder coat finish.
- [Click here for our surge protected version.](#)

Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Plug types available are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Includes 15 Amp, 125 VAC circuit breaker to prevent accidental overload.
- 6 outlet models include 2 outlets with extra spacing for clearance of most plug in transformers.
- CSA certified, Standards C22.2 (No. 21-95 and No. 42-99)
- UL recognized, Standard UL1363 - file # E166039



Gallery



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit

Black Finish

| Illuminated On/Off Switch Part No. | Illuminated Light Only Part No. | Overall Dimensions | | | Number of Outlets | | NEMA Type | | Plug | | | Cord Length | Rack Units |
|--|---------------------------------------|--------------------|-------|-------|-------------------|------|-----------|--------|---------------|--------------------|-------|----------------|---------------|
| | | Height | Width | Depth | Front | Rear | Outlet | Plug | Blade Type | Rotated Outlets | | | |
| 1582H6A1BK | 1582T6A1BK | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | 5-15P | Straight | No | 6 ft | 1U | |
| 1582H6A1BKRA | 1582T6A1BKRA | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | 5-15P | Straight | Yes | 6 ft | 1U | |
| 1582H6B1BK | 1582T6B1BK | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | 5-15P | Straight | No | 15 ft | 1U | |
| 1582H6B1BKRA | 1582T6B1BKRA | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | 5-15P | Straight | Yes | 15 ft | 1U | |
| 1582H6C1BK | 1582T6C1BK | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | L5-15P | Locking | No | 6 ft | 1U | |
| 1582H6C1BKRA | 1582T6C1BKRA | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | L5-15P | Locking | Yes | 6 ft | 1U | |
| 1582H6D1BK | 1582T6D1BK | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | L5-15P | Locking | No | 15 ft | 1U | |
| 1582H6D1BKRA | 1582T6D1BKRA | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | L5-15P | Locking | Yes | 15 ft | 1U | |
| 1582H8A1BK | 1582T8A1BK | 1.72 | 19.00 | 2.66 | 8 | 0 | 5-15R | 5-15P | Straight | No | 6 ft | 1U | |
| 1582H8B1BK | 1582T8B1BK | 1.72 | 19.00 | 2.66 | 8 | 0 | 5-15R | 5-15P | Straight | No | 15 ft | 1U | |

| Illuminated On/Off Switch Part No. | Illuminated Light Only Part No. | Overall Dimensions | | | Number of Outlets | | NEMA Type | | Plug | | | |
|--|---------------------------------------|--------------------|-------|-------|-------------------|------|-----------|--------|---------------|--------------------|----------------|---------------|
| | | Height | Width | Depth | Front | Rear | Outlet | Plug | Blade Type | Rotated Outlets | Cord Length | Rack Units |
| 1582H8C1BK | 1582T8C1BK | 1.72 | 19.00 | 2.66 | 8 | 0 | 5-15R | L5-15P | Locking | No | 6 ft | 1U |
| 1582H8D1BK | 1582T8D1BK | 1.72 | 19.00 | 2.66 | 8 | 0 | 5-15R | L5-15P | Locking | No | 15 ft | 1U |

ASA 61 Grey Finish

| Illuminated On/Off Switch Part No. | Illuminated Light Only Part No. | Overall Dimensions | | | Number of Outlets | | NEMA Type | | Plug | | | |
|--|---------------------------------------|--------------------|-------|-------|-------------------|------|-----------|--------|---------------|--------------------|----------------|---------------|
| | | Height | Width | Depth | Front | Rear | Outlet | Plug | Blade Type | Rotated Outlets | Cord Length | Rack Units |
| 1582H6A1 | 1582T6A1 | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | 5-15P | Straight | No | 6 ft | 1U |
| 1582H6B1 | 1582T6B1 | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | 5-15P | Straight | No | 15 ft | 1U |
| 1582H6C1 | 1582T6C1 | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | L5-15P | Locking | No | 6 ft | 1U |
| 1582H6D1 | 1582T6D1 | 1.72 | 19.00 | 2.66 | 6 | 0 | 5-15R | L5-15P | Locking | No | 15 ft | 1U |
| 1582H8A1 | 1582T8A1 | 1.72 | 19.00 | 2.66 | 8 | 0 | 5-15R | 5-15P | Straight | No | 6 ft | 1U |
| 1582H8B1 | 1582T8B1 | 1.72 | 19.00 | 2.66 | 8 | 0 | 5-15R | 5-15P | Straight | No | 15 ft | 1U |
| 1582H8C1 | 1582T8C1 | 1.72 | 19.00 | 2.66 | 8 | 0 | 5-15R | L5-15P | Locking | No | 6 ft | 1U |
| 1582H8D1 | 1582T8D1 | 1.72 | 19.00 | 2.66 | 8 | 0 | 5-15R | L5-15P | Locking | No | 15 ft | 1U |

Data subject to change without notice