



Blade Terminal
T&B Catalog Number:

TV14-18BL-XV

UPC Number:

72849414462

Status:

Active

Description:

Insulated Vinyl Blade Terminal for Wire Range 16-14, Blue, Canister

Features


For use in DIN-Style Blade Terminal blocks. Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations.

General

Insulation Type	Insulated Vinyl
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14

Dimension Information

d1 (inches)	.091
D (inches)	.177
E (inches)	.433
F (inches)	.709
L (inches)	1.134
T (inches)	.031
W (inches)	.087



Specifications

Temperature Rating	75°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Application Tools	WT112M, CM2000A
-------------------	-----------------

Packaging

T&B Order Multiple	75
T&B Inner Pack	75
Package in Units	900
Package Type	Canister
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000
Alternate Package Qty	TV1418BLL

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com