

## Product Datasheet

**Product code:** **E6024.CR.BG**

**Product type:** High Precision Pliers

**Made in:** Switzerland

**Description:** The 6024 is a high precision pliers belonging to the long snipe nose plier family. The long jaw length improves the ease of the hold. The serrated surface on the jaw increases its holding capacity. The 6024 is equipped with an ESD Ergo-tek handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The jaws are hardened to 45HRC hardness.


**Head description:** Long Snipe Nose

**Body material:** High carbon-chromium low alloy steel (100Cr6)

**Body finishing:** Sandblasted

**Handle material:** Ergo-tek - Thermoplastic Elastomer + PP compound

**Picture:**




**Dimensions:**


OAL (A)	145.0 mm – 5.709 inch
Width	60.0 mm – 2.362 inch
Height	21.0 mm – 0.827 inch

**Head dimensions:**

Width (C)	10.0 mm – 0.394 inch
Thickness (D)	6.4 mm – 0.252 inch
B	30.0 mm – 1.181 inch
E	1.0 mm – 0.039 inch
F	1.0 mm – 0.039 inch



Dimensions  
in mm



Dimensions  
in inch