

RefLED PAR30

RefLED Retro PAR30 V2 DIM 820L 840 36 SL

0029199



Product features

- High performance LED PAR30 lamp with the same look and feel of traditional PAR lamps
- Glass construction - means no colours clashing between the lamp and fixture
- Reduced visible heatsink from the front
- Mercury-free solution
- Lower maintenance cost
- Lifetime: up to 25,000 hours
- High lumen efficacy
- Dimmable with approved dimmers*
- 3 year warranty
- Suitable for general lighting and accent lighting for hotels, restaurants, bars, lobbies, corridors and halls



PRODUCT OVERVIEW

Product name	RefLED Retro PAR30 V2 DIM 820L 840 36 SL
Technology	LED
Watt (Rated) (W)	11
Type	LED exchangeable
Fixture rating	Open
General application	Hospitality, Museums & Galleries, Residential & Consumer, Retail
ETIM Class	EC001959
E-number FI	4741081
Warranty	3 years
Colour temperature (K)	4000
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Colour Consistency (SDCM)	6
Beam Angle (°)	36
Photobiological Risk Group	RG1
Wattage (W)	11
Product Voltage (V)	230
Dimmable	Yes
Average life (Nominal) (h)	25000
Product EAN number	5410288291994

DATA TABLE

General data

Product name	RefLED Retro PAR30 V2 DIM 820L 840 36 SL
Technology	LED
Watt (Rated) (W)	11
Type	LED exchangeable
Fixture rating	Open
General application	Hospitality, Museums & Galleries, Residential & Consumer, Retail

RefLED PAR30

RefLED Retro PAR30 V2 DIM 820L 840 36 SL

0029199

Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4741081
Warranty	3 years

Optical data

Colour temperature (K)	4000
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Colour Consistency (SDCM)	6
Luminous Intensity (cd)	1900
Beam Angle (°)	36
Photobiological Risk Group	RG1
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	11
Equivalent watt (W)	95
Product Voltage (V)	230
Control gear required	No
No. Of switching cycles before premature failures	>50000
Transformer required	No
Dimmable	Yes
Inrush Current (A)	2.2
Inrush Duration (µs)	50
Lamp Energy Label (class)	F

Lifetime data

Lifespan L70 B50	25000
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000

Physical data

Nominal Product Length (mm)	94
Nominal Product Diameter (mm)	95
Weight (kg)	0.234

Packaging

Single packaging type	Carton
Product EAN number	5410288291994
Packaging single length / height (cm)	10.3
Packaging single width (cm)	10.3
Packaging single depth (cm)	11.1
DUN14 (outer)	15410288291991
Units per outer package	6

RefLED PAR30

RefLED Retro PAR30 V2 DIM 820L 840 36 SL


0029199

Packaging outer length / height (cm)	33.7
Packaging outer width (cm)	24.1
Packaging outer depth (cm)	15.5


Safety data

Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Dimmable with approved dimmers

PHOTOMETRY



TECHNICAL DRAWINGS




RefLED PAR30

RefLED Retro PAR30 V2 DIM 820L 840 36 SL
0029199



SYLVANIA

0029199



11
kWh/1000h



2019/2015

RefLED PAR30

RefLED Retro PAR30 V2 DIM 820L 840 36 SL
0029199



0029199



11
kWh/1000h



2019/2015