


SuperBase V Product specification EU

ID		
Model:	ZDSBV6400	ZDSBV4600
Farbe	Gray	
Kapazität	6438Wh (Semi-Solid State)	4608Wh (LiFePO4)
Max. AC Ausgangsleistung	3800W	7600W peak
Maße	73 x 34.6 x 44.2cm	
Gewicht	130lbs (59kg)	127lbs (57.8kg)
AC Eingang:	12.5A Max, 230VAC 2900W	
XT90 Eingang:	12-150V=25A*, 3000W Max	
ZenT2 Eingang:	230VAC, 3600W Max	
Ausgänge:	4x EU (Type F): 230V~50Hz, 16A	
	2x 5-20: 115V~60Hz, 15A**	
	1x Car Outlet : 12.6V=10A, 126W Max***	
	2x DC5521: 12.6V=3A	
	1x Anderson: 12.6V=30A, 378W Max	
	USB-C(1)/(2): 5V-20V, 100W Max each	
	USB-C(3)/(4): 5V-12V, 20W Max each	
	USB-A(1)(2): 5V2.4A total	
Ladetemperatur:	-20°C to 45 °C	0°C to 45°C
Entladetemperatur:	-20°C to 45°C	
LED Licht	RGB	
Sonstiges:	Smart APP kompatibel	
Lieferumfang	AC-Ladekabel, KFZ-Kabel, Satellitenakku-Kabel, Zubehörtasche	
Geräuschpegel	Umgebung: 39dB Leise-Modus: 48dB, Eingang <400W 0W: 45dB 200W: 51dB 400W: 52.5dB 800W: 54dB 1200W: 56dB 1600W: 57dB 1900W: 58dB 2500W: 58dB	