

Adapter for  
Y-ConJack-16




Adapter for  
Y-ConJack-16M

**DESCRIPTION**

RJ45 180° coupler jack, Cat 5, with 8 pin 1:1 wiring, (including flange adapter and locking clip). For use with Y-ConFlange-10-\* or Y-ConFlange-40-\*

RJ45 180°-Verbindungsbuchse, Cat 5, mit 8-poliger 1:1-Verdrahtung (inklusive Flansch-Adapter und Stopper-Keil). Für den Einsatz mit Y-ConFlange-10-\* oder Y-ConFlange-40-\*



**PART NUMBER**

Y-ConJack - 16 M

Series	↑
16 = for use with Y-ConFlange-10-* only	↑
M = for use with Y-ConFlange-40-* only	↑

**MATERIAL**

Jack body Isolierkörper	PBT, UL94V-0
Shielding Schirmung	Stainless Steel
Contact Kontakte	Contact area Au/Ni
Adapter / Locking Clip	PBT, UL94V-0 PA, UL94V-0

**SPECIFICATIONS**

Operating Temp.: Betriebstemp.	-20°C ~ +80°C
Durability: Lebensdauer	750 mechanical cycles