


ROHS-COMPLIANT

REV	DESCRIPTION	DATE
C	ECR # 080514-5 EDIT PACKING, ADD BARCODE NO.	05/14/08'
D	ECR # 111226-4 ADD LENGTH, EDIT TEST	12/26/11'



NOTE:

- CABLE: UL-20276 [30AWG(7/0.10 T.C)×1P INS:FOAM-SKIN-PE + D.W(7/0.127 T.C) + AL/MY(SPREAD THE WRING)×4C + 28AWG(7/0.127 T.C)×1P INS:HD-PE + 30AWG(7/0.10 T.C)×3C INS:HD-PE + AL/MY + B.D(85%) PVC JACKET; OD:6.0±0.2mm COLOR:BLACK(NK-K01),(SPACE SHUTTLE).
- CONNECTOR:
P1: HDMI 19P MALE CONTACT:15u"; SHELL:NICKEL PLATED .
P2: DVI 18+1 DIGITAL MALE CONTACT:G/F,SHELL:NICKEL PLATED .
- SHIELD P1:INNER MOLD MUST BE WRAPPED COPPER 360° TO CONNECTOR SHELL & CABLE BRAID
P2:COPPER FOIL 360° SOLDER TO CONNECTOR SHELL & CABLE BRAID .
- HOOD:P1&P2:MOLDED TYPE,PVC 45P,COLOR:BLACK(NK-K01) .
- ELECTRICAL TEST:
(1)100% OPEN SHORT & MIS WIRE TEST.
(2)CONTACT RESISTANCE (SEE LIST) Max .
(3)INSULATION RESISTANCE 10M ohm Min .
- PACKING:EACH PC / POLY BAG + HEADER CARD(ROLINE,SIZE:205×84mm)
+ P/N LABEL.


11.04.5519	1000	20	20	7611990198115	3Ω
11.04.5552	5000	50	10	7611990158300	5Ω
11.04.5532	3000	30	20	7611990158294	3Ω
11.04.5522	2000	30	20	7611990158287	3Ω
P/N	L(mm)	T(mm)	PCS/CTN	BAR CODE NO.	CONTACT RESISTANCE

Tolerance Inch M/M	
.X	.015 .30
.XX	.010 .10
.XXX	.005 .05
Draw	FANNIE 12/26/11'
Chek	
Engr	

Rotronic Co., Ltd.				
ROLINE DVI Cable, DVI M - HDMI M, 1m, black				
Item No.: see the chart				
Scale	NONE	Units	M/M	Third Angle Projection
REV:D				Sheet. 1/2

REV	DESCRIPTION	DATE
C	ECC # 111226-5 EDIT PACKING, ADD, BARCODE NO.	05/14/08'
D	ECC # 111226-4 ADD LENGTH, EDIT TEST	12/26/11'

PIN OUT



Tolerance	Inch	M/M
X	.015	.30
XX	.010	.10
XXX	.005	.05

Draw
FANNIE 12/26/11'

Check

Engr

Rotronic Co., Ltd.		
ROLINE DVI Cable, DVI M - HDMI M, 1m, black		
Item No.: see the chart		
Scale	NONE	Units
	M/M	
Third Angle Projection		
REV:D	Sheet. 2/2	