

D-sub-data transmission cord for AS-i Master in IP65, 1,5 m



AS-i Master in IP65 (Specification 2.0)

Clamps	PIN	Function	Colour
1		PE	
2		SHIELD	
3	3	BUS P	green
4	8	BUS N	yellow
5	5	GRND	blue
6		PE	
7		SHIELD	
8		BUS P	
9		BUS N	
10	6	+5 V	red

Article no. BW1097	
Connection	RS 485 prefabricated cable
Storage temperature	-40°C ... +85°C
Operating temperature	-25°C ... +60°C
Protection category (IEC) EN 60529	connector IP65, plug IP20
Dimensions (L, W, H)	ca. 50 mm, 20 mm, 30 mm
Length	1,5 m

D-sub-data transmission cord 9-pin, 1,8 m



Article no. BW1058	
Connection	D-Sub plug D-Sub socket
Length	1,8m
PIN 1 connected with PIN 1	

D-sub-data transmission cord for AS-i Gateways with CAN interface




AS-i/CAN Gateway

Clamps	PIN	Function	Colour
1		n.c.	
2	7	CAN_H	white
3		SHIELD	
4	2	CAN_L	brown
5		n.c.	

Article no. BW1226	
Connection	D-subsocket, 5-pin COMBICON plug
Operating temperature	-40°C ... +85°C
Storage temperature	-25°C ... +60°C
Protection category (IEC) EN 60529	IP20
Dimensions (L, W, H)	ca. 50 mm, 20 mm, 30 mm
Length	1,5 m

AS-i addressing cable (with COMBICON connector) for direct addressing with AS-i master



Article no. BW2324	
Connection	round connector 2-pin COMBICON-connector
Length	1,5 m
Connector (Master)	+ AS-i -

AS-i addressing cable - infrared addressing adapter



Article no. BW1935	
Connection	infrared head/M12 connector
Length	1 m

AS-i addressing cable for addressing with handheld address programming device



Article no. BW3304	
Connection	AS-i profile cable to M12
Length	1,0 m
scoop of delivery incl. 2 x substructure modules 60 mm x45 mm	

AS-i addressing cable for direct addressing with AS-i master



Article no. BW3305	
Connection	AS-i profile cable to COMBICON
Length	1,0 m
scoop of delivery incl. 2 x substructure modules 60 mm x45 mm	

Connecting cable (Module/programming device)



Article no. BW1802	
Connection	round connector 2-pin/ M12 connector
Length	1,6 m

Addressing plug



Article no. BW3340	
Color	black
Packing unit	5 pieces

Protection cap for not used M12 sockets



Article no. BW2368	
Color	blue
Packing unit	50 pieces

Memory plug cover



Article no. BW3155	
Color	blue
Packing unit	1 piece

Cross-Link-cable for AS-i/Ethernet Gateway



Article no. BW1304

AS-i Probe



Article no. BW1745

Chip card for Bihl+Wiedemann AS-i products



Article no.	BW2079	BW2222
Memory capacity	32 kByte (256 kbit)	128 kByte (1024 kbit)
Labeling on the chip card	C 256	C 1024
Weight	approx. 1 g	
Dimensions (L / W / H in mm)	25 / 15 / 1	
Accessories:		
<ul style="list-style-type: none"> • BW2079 for all Standard and all Safety products with chip card by Bihl + Wiedemann. • BW2222 for Safety Monitors and Gateways in Stainless Steel Safety Version 4.X (for maximum 4 Safety configurations on a chip card). 		