

Product characteristics

Splitter box

Connector

Gold-plated contacts

Electrical data

Electrical design

DC

Operating voltage [V]

15...30 DC

Max. total current load [A]

1

Max. current load per location [A]

1

Protection class

III

Environment

Ambient temperature [°C]

-25...80

Ambient temperature (moving) [°C]

-5...60

Protection

IP 67

Mechanical data

Design

8 way

Housing materials

PBT-GF 20; Brass nickel-plated

Tightening torque for knurled nut [Nm]

0.8...1.5

Weight [kg]

0.124

Displays / operating elements

Output status indication LED

8 x yellow

Operation LED

green




Electrical connection

Connection

M12 connector

Wiring

EBC045 - Splitter box - eclass: 27279219 / 27-27-92-19



Remarks		
Pack quantity	[piece]	1
Other data		
Ports		M8