

Product characteristics

Jumper

M8-plug / M12-socket

Free from silicone

Gold-plated contacts

For hygienic and wet areas in the food industry

Electrical data

Electrical design

DC PNP

Operating voltage [V]

10...36 DC

Current rating [A]

3

Protection class

III

Environment

Ambient temperature [°C]

-25...80, cULus: max. 50 °C

Ambient temperature (moving) [°C]

5...80, cULus: max. 50 °C

Protection

IP 65 / IP 67 / IP 68 / IP 69K

Mechanical data

Design

angled / angled

Material body

housing connector: PVC orange; housing socket: PVC black transparent; sealing: EPDM

Material nut

stainless steel 316L / 1.4404

Tightening torque for knurled nut [Nm]

plug: 0.3...0.5 *) / socket: 0.6...1.5

Drag chain suitability

Bending radius for flexible applications: min. 10 x cable diameter
max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
Travel speed: > 1 million
Bending cycles: > 1 million
Torsional strain: ± 180 °/m

Displays / operating elements

Output status indication LED

yellow

Operation LED

green

Electrical connection

Connection




PVC cable / 0.3 m;
3 x 0.34 mm² (42 x Ø 0.1 mm); Ø 4.9 mm

Sheath colour

orange

Wiring

EVT304 - Jumper - eclass: 27279201 / 27-27-92-01



Remarks

Remarks

*) Take into account the maximum value of the counterpart!

Pack quantity

[piece]

1