



SIMATIC DP, DISTRIBUTED I/O DP/DP COUPLER COUPLING MODULE FOR CONNECTING TWO PROFIBUS DP NETWORKS REDUNDANTE POWERSUPPLY

Figure similar

Supply voltage	
Rated value (DC)	Yes
<ul style="list-style-type: none"> • 24 V DC 	
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Protocols	
PROFIBUS DP	Yes
AS-Interface	No
Interrupts/diagnostics/status information	
Status indicator	Yes
Diagnostic messages	
<ul style="list-style-type: none"> • Diagnostic functions 	Yes
Degree and class of protection	
Degree of protection to EN 60529	Yes
<ul style="list-style-type: none"> • IP20 	
Ambient conditions	
Ambient temperature in operation	
<ul style="list-style-type: none"> • Min. 	0 °C
<ul style="list-style-type: none"> • max. 	60 °C
Dimensions	
Width	40 mm
Height	127 mm
Depth	117 mm

last modified:

12.03.2015