

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731120133](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Pneumatic Contact, Male, Straight, 2.60mm Tube Inner Diameter

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	D-Sub Products
Series	173112
Brochure Order No	987651-9941
Contact Type	Pneumatic
Exclude SD Check	Yes
Overview	FCT D-Sub Connectors
Product Category	Contacts
Product Name	FCT Products
Type	Mixed Layout
UPC	889056488884

Physical

Durability (mating cycles max)	500
Gender	Male
Material - Contact	Metal Alloy
Material - Retaining Clip	PEI
Net Weight	1.300/g
Orientation	Straight
Packaging Type	Bag
Plating - Contact	N/A
Temperature Range - Operating	-10° to +60°C

Electrical

Current - Maximum per Contact	N/A
-------------------------------	-----

Material Info

Engineering Number	FMG001P149KR
--------------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[173112 Series](#)

Use With

FCT Mixed Layout Connectors