

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2064600021](#)  
**Status:** **Active**  
**Overview:** [Micro-Fit Connector System](#)  
**Description:** Micro-Fit+ Crimp Terminal, Female, with Tin (Sn) over Nickel Plating, 20-24 AWG

**Documents:**

[Drawing \(PDF\)](#) [Test Summary 2064600000-TS-000 \(PDF\)](#)  
[Product Specification 2064600000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 2064600000-PK-000 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">206460</a>
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Datasheet Order No	987651-9552
Overview	<a href="#">Micro-Fit Connector System</a>
Product Name	Micro-Fit+
UPC	191130125357

**Physical**

Durability (mating cycles max)	25
Gender	Female
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin over Nickel
Net Weight	0.066/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm
Wire Size AWG	20, 22, 24
Wire Size mm <sup>2</sup>	0.20-0.50


**Electrical**

Current - Maximum per Contact	12.5A
Voltage - Maximum	600V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2064600000-PK-000
Product Specification	2064600000-PS-000
Sales Drawing	2064600000-SD-000
Test Summary	2064600000-TS-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[206460 Series](#)

**Use With**

Micro-Fit Receptacle Housing [206461](#)