

[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Centrifugal Blowers](#) > **04520GA-12N-AA-00**


[Back To DC Centrifugal Blowers](#)

Have a question about this product?



[Ask Our Experts](#)

DC Centrifugal Blowers - 04520GA-12N-AA-00



We use cookies. We may place these for analysis of our visitor data, to improve our website, show personalized content and to give you a great customer experience. For more information about how we use your personal data and our cookies, please see our [privacy policy](#).

Privacy Policy

Accept

[Get a sample](#)

Specifications

Category	DC Centrifugal Blowers
Part Number	04520GA-12N-AA-00
Legacy Part Number	BM4520-04W-B50-L00
Frame Size [mm]	45
Frame Width [mm]	20
Nominal Voltage [V]	12
Max. Air Flow [CFM]	5.6
Max. Static Pressure [In H2O]	0.76
Speed [min-1]	7700
Noise [dB]	35

We use cookies. We may place these for analysis of our visitor data, to improve our website, show personalized content and to give you a great customer experience. For more information about how we use your personal data and our cookies, please see our [privacy policy](#).

Privacy Policy

[Accept](#)

Operating Voltage Upper [V]	13.8
------------------------------------	------

Nominal Current [A]	0.17
----------------------------	------

Input Power [W]	2.04
------------------------	------

Mass [g]	25
-----------------	----

Have A Question?

Our precision component experts can help you find the right solutions.

Contact Us Today

Find A Distributor

Find Sales Rep For Fans

PRODUCTS

[See All Products](#)

[Find A Distributor](#)

[Find a Sales Representative](#)

We use cookies. We may place these for analysis of our visitor data, to improve our website, show personalized content and to give you a great customer experience. For more information about how we use your personal data and our cookies, please see our privacy policy.

Privacy Policy

Accept