



Main

Range	Linergy
Product name	FT
Device short name	GV2G
Product or component type	Terminal block
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys GV2 TeSys D TeSys K TeSys U

Complementary

[Ie] rated operational current	63 A
Mounting location	35 mm DIN rail
IP degree of protection	IP20 conforming to IEC 60529
[Ui] rated insulation voltage	690 V IEC 60947-1
Connections - terminals	Screw clamp terminals 1 solid AWG 4 Screw clamp terminals 1 0.00...0.02 in ² (1.5...16 mm ²) flexible with cable end Screw clamp terminals 1 0.00...0.02 in ² (1.5...16 mm ²) flexible without cable end Screw clamp terminals 1 0.00...0.04 in ² (1.5...25 mm ²) solid Screw clamp terminals 2 0.00...0.01 in ² (1.5...4 mm ²) flexible with cable end Screw clamp terminals 2 0.00...0.01 in ² (1.5...6 mm ²) solid Screw clamp terminals 2 0.00...0.01 in ² (2.5...4 mm ²) flexible without cable end Screw clamp terminals 1 flexible AWG 4
Tightening torque	15.05 Lbf.in (1.7 N.m) screw clamp terminals 19.47 lbf.in (2.2 N.m) connector
Net Weight	0.25 lb(US) (0.115 kg)

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901808350
Nbr. of units in pkg.	1
Package weight(Lbs)	0.27 lb(US) (0.12 kg)
Returnability	Yes
Country of origin	RO

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.01 in (5.1 cm)
Package 1 width	4.69 in (11.9 cm)
Package 1 Length	5.98 in (15.2 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	1
Package 2 Weight	4.23 oz (120 g)
Package 2 Height	2.01 in (5.1 cm)
Package 2 width	4.69 in (11.9 cm)

Package 2 Length	5.98 in (15.2 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	11.04 lb(US) (5.009 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Sets of Busbars GV2G445, GV2G454, GV2G472, with Terminal Block GV2G05



	l	p
GV2G445 (4 x 45 mm)	179	45
GV2G454 (4 x 54 mm)	206	54
GV2G472 (4 x 72 mm)	260	72

Number of tap-offs	a			
	5	6	7	8
GV2G445	224	269	314	359
GV2G454	260	314	368	422
GV2G472	332	404	476	548