

Electronic 3-point internal micrometer

Micromar 44 EWR, carbide-tipped measuring surfaces



Application:

For measuring through holes and blind bores and short centring shoulders in series.

Execution:

- Self-centring and self-aligning
- Carbide-tipped measuring faces
- Locking function
- Zero setting at any position
- mm/inch changeover
- ABS function
- Preset function

Delivery:

Single device with battery (1 x 3 V lithium, type CR 2032) and operating instructions in a case



Art. no.	31912 020
Brand	MAHR
Manufacturer Part Number	4191125
Min./max. length measuring range	20-25 mm
Measuring depth	68 mm
Data transmission type	multiCOM
Digit increment	0.001 mm
IP protection class	IP 52
Error limit	0.004 mm
Display	Digital
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
DIN	863
Calibration Group	I
Gross Weight	1.244 kg
Product Group	305

EAN

4059192010942