

## Electronic outside micrometer

with replaceable inserts

Mitutoyo

### Application:

For measuring e.g. Screw thread

### Execution:

- carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Preset function
- IP65

### Advantage:

- IP65

### Delivery:

Includes box, set standard (60°), hand guard, adjustment wrench, battery



<b>Art. no.</b>	<b>32017 584</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	326-252-30
<b>Display</b>	Digital
<b>Min./max. length measuring range</b>	25-50 mm
<b>Digit increment</b>	0.001 mm
<b>Measuring surface diameter</b>	6.3 mm
<b>IP protection class</b>	IP 65
<b>Data transmission type</b>	DIGIMATIC
<b>Spindle clamping</b>	Yes
<b>Digit height</b>	7.5 mm
<b>Functions</b>	Hold-function (AE lock), Preset function, ABS function, Automatic switch-off
<b>Min./max. measurement force</b>	5-10 N
<b>Error limit</b>	4 µm
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	1,5 V SR44
<b>DIN</b>	863
<b>Bracket depth</b>	32 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Calibration Group</b>	D
<b>Gross Weight</b>	0.820 kg
<b>Product Group</b>	3MA

### EAN

4946368695778