



**Part no.: 50114700**  
**KB DN/CAN-10000 SA**  
**Connection cable**




Figure can vary

## Contents

- Technical data
- Electrical connection

Part no.: 50114700 – KB DN/CAN-10000 SA – Connection cable

## Technical data

### Basic data

Suitable for interface	CANopen DeviceNet
------------------------	----------------------

### Connection

#### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

#### Connection 2

Type of connection	Open end
--------------------	----------

#### Cable properties

Number of conductors	5 Piece(s)
Sheathing color	Black
Shielded	Yes
Cable design	Connection cable (open on one end)
Cable diameter (external)	7 mm
Cable length	10,000 mm
Sheathing material	PUR
Suitability for drag chains	Yes
Traverse rate	Max. 3.3 m/s with horiz. traverse path of 5m and and max. acceleration of 5m/s <sup>2</sup>

### Mechanical data


#### Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

## Electrical connection

Connection 1	
Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Part no.: 50114700 – KB DN/CAN-10000 SA – Connection cable



<b>Connection 2</b>	
Type of connection	Open end