



worldwide



140-180EL Cordless 12V  
140 Staples 8-12mm 180 Nails 10mm  
UK  
EU

# Catalogue 2023

Europe's Widest Quality Range of **Stapling and Nailing Products**



Europe's Widest Quality Range of **Stapling and Nailing Products**

---

# Contents

|   | Pages          |
|---|----------------|
| Tacwise Story   | 6 – 7          |
| New Products  | 8 – 9          |
| <b>Hand Tackers</b>   | <b>10 – 29</b> |
| 13, 140 & 53 Series Tools at a Glance                                   | 11             |
| Z1 Series   | 12             |
| Z2 Series   | 13 – 14        |
| Z3 Series   | 16 – 17        |
| Cable Tackers   | 18 – 19        |
| Hammer Tackers  | 20 – 21        |
| Hammer Tacker Bundles   | 22             |
| Staple Remover  | 23             |
| 13, 140 & 53 Series Tools – Features, Applications & Specifications     | 24 – 27        |
| Stapling Pliers   | 28 – 29        |
| <b>Cordless Staple/Nail Guns</b>  | <b>30 – 35</b> |
| Hobby 53-13EL 4V  | 30 – 31        |
| 140 and 53-13EL 12V   | 32 – 33        |
| Ranger EL-PRO 18V   | 34 – 35        |
| <b>Corded Electric Staple &amp; Nail Guns</b>                           | <b>36 – 47</b> |
| Compact Electric Tackers  | 36 – 39        |
| Medium Duty Electrics – 181ELS & 191EL Pro                              | 40 – 41        |
| Heavy Duty Electrics – Duo 35 & Duo 50                                  | 42 – 43        |
| Heavy Duty Electrics – 400ELS Pro & 18G/50                              | 44 – 45        |
| Electric Staple & Nail Guns – Features, Applications & Specifications   | 46 – 47        |
| <b>Hand &amp; Electric Staple &amp; Nail Guns – Staples &amp; Nails</b> | <b>48 – 51</b> |

|  | Pages          |
|--|----------------|
| <b>Hot &amp; Cool Melt Glue Guns</b>                                   | <b>52 – 55</b> |
| Cordless Glue Guns   | 52 – 53        |
| Corded Glue Guns   | 54             |
| Glue Guns & Glue Sticks – Features, Applications & Specifications      | 55             |
| <br>   |                |
| <b>Air Stapling</b>  | <b>56 – 64</b> |
| General Purpose & Upholstery Staple Guns                               | 58 – 60        |
| General Purpose & Upholstery Staple Guns – Staples                     | 60             |
| Narrow Crown Staplers  | 61             |
| Narrow Crown Staplers & Corrugated Fasteners – Staples                 | 62             |
| Heavy Duty & Wide Crown Staplers & Corrugated Fastener                 | 63 – 64        |
| <br>   |                |
| <b>Air Nailing</b>   | <b>65 – 83</b> |
| Nailers & Pinners  | 65 – 67        |
| Nails, Brads & Finish Nails  | 68 – 69        |
| Coil Nailers   | 70 – 75        |
| Coil Nailers – Nails   | 76             |
| Strip Nailers  | 77 – 78        |
| Strip Nailers – Nails  | 78             |
| Variations of Air Tool Triggers, Choosing the Correct Fastening Length | 79             |
| Air Tools – Features, Applications & Specifications                    | 80 – 83        |
| <br>   |                |
| <b>RAPESCO® Packaging</b>  | <b>84 – 87</b> |
| Packing Tape Dispensers  | 84 – 85        |
| Packing Tapes and Cutting Knives                                       | 86 – 87        |
| Browse by Project  | 88 – 89        |
| Key & Conversion Chart   | 90             |

# Our Story

## User comfort, performance and best value

With a wealth of industry experience, Tacwise delivers the most complete range of quality stapling and nailing products in Europe, from DIY through to all-professional models and consumables.

Using our extensive knowledge, we build class-leading tools and fasteners for world markets with a focus on user comfort, performance and best value.

Productivity and satisfaction are at the very heart of our mission, enabling users to do and achieve more. Our cordless tools are perfect for convenience without the hassle of wires or cables.



## Care for the environment


We're stripping out single-use plastic without compromising on protective packaging and we plan to do much more. We'll accelerate our efforts to find more, new ways to reduce, reuse and recycle.

Our tools are easily disassembled to allow for specific recycling, such as our tackers, which are screwed together whilst others are mostly welded or pressed together.

Products are designed to achieve strength and longevity through carefully selected materials.

Our worldwide customers expect us to make our designs, developments, manufacturing processes and products as energy efficient and environmentally responsible as possible. It is a continuing mission.

Like quality, environmental management is a journey without a destination. We have to think globally and act locally. After all, we are all in this together.



## Repair, reuse and recycle

We must all be more responsible and shift away from the global 'throw away' society. At Tacwise we have made it easy and inexpensive to service our air tools by yourself. Simply follow the step-by-step video instructions and quickly identify and purchase the parts you need from Tacwise.com.



## What is Germ-Savvy<sup>®</sup>

Tacwise/Rapesco have invested in advanced technology to create a range of antibacterial products to help improve hygiene wherever you are working. Our Germ-Savvy<sup>®</sup> antimicrobial agent is added to external plastic parts during manufacture to provide protection for the lifetime of the product.

- It kills up to 99% of bacteria.
- It's ISO certified, making it highly credible.
- With no price premium.

Look for the Germ-Savvy symbol throughout this catalogue



**NEW**

# 81 new products

## Hand Tackers

We've added 2 new lightweight additions to the Z2 range of hand tackers for 53 & 13 type staples in one tool.

**3 new items**



## Cordless Staple/Nail Guns

Our new body only versions of our feature-full 12V cordless staple/nail guns.

**2 new items**



## Hammer Tackers

Offering exceptional value, these hammer tackers are supplied in bundles with up to 75,000 staples.

**4 new items**



## Corded Electric Tools

Presenting 2 new compact corded tools packed with features and 4 new bundles with fastenings included.

**6 new items**



## Stapling Pliers

We've added in a stapling plier range with 8 high performing pliers, including the durable Porpoise Classic and Porpoise One – with a bypass anvil.

**8 Rapesco items**



## Staples

Made from high grade raw materials that always deliver outstanding results. With 13 new additions to our staple range you'll find what you need with ease.

**2 new plus 11 Rapesco items**





### Staple/Nail Selection Packs

3 new handy selection packs all supplied in resealable clams to keep your staples and nails organised.

**3 new items**



### Cordless Glue Guns

2 new 12V hot melt glue guns, 1 for 12mm glue sticks and a new variation of the 12V 7mm gun.

**2 new items**



### Air Stapling & Nailing

5 new reliable and versatile products, including the 90mm coil nailer and 90mm 21° inclined strip nailer.

**5 new items**



### Brad/Finish Nails

New pack sizes for the ever-popular 18G nails and new reusable storage boxes for our 15G finish nails.


**14 new items**



### Coil & Strip Nails

Our 4 new stainless steel coil nails are ideal for external applications with long-lasting corrosion protection. Plus 3 new strip nails.

**7 new items**



### Packing Tapes, Dispensers & Cutters

We've added a range of 14 packing tapes, dispensers and cutting products to make sure your packing needs are met.

**14 Rapesco items**



# Hand Tackers

## Loaded with features

Tacwise incorporate many great user features into their tools as standard compared to other brands, making these high quality dependable tools a pleasure to use and own. Our extensive range of lightweight and heavy-duty hand tackers are compatible with the popular 13, 53 and 140 series staples. Clean designs and outstanding engineering make this range ideal for a variety of jobs.



### Easily disassembled for recycling

Committed to sustainable manufacturing, Tacwise hand tools are in a class of their own. Easy to disassemble for recycling, simply unscrew the tool housing and dismantle.

### Wide ergonomic grip

Our range of hand tackers all feature specially developed ergonomic grips, providing maximum user comfort and avoiding hand strain when in use.



### Lock-down handle

This useful safety feature helps save space and offers a quick and easy storage solution. Handles can be locked without the need to fire the tool, some pull into the lock position and others have a separate switch.

### Staple viewing window

Our staple viewing window located at the front of the tool is a helpful feature, that shows when staples need to be replenished when they are running low.



### Tough steel working parts/cutaway nose

Our durable range is built to last; featuring full steel chassis and a hardened steel magazine rail even on the very lightweight models.

### Linear power curve

Avoids that uncomfortable 'snap' at the end of the firing cycle. This superb feature reduces hand strain and improves comfort during prolonged periods of use.



Z1 & Z3 Tackers

Most other tools (extra force)

Staple firing point

Time



### Bottom-loading

All our tackers feature a bottom-loading magazine, offering quick and easy loading. This simple feature provides easy access and makes for hassle-free use.



# 13, 140 & 53 tools at a glance

|           |                     | 13 Series   | 140 Series                               | 53 Series   |
|-----------|---------------------|---|--|---|
| Hand      | Compact (4-8mm)     | Z2 53-13M (1218)            Z2 53-13T (1728)                          | Z1-140 (0854)                            | Z2 53-13T (1728)            Z1-53 (0856)            Z1-53 Kit (0889)    |
|           |                     | Z2-M Kit (1219)            Z2 53-13L (1727)                           |  | Z2 53-13M (1218)            Z2-M Kit (1219)            Z2 53-13L (1727) |
|           | Heavy Duty (4-14mm) | Z3-13L (0881)            Z3-13 (0880)                                 | Z3-140L (0807)            Z3-140 (0806)  | Z3-53 (0808)            Z3 4-in-1 (1022)                                |
|           | Hammer              | A19 (1327)  | A11 (0322)            A54 (1173)         | A19 (1327)  |
| Cordless  | 4V                  | Hobby 53-13EL (1563)            Hobby 53-13EL with storage bag (1564) |  | Hobby 53-13EL (1563)            Hobby 53-13EL with storage bag (1564)   |
|           | 12V                 | 53-13EL (1565/1632)   | 140-180EL (1586/1603)                    | 53-13EL (1565/1632)   |
| Electric  | Corded              | Hobby 53 & 13EL (1702)  | 140EL (0274)            140EL Pro (1703) | Hobby 53EL Kit (1038)            Hobby 53 & 13EL (1702)                 |
| Pneumatic | Air                 |   | A14014V                                  |   |

Hand Tackers | Stapling up to 8mm

# Z1 Compact Metal Tackers

Tough and lightweight

Whilst being compact, these models are also perfect for trades. With a broad, comfortable grip to avoid hand strain, combined with low grasp height and the metal/polymer combination body it is tough and lightweight at just 0.26kg.



Watch the Z1 video



Z1-53 Kit



## Z1-53 Metal Staple Tacker 53/4-8mm

**Professional** Code: 0856 Includes: 200pcs 53 staples

• Whilst stocks last

- 53 Staples 4-8mm (Capacity 125)
- 0.26kg
- Retail Clam
- Trade = 6 Units  
Transit = 36 Units

## Z1-53 Metal Staple Kit 53/4-8mm

**Professional** Code: 0889 Includes: 200pcs 53 staples

- 53 Staples 4-8mm (Capacity 125)
- 0.26kg (tool only)
- Retail Clam
- Trade = 6 Units  
Transit = 36 Units

## Z1-140 Metal Staple Tacker 140/6-8mm


**Professional** Code: 0854 Includes: 200pcs 140 staples

- 140 Staples 6-8mm (Capacity 83)
- 0.26kg
- Retail Clam
- Trade = 6 Units  
Transit = 36 Units

# Z2 53-13T Transparent

## Perfect for DIY

Stylish, compact and lightweight. Built for both the professional and hobby user alike. The frosted transparent design is paired with outstanding engineering. For the very popular 53 & 13 series staples.



### Tool Features

Comfortable and ergonomic. Incorporating a powerful range of features unseen before on traditional hand stapling tackers. Even our smallest tackers include a full steel chassis with a hardened steel magazine rail to avoid wear as the staple strip travels.

## Z2 53-13T Staple Tacker 53/4-8mm 13/4-8mm NEW

Professional Code: 1728 Includes: 300pcs 53 staples

 53 Staples 4-8mm  
(Capacity 105)  
13 Staples 4-8mm  
(Capacity 110)

 0.19kg

 Hanging  
Retail Box

 Trade = 6 Units  
Transit = 36 Units

Hand Tackers | Stapling up to 8mm

# Z2 53-13L Lightweight

## Perfect for DIY

Powerful and super lightweight. At just 0.18kg, this polymer-bodied tool is tough yet comfortable to use for long periods of time.


## Attention to the detail

At Tacwise we pride ourselves on adding details and features to our tools that benefit and enhance the user experience.




Z2 53-13L Staple Tacker 53/4-8mm 13/4-8mm **NEW**

Professional Code: 1727 Includes: 300pcs 53 staples

 53 Staples 4-8mm  
(Capacity 105)

 0.18kg

 Hanging  
Retail Box

 Trade = 6 Units  
Transit = 36 Units

# Z2 53-13M All-Metal Staple Tacker

For professional and serious DIY

This all-metal aluminium bodied tool is lightweight and durable. Fires both 53 and 13 series staples without any need for adjustment. Requires very little firing pressure.



## Z2 53-13M Staple Tacker 53/4-8mm 13/4-8mm

**Professional** Code: 1218 Includes: Margin guide, 300pcs 13 staples

- 

53 Staples 4-8mm  
(Capacity 105)
- 

13 Staples 4-8mm  
(Capacity 110)
- 

0.30kg
- 

Hanging  
Retail Box
- 

Trade = 6 Units  
Transit = 12 Units

## Z2-M Staple Tacker Kit 53/4-8mm 13/4-8mm

**Semi-Professional** Code: 1219 Includes: Margin guide, remover, 5000pcs 53 staples

- 

53 Staples 4-8mm  
(Capacity 102)
- 

13 Staples 4-8mm  
(Capacity 110)
- 

0.32kgs  
(tool only)
- 

Carry  
Case
- 

Trade = 6 Units  
Transit = 12 Units

• Whilst stocks last



For complete convenience, you'll find everything you need in one handy kit featuring our all-metal staple tacker, a handy staple remover and a selection of the most commonly used and versatile 53 series staples.

# Z3 3-in-1 Tackers



Watch the Z3 video

## Durable die cast

Ultra tough and weighing in at a heavyweight 0.9kg, these aluminium die cast tools reach the highest standards within their category. Utilising die cast extrusion technology, resulting in fewer parts for enhanced reliability.



### Z3-140 Metal Staple/Nail Tacker

- 140/6-14mm
- 180(18G)/10-15mm
- 180/15mm headless

|                     |  |
|---------------------|--|
| <b>Professional</b> |  |
| Code: 0806          | Includes: Margin guide, 200pcs 140 staples                 |
| Code: 1263          | Includes: Margin guide, 140 selection pack, staple remover |

**NEW**

|                                  |                                       |                                     |       |                   |                 |
|----------------------------------|---------------------------------------|-------------------------------------|-------|-------------------|-----------------|
| 140 Staples 6-14mm (Capacity 83) | 180 (18G) Nails 10-15mm (Capacity 90) | 180/15mm Headless Pin (Capacity 90) | 0.9kg | 0806  Retail Clam | Trade = 6 Units |
|                                  |                                       |                                     |       | 1263  Retail Box  | Trade = 1 Unit  |

Sitting at the top of the range, this all professional workhorse drives 140 flat wire staples and 180 series nails. Built to withstand years of trouble-free use. A true heavyweight.

### Z3-53 Metal Staple/Nail Tacker

- 53/6-14mm
- 180(18G)/10-15mm
- 180/15mm headless

|                          |            |   |
|--------------------------|------------|---|
| <b>Semi-Professional</b> | Code: 0808 | Includes: Margin guide, 200pcs 53 staples |
|--------------------------|------------|---|

|                                  |                                       |                                     |       |             |                    |
|----------------------------------|---------------------------------------|-------------------------------------|-------|-------------|--------------------|
| 53 Staples 6-14mm (Capacity 125) | 180 (18G) Nails 10-15mm (Capacity 90) | 180/15mm Headless Pin (Capacity 90) | 0.9kg | Retail Clam | Trade = 6 Units    |
|                                  |                                       |                                     |       | Retail Box  | Transit = 12 Units |

The 53 discreet fine wire version of the heavyweight all professional tool. Ideally suited to trades on the move and working around site.

### Z3-13 Metal Staple/Nail Tacker

- 13/6-14mm
- 180(18G)/10-15mm
- 180/15mm headless

|                          |            |   |
|--------------------------|------------|---|
| <b>Semi-Professional</b> | Code: 0880 | Includes: Margin guide, 200pcs 13 staples |
|--------------------------|------------|---|

|                                  |                                       |                                     |       |             |                    |
|----------------------------------|---------------------------------------|-------------------------------------|-------|-------------|--------------------|
| 13 Staples 6-14mm (Capacity 150) | 180 (18G) Nails 10-15mm (Capacity 90) | 180/15mm Headless Pin (Capacity 90) | 0.9kg | Retail Clam | Trade = 6 Units    |
|                                  |                                       |                                     |       | Retail Box  | Transit = 12 Units |

The 13 series is a fine wire staple commonly used in education and other markets.



# Z3L 3-in-1 Tackers

## Tough lightweight polymer

Tough and durable yet weighing just 0.4kg, this polymer range is a big hit with trades on the move. With a cut away nose for enhanced firing access and a bottom loading magazine for easy switching between staples, nails and headless pins without any adjustment.

### Z3-140L Staple/Nail Tacker

140/6-14mm 180(18G)/15mm 180/15mm headless

Semi-Professional Code: 0807 Includes: 200pcs 140 staples

|   |   |  |   |  |   |
|---|---|--|---|--|---|
|  140 Staples 6-14mm<br>(Capacity 83) |  180 (18G) Nails 15mm<br>(Capacity 90) |  180/15mm<br>Headless Pin (Capacity 90) |  0.4kg |  Retail<br>Clam |  Trade = 6 Units<br>Transit = 12 Units |
|---|---|--|---|--|---|

Incorporating all of the features of the Z3 metal bodied tool, this model is ultra-light but still robust with its internal steel running gear and external polymer body construction.



### Z3-13L Staple/Nail Tacker

13/6-14mm 180(18G)/15mm 180/15mm headless

Semi-Professional Code: 0881 Includes: 200pcs 13 staples • Whilst stocks last

|   |   |  |   |  |   |
|---|---|--|---|--|---|
|  13 Staples 6-14mm<br>(Capacity 150) |  180 (18G) Nails 15mm<br>(Capacity 90) |  180/15mm<br>Headless Pin (Capacity 90) |  0.4kg |  Retail<br>Clam |  Trade = 6 Units<br>Transit = 12 Units |
|---|---|--|---|--|---|

Driving fine wire staples up to 14mm and nails and pins up to 15mm, this tool is perfect for tasks where leaving a neat/discreet staple head showing is essential.

# Z3 4-in-1 Tackers

## Many fasteners – one tool

Load four staple and nail types quickly and easily thanks to the handy bottom loading system. To switch between different staple and nail sizes, simply use the small lever located at the front of the tool. The power adjuster provides optimum impact and versatility dependent on the workpiece material.

### Z3 4-in-1 Stapler/Nail Tacker

53/8-14mm 180(18G)/15mm CT-60/12-14mm 180/15mm headless

Semi-Professional Code: 1022 Includes: 400pcs staples and nails • Whilst stocks last

|   |   |  |  |   |  |   |
|---|---|--|--|---|--|---|
|  53 Staples 8-14mm<br>(Capacity 150) |  180 (18G) Nails 15mm<br>(Capacity 85) |  CT-60 Staples 12-14mm<br>(Capacity 85) |  180/15mm<br>Headless Pin (Capacity 85) |  0.4kg |  Retail<br>Clam |  Trade = 6 Units<br>Transit = 12 Units |
|---|---|--|--|---|--|---|



Hand Tackers | Cable stapling up to 14mm

# Cable Tackers

## Ideal for:

Cables up to 6mm diameter  
Lightweight CT-60, Z3-CT60 and Combi



Satellite coaxial screened



Coaxial air spaced 1mm brown



2 core electric cable, in low voltage applications



Cat 5e/data cable



Cat 6 cable



Coaxial air spaced 1mm white

Cables up to 4.5mm diameter  
Lightweight CT-45, Z3-CT45 and Combi



Telephone 6 pair 0.5mm



Alarm to BS4773



Alarm 4 core

## Lightweight polymer

Ideal for high level cabling installation and for the mobile user where the reduced weight will take the strain out of larger fixing tasks.

### CT-45 Cable Tacker CT-45/8-10mm

Professional

Code: 0320

• Whilst stocks last



CT-45 Staples 8-10mm  
(Capacity 72)



0.4kg



Retail  
Clam



Trade = 6 Units  
Transit = 12 Units

### CT-60 Cable Tacker CT-60/10-14mm

Professional

Code: 0321



CT-60 Staples 10-14mm  
(Capacity 75)



0.4kg



Retail  
Clam



Trade = 6 Units  
Transit = 12 Units

## Metal combi 2-in-1



Watch the Combi Tacker video

Unique all-metal cable tacker driving both CT-45 and CT-60 staples through the same tool without the need for any adjustment.

### Combi Cable Tacker CT-45/8-10mm CT-60/10-14mm

Professional

Code: 1153



CT-45 Staples 8-10mm  
(Capacity 85)



0.84kg



Retail  
Clam



Trade = 6 Units  
Transit = 12 Units



CT-60 Staples 10-14mm  
(Capacity 82)



## Metal – fully featured

This professional die-cast metal-bodied tool has an ergonomic grip, low grasp height for optimum handling comfort and is ideal for fixing cables into place on wooden surfaces such as skirting boards.

### Z3-CT45 Metal Cable Tacker CT-45/8-10mm

Professional

Code: 0809



CT-45 Staples 8-10mm  
(Capacity 75)



0.9kg



Retail  
Clam



Trade = 6 Units  
Transit = 12 Units



### 45° Angled Nose

Ideal for fixing cables neatly and securely into tight corners. Perfect for low voltage telecommunications and security cabling. Plus a wide range of electrical related installations.

Hand Tackers | Stapling up to 12mm

# Hammer Tackers

For high volume fixing tasks

Built without compromise, our hammer tackers are designed to offer the very best in speed and performance. The perfect solution to many fixing tasks, from roofing to flooring. Tacwise all-metal hammer tackers, with perfect grip, continue to meet the needs of a diverse range of trades.

## A19

**A19 (53 & 13 Type) Hammer Tacker** 53/6-10mm 13/6-10mm

Professional Code: 1327



This compact model takes both the popular 53 and 13 series staples from 6mm to 10mm without the need for any adjustment. A fast and easy way to deal with tasks where many staples are fired in a short time such as securing plastic sheeting. 53 series staples are now available in stainless steel for exterior applications.



## A11

**A11 (140 Type) Hammer Tacker** 140/6-10mm

Professional Code: 0322



Robust hammer tacker firing 140 series staples, available in galvanised or stainless steel – making it ideal for exterior applications.



Surface Protection Plate



Tough Construction



Ergonomic Handle Grip



# A54

**A54 (140 Type) Hammer Tacker** 140/6-12mm

Professional

Code: 1173



140 Staples 6-12mm  
(Capacity 175)



0.9kg



Retail  
Clam



Trade = 6 Units  
Transit = 18 Units

Ideal for securing roofing felt with 140/12mm stainless steel staples. The surface protection plate also enables this tool to rapidly secure sheeting and breather membrane without tearing it.

# Hammer Tackers/Staple Remover | Stapling up to 12mm

## Hammer Tacker Bundles

### Great value bundles

Tough all-metal hammer tackers designed to offer the best in speed and performance for many high volume fixing tasks. Supplied with a choice of Tacwise fastenings in various leg lengths and pack sizes. Suitable for a range of fixing jobs including securing flooring underlay, roofing felt, sheeting, breather membrane and many more.

#### A54 (140 Type) Hammer Tacker Bundle 140/6-12mm **NEW**

**Professional** Code: 1262 Includes: A54 hammer tacker, 2000pcs 140/12mm stainless steel staples



Built to withstand constant daily use and supplied with 2000pcs 140/12mm stainless steel staples, ideal for securing roofing felt.



#### A54 (140 Type) Hammer Tacker Bundle 140/6-12mm **NEW**

**Professional** Code: 1221 Includes: A54 hammer tacker, 5000pcs 140/10mm stainless steel staples



The surface protection plate enables this tool to rapidly secure sheeting and breather membrane without tearing it. Supplied with 5000 stainless steel staples.



#### A11 (140 Type) Hammer Tacker Bundle 140/6-10mm **NEW**

**Professional** Code: 1185 Includes: A11 hammer tacker, 15 x 5000pcs 140/10mm staples



Robust hammer tacker firing 140 series staples. Offering exceptional value and supplied with 75,000 staples, great for fitting underlay and construction membrane.



#### A11 (140 Type) Hammer Tacker Bundle 140/6-10mm **NEW**

**Professional** Code: 1179 Includes: A11 hammer tacker, 15 x 5000pcs 140/8mm staples




Robust hammer tacker firing 140 series staples. Offering exceptional value and supplied with 75,000 staples, ideal for carpet fitters and floor layers.



# Staple Remover

## Ideal for wood

The Tacwise staple remover is ideal for lifting out a variety of staples from timber. It grips and retains staples whilst removing them. The ergonomic handle grip provides comfort during extended periods of use. Designed to safely and securely remove fastenings from a range of materials, our staple remover is the ideal addition to every tool kit.



Ergonomic grip



All-metal working parts



Vice grip mechanism

### Pro Staple Remover

Professional

Code: 0206



Hanging  
Retail Box



Trade = 12 Units  
Transit = 48 Units

The Pro Staple Remover grips and retains staples whilst removing them. Perfect for lifting out many types of staples from panelling, insulation & lining, upholstery, carpet underlay and many more. Plus with built-in Germ-Savvy® antibacterial protection in the handle; tested to – ISO 22196:2011.



### Features

|                      |             |  | Air vents | All metal construction | Belt hook | Bottom loading magazine | Extended cutaway nose | Removable battery 12V | Full length cable guide | Impact power adjuster | Impact resistant metal body | LED work light | Lock-down handle | Lock-down switch | Long power cord | Margin edge adjuster | On/off switch | Personalisation window | Pull-out handle lock | Recessed cutaway nose | Removable margin edge adjuster | Safety contact nose | Staple/nail viewing window | Takes 53 & 13 staples | Tough polymer lightweight body | Trigger lock mechanism | USB rechargeable battery 4V | Wide ergonomic grip |  |
|----------------------|-------------|--|-----------|------------------------|-----------|-------------------------|-----------------------|-----------------------|-------------------------|-----------------------|-----------------------------|----------------|------------------|------------------|-----------------|----------------------|---------------|------------------------|----------------------|-----------------------|--------------------------------|---------------------|----------------------------|-----------------------|--------------------------------|------------------------|-----------------------------|---------------------|--|
| <b>13 Series</b>     |             |  |           |                        |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            |                       |                                |                        |                             |                     |  |
| Code                 | Description |  |           |                        |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            |                       |                                |                        |                             |                     |  |
| Z2 53-13M            | 1218        | Compact, metal and tough               | •         | •                      | •         |                         |                       |                       |                         | •                     | •                           |                |                  |                  | •               | •                    |               |                        |                      |                       |                                |                     | •                          | •                     |                                |                        |                             |                     |  |
| Z2-M Kit             | 1219        | Lightweight aluminium                  | •         |                        | •         |                         |                       |                       |                         | •                     |                             | •              |                  |                  | •               | •                    |               |                        |                      |                       |                                |                     | •                          | •                     |                                |                        |                             |                     |  |
| Z2 53-13L            | 1727        | Durable, compact and lightweight       |           |                        | •         | •                       |                       |                       |                         |                       |                             |                | •                |                  |                 |                      |               | •                      |                      |                       |                                |                     | •                          | •                     | •                              |                        |                             |                     |  |
| Z2 53-13T            | 1728        | Stylish, compact and lightweight       |           |                        | •         | •                       |                       |                       |                         |                       |                             |                | •                |                  |                 |                      |               | •                      |                      |                       |                                |                     | •                          | •                     | •                              |                        |                             |                     |  |
| Z3-13L               | 0881        | Lightweight, semi-professional         |           |                        | •         | •                       |                       |                       |                         | •                     |                             |                |                  | •                |                 |                      |               | •                      | •                    |                       |                                |                     | •                          |                       | •                              |                        | •                           |                     |  |
| Z3-13                | 0880        | Heavyweight professional choice        |           |                        | •         | •                       |                       |                       |                         | •                     | •                           |                |                  | •                |                 |                      |               | •                      | •                    |                       |                                |                     | •                          |                       |                                |                        | •                           |                     |  |
| A19 – Hammer         | 1327        | Takes 53 and 13 type staples           |           | •                      |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            | •                     |                                |                        | •                           |                     |  |
| Hobby 53-13EL – 4V   | 1563/1564   | Rechargeable via USB                   |           |                        | •         | •                       |                       |                       |                         |                       |                             | •              |                  |                  |                 |                      | •             |                        |                      |                       |                                | •                   |                            | •                     |                                |                        | •                           |                     |  |
| 53-13EL – 12V        | 1565/1632   | Removable, rechargeable battery        |           |                        | •         | •                       | •                     |                       |                         |                       |                             | •              |                  |                  |                 | •                    |               |                        |                      |                       |                                | •                   |                            | •                     |                                |                        | •                           |                     |  |
| Hobby 53 and 13EL    | 1702        | Compact corded electric                | •         |                        | •         |                         |                       |                       |                         |                       |                             | •              |                  |                  | •               |                      | •             |                        |                      |                       |                                | •                   | •                          | •                     | •                              | •                      | •                           |                     |  |
| <b>140 Series</b>    |             |  |           |                        |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            |                       |                                |                        |                             |                     |  |
| Z1-140               | 0854        | Compact, metal and tough               |           |                        | •         | •                       |                       |                       |                         | •                     |                             |                | •                |                  |                 |                      | •             | •                      |                      |                       |                                | •                   |                            |                       |                                |                        | •                           |                     |  |
| Z3-140L              | 0807        | Lightweight, semi-professional         |           |                        | •         | •                       |                       |                       |                         | •                     |                             |                |                  | •                |                 |                      |               | •                      | •                    |                       |                                | •                   |                            | •                     |                                |                        | •                           |                     |  |
| Z3-140               | 0806        | Heavyweight professional choice        |           |                        | •         | •                       |                       |                       |                         | •                     | •                           |                |                  | •                |                 |                      |               | •                      | •                    |                       |                                | •                   |                            |                       |                                |                        | •                           |                     |  |
| A11 – Hammer         | 0322        | Traditional hammer tacker              |           | •                      |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            |                       |                                |                        | •                           |                     |  |
| A54 – Hammer         | 1173        | Heavyweight hammer tacker              |           | •                      |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            |                       |                                |                        | •                           |                     |  |
| 140-180EL – 12V      | 1586/1603   | Removable, rechargeable battery        |           |                        | •         | •                       | •                     |                       |                         |                       |                             | •              |                  |                  |                 | •                    |               |                        |                      |                       |                                | •                   |                            |                       |                                |                        | •                           |                     |  |
| 140EL                | 0274/0928   | Compact corded electric                | •         |                        | •         | •                       |                       |                       |                         |                       |                             |                |                  | •                |                 | •                    | •             |                        |                      |                       |                                | •                   |                            | •                     |                                |                        | •                           |                     |  |
| 140EL Pro            | 1703        | Compact corded electric                | •         |                        | •         |                         |                       |                       |                         |                       |                             | •              |                  | •                |                 | •                    |               |                        |                      |                       |                                | •                   | •                          | •                     | •                              | •                      | •                           |                     |  |
| A14014V – Air        | A14014V     | Compact air powered                    |           |                        |           | •                       |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            |                       |                                | •                      | •                           |                     |  |
| <b>53 Series</b>     |             |  |           |                        |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            |                       |                                |                        |                             |                     |  |
| Z1-53 Kit            | 0856/0889   | Compact, metal and tough               |           |                        | •         | •                       |                       |                       |                         | •                     |                             | •              |                  |                  |                 | •                    | •             |                        |                      |                       | •                              | •                   |                            |                       |                                |                        | •                           |                     |  |
| Z2 53-13M            | 1218        | Compact, metal and tough               | •         | •                      | •         |                         |                       |                       |                         | •                     | •                           |                |                  |                  | •               | •                    |               |                        |                      |                       |                                |                     | •                          | •                     |                                |                        |                             |                     |  |
| Z2-M Kit             | 1219        | Lightweight aluminium                  | •         |                        | •         |                         |                       |                       |                         | •                     |                             | •              |                  |                  | •               | •                    |               |                        |                      |                       |                                |                     | •                          | •                     |                                |                        |                             |                     |  |
| Z2 53-13L            | 1727        | Durable, compact and lightweight       |           |                        | •         | •                       |                       |                       |                         |                       |                             |                | •                |                  |                 |                      |               | •                      |                      |                       |                                |                     | •                          | •                     | •                              |                        |                             |                     |  |
| Z2 53-13T            | 1728        | Stylish, compact and lightweight       |           |                        | •         | •                       |                       |                       |                         |                       |                             |                | •                |                  |                 |                      |               | •                      |                      |                       |                                |                     | •                          | •                     | •                              |                        |                             |                     |  |
| Z3-53                | 0808        | Heavyweight professional choice        |           |                        | •         | •                       |                       |                       |                         | •                     | •                           |                |                  | •                |                 |                      |               | •                      | •                    |                       |                                |                     | •                          |                       |                                |                        | •                           |                     |  |
| Z3 4-in-1            | 1022        | Lightweight firing 4 fastening types   |           |                        | •         | •                       | •                     | •                     |                         |                       |                             |                |                  |                  |                 |                      |               |                        | •                    |                       |                                |                     | •                          | •                     |                                |                        | •                           |                     |  |
| A19 – Hammer         | 1327        | Taking both 53 and 13 type staples     |           | •                      |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            | •                     |                                |                        | •                           |                     |  |
| Hobby 53-13EL – 4V   | 1563/1564   | Rechargeable via USB                   |           |                        | •         | •                       |                       |                       |                         |                       |                             | •              |                  |                  |                 |                      | •             |                        |                      |                       |                                | •                   |                            | •                     |                                |                        | •                           |                     |  |
| 53-13EL – 12V        | 1565/1632   | Removable, rechargeable battery        |           |                        | •         | •                       | •                     |                       |                         |                       |                             | •              |                  |                  |                 | •                    |               |                        |                      |                       |                                | •                   |                            | •                     |                                |                        | •                           |                     |  |
| Hobby 53EL Kit       | 1038        | Compact corded electric                | •         |                        | •         | •                       |                       |                       |                         |                       |                             |                |                  | •                |                 | •                    | •             |                        |                      |                       |                                | •                   |                            | •                     |                                |                        | •                           |                     |  |
| Hobby 53 and 13EL    | 1702        | Compact corded electric                | •         |                        | •         |                         |                       |                       |                         |                       |                             | •              |                  | •                |                 | •                    |               |                        |                      |                       |                                | •                   | •                          | •                     | •                              | •                      | •                           |                     |  |
| <b>Cable Tackers</b> |             |  |           |                        |           |                         |                       |                       |                         |                       |                             |                |                  |                  |                 |                      |               |                        |                      |                       |                                |                     |                            |                       |                                |                        |                             |                     |  |
| CT-45                | 0320        | Lightweight. High level installation   |           |                        | •         | •                       | •                     | •                     |                         |                       |                             |                |                  |                  |                 |                      |               |                        | •                    |                       |                                |                     | •                          |                       | •                              |                        | •                           |                     |  |
| CT-60                | 0321        | Lightweight. High level installation   |           |                        | •         | •                       | •                     | •                     |                         |                       |                             |                |                  |                  |                 |                      |               |                        | •                    |                       |                                |                     | •                          |                       | •                              |                        | •                           |                     |  |
| Z3 CT-45             | 0809        | Heavyweight professional choice        |           |                        | •         | •                       | •                     | •                     | •                       |                       |                             |                | •                |                  |                 |                      |               | •                      |                      |                       |                                |                     | •                          |                       |                                |                        | •                           |                     |  |
| Combi                | 1153        | All-metal. Takes CT-45 & CT-60 staples | •         |                        | •         |                         |                       | •                     | •                       |                       |                             |                |                  |                  |                 |                      |               |                        | •                    | •                     |                                |                     |                            |                       |                                |                        |                             |                     |  |



# Applications

|                      |           | Alarm/data cable | Blinds & awnings | Building membranes | Carpeting & underlay | Damp proof coursing | Display/shop fitting | Exhibition/shows | Fabrics & blinds | Heavy textiles (leather, canvas) | Hobby crafts | Insulation (Roll) | Light carpentry | Masonite | Moulding & beading | Netting/wire fencing | Picture framing | Posters/displays | Plastic sheeting | Roofing | Schools/education | Tarpaulin | Telecommunications | Theatre/film scenery | Thinner boards | Trellis/garden | Underfloor heating | Upholstery | Weather strips | Window dressing |
|----------------------|-----------|------------------|------------------|--------------------|----------------------|---------------------|----------------------|------------------|------------------|----------------------------------|--------------|-------------------|-----------------|----------|--------------------|----------------------|-----------------|------------------|------------------|---------|-------------------|-----------|--------------------|----------------------|----------------|----------------|--------------------|------------|----------------|-----------------|
| <b>13 Series</b>     |           | <b>Code</b>      |                  |                    |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      |                 |                  |                  |         |                   |           |                    |                      |                |                |                    |            |                |                 |
| Z2 53-13M            | 1218      |                  |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            |                   |                 |          |                    | •                    | •               | •                |                  |         | •                 |           |                    | •                    | •              | •              |                    |            |                |                 |
| Z2-M Kit             | 1219      |                  |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            |                   |                 |          |                    | •                    | •               | •                |                  |         | •                 |           |                    | •                    | •              | •              |                    |            |                |                 |
| Z2 53-13L            | 1727      |                  |                  |                    |                      |                     |                      | •                |                  | •                                |              |                   |                 |          |                    |                      | •               | •                |                  |         |                   | •         |                    |                      | •              | •              |                    |            |                |                 |
| Z2 53-13T            | 1728      |                  |                  |                    |                      |                     |                      | •                |                  | •                                |              |                   |                 |          |                    |                      | •               | •                |                  |         |                   | •         |                    |                      | •              | •              |                    |            |                |                 |
| Z3-13L               | 0881      |                  |                  |                    |                      | •                   | •                    | •                |                  |                                  |              | •                 |                 |          | •                  |                      | •               | •                |                  |         |                   | •         |                    |                      | •              | •              |                    | •          | •              | •               |
| Z3-13                | 0880      |                  |                  |                    |                      | •                   | •                    | •                |                  |                                  |              | •                 |                 |          | •                  |                      | •               | •                |                  |         |                   | •         |                    |                      | •              | •              |                    | •          | •              | •               |
| A19 – Hammer         | 1327      | •                |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            |                   |                 |          |                    |                      |                 | •                | •                |         |                   | •         |                    |                      | •              | •              |                    |            |                | •               |
| Hobby 53-13EL – 4V   | 1563/1564 | •                |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            | •                 |                 |          | •                  |                      | •               | •                |                  |         |                   | •         |                    |                      | •              | •              |                    | •          | •              | •               |
| 53-13EL – 12V        | 1565/1632 | •                |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            | •                 |                 |          | •                  |                      | •               | •                |                  |         |                   |           |                    | •                    | •              |                | •                  | •          | •              | •               |
| Hobby 53 and 13EL    | 1702      | •                |                  |                    |                      | •                   | •                    | •                | •                | •                                | •            | •                 |                 |          |                    |                      | •               | •                |                  |         |                   |           |                    | •                    | •              |                | •                  | •          | •              | •               |
| <b>140 Series</b>    |           |                  |                  |                    |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      |                 |                  |                  |         |                   |           |                    |                      |                |                |                    |            |                |                 |
| Z1-140               | 0854      |                  |                  |                    | •                    | •                   | •                    | •                | •                |                                  | •            |                   |                 |          |                    | •                    | •               | •                | •                | •       |                   |           |                    |                      | •              | •              | •                  | •          |                |                 |
| Z3-140L              | 0807      | •                | •                | •                  | •                    | •                   | •                    | •                |                  | •                                |              | •                 | •               | •        | •                  | •                    | •               | •                | •                | •       |                   | •         |                    |                      | •              | •              | •                  | •          |                |                 |
| Z3-140               | 0806      | •                | •                | •                  | •                    | •                   | •                    | •                |                  | •                                |              | •                 | •               | •        | •                  | •                    | •               | •                | •                | •       |                   | •         |                    |                      | •              | •              | •                  | •          |                |                 |
| A11 – Hammer         | 0322      |                  |                  | •                  |                      |                     | •                    |                  |                  |                                  | •            |                   |                 |          |                    | •                    |                 |                  | •                |         |                   |           |                    |                      |                |                |                    |            |                |                 |
| A54 – Hammer         | 1173      |                  |                  | •                  |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      |                 |                  |                  |         |                   |           |                    |                      |                |                |                    |            |                |                 |
| 140-180EL – 12V      | 1586/1603 | •                | •                | •                  | •                    | •                   | •                    | •                |                  | •                                |              | •                 | •               | •        | •                  | •                    | •               | •                | •                | •       |                   | •         |                    |                      | •              | •              | •                  | •          |                |                 |
| 140EL                | 0274      | •                | •                | •                  | •                    | •                   | •                    | •                |                  | •                                |              | •                 | •               | •        | •                  | •                    | •               | •                | •                | •       |                   | •         |                    |                      |                |                | •                  |            |                |                 |
| 140EL Pro            | 1703      | •                | •                | •                  | •                    | •                   | •                    | •                |                  | •                                |              | •                 | •               | •        | •                  | •                    | •               | •                | •                | •       |                   | •         |                    |                      |                |                | •                  |            |                |                 |
| A14014V – Air        | A14014V   | •                | •                | •                  | •                    | •                   | •                    | •                |                  | •                                |              | •                 | •               | •        | •                  | •                    | •               | •                | •                | •       |                   | •         |                    |                      |                |                | •                  |            |                |                 |
| <b>53 Series</b>     |           |                  |                  |                    |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      |                 |                  |                  |         |                   |           |                    |                      |                |                |                    |            |                |                 |
| Z1-53 Kit            | 0856/0889 |                  |                  |                    |                      |                     |                      | •                |                  | •                                |              |                   |                 |          |                    |                      | •               | •                |                  |         |                   | •         |                    |                      | •              | •              |                    |            |                |                 |
| Z2 53-13M            | 1218      |                  |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            |                   |                 |          |                    | •                    | •               | •                |                  |         |                   | •         |                    |                      | •              | •              | •                  |            |                |                 |
| Z2-M Kit             | 1219      |                  |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            |                   |                 |          |                    | •                    | •               | •                |                  |         |                   | •         |                    |                      | •              | •              | •                  |            |                |                 |
| Z2 53-13L            | 1727      |                  |                  |                    |                      |                     |                      | •                |                  | •                                |              |                   |                 |          |                    |                      | •               | •                |                  |         |                   |           | •                  |                      |                | •              | •                  |            |                |                 |
| Z2 53-13T            | 1728      |                  |                  |                    |                      |                     |                      | •                |                  | •                                |              |                   |                 |          |                    |                      | •               | •                |                  |         |                   |           | •                  |                      |                | •              | •                  |            |                |                 |
| Z3-53                | 0808      |                  |                  |                    |                      |                     |                      | •                | •                | •                                |              | •                 |                 |          | •                  |                      | •               | •                |                  |         |                   |           | •                  |                      |                | •              | •                  | •          |                |                 |
| Z3 4-in-1            | 1022      | •                | •                | •                  |                      | •                   |                      | •                | •                | •                                | •            | •                 |                 |          |                    | •                    |                 |                  | •                |         |                   |           |                    |                      | •              |                |                    | •          |                |                 |
| A19 – Hammer         | 1327      | •                |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            |                   |                 |          |                    |                      |                 | •                | •                |         |                   | •         |                    |                      | •              | •              |                    |            |                | •               |
| Hobby 53-13EL – 4V   | 1563/1564 | •                |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            | •                 |                 |          | •                  |                      | •               | •                |                  |         |                   | •         |                    |                      | •              | •              |                    | •          | •              | •               |
| 53-13EL – 12V        | 1565/1632 | •                |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            | •                 |                 |          | •                  |                      | •               | •                |                  |         |                   |           |                    | •                    | •              |                | •                  | •          | •              | •               |
| Hobby 53EL Kit       | 1038      | •                |                  |                    |                      | •                   | •                    | •                |                  | •                                | •            | •                 |                 |          |                    |                      | •               | •                |                  |         |                   |           |                    | •                    | •              |                | •                  | •          | •              | •               |
| Hobby 53 and 13EL    | 1702      | •                |                  |                    |                      | •                   | •                    | •                | •                | •                                | •            | •                 |                 |          |                    |                      | •               | •                |                  |         |                   |           |                    | •                    | •              |                | •                  | •          | •              | •               |
| <b>Cable Tackers</b> |           |                  |                  |                    |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      |                 |                  |                  |         |                   |           |                    |                      |                |                |                    |            |                |                 |
| CT-45                | 0320      | •                |                  |                    |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      | •               |                  |                  |         |                   |           |                    | •                    |                |                |                    |            |                |                 |
| CT-60                | 0321      | •                |                  |                    |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      | •               |                  |                  |         |                   |           |                    | •                    |                |                |                    |            |                |                 |
| Z3 CT-45             | 0809      | •                |                  |                    |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      |                 |                  |                  |         |                   |           |                    | •                    |                |                |                    |            |                |                 |
| Combi                | 1153      | •                |                  |                    |                      |                     |                      |                  |                  |                                  |              |                   |                 |          |                    |                      | •               |                  |                  |         |                   |           |                    | •                    |                |                |                    |            |                |                 |

### Specifications

|                      |           |  | Approx. Charge Time/Shots<br>Per Charge (4 & 12V) | Dimensions in mm<br>(H x W x D) |                |
|----------------------|-----------|--|---|---------------------------------|----------------|
| 13 Series            | Code      | Description/Overview                     | Time (hr)   | Shots                           |                |
| Z2 53-13M            | 1218      | Compact, metal and tough                 | –   | –                               | 85 x 165 x 39  |
| Z2-M Kit             | 1219      | Lightweight aluminium                    | –   | –                               | 85 x 158 x 28  |
| Z2 53-13L            | 1727      | Durable, compact and lightweight         | –   | –                               | 85 x 165 x 39  |
| Z2 53-13T            | 1728      | Stylish, compact and lightweight         | –   | –                               | 85 x 165 x 39  |
| Z3-13L               | 0881      | Lightweight, semi-professional           | –   | –                               | 121 x 193 x 33 |
| Z3-13                | 0880      | Heavyweight professional choice          | –   | –                               | 121 x 193 x 33 |
| A19 – Hammer         | 1327      | Takes 53 and 13 type staples             | –   | –                               | 45 x 278 x 32  |
| Hobby 53-13EL – 4V   | 1563/1564 | Rechargeable via USB                     | 1.5   | 850 – 1000                      | 147 x 47 x 150 |
| 53-13EL – 12V        | 1565/1632 | Removable, rechargeable battery          | 3 – 5   | 3000 – 4000                     | 150 x 50 x 180 |
| Hobby 53 and 13EL    | 1702      | Compact corded electric                  | –   | –                               | 161 x 188 x 54 |
| <b>140 Series</b>    |           |  |   |                                 |                |
| Z1-140               | 0854      | Compact, metal and tough                 | –   | –                               | 95 x 160 x 27  |
| Z3-140L              | 0807      | Lightweight, semi-professional           | –   | –                               | 121 x 193 x 33 |
| Z3-140               | 0806      | Heavyweight professional choice          | –   | –                               | 121 x 193 x 33 |
| A11 – Hammer         | 0322      | Traditional hammer tacker                | –   | –                               | 55 x 308 x 42  |
| A54 – Hammer         | 1173      | Heavyweight hammer tacker                | –   | –                               | 78 x 308 x 35  |
| 140-180EL – 12V      | 1586/1603 | Removable, rechargeable battery          | 3 – 5   | 3000 – 4000                     | 150 x 50 x 180 |
| 140EL                | 0274      | Compact corded electric                  | –   | –                               | 135 x 195 x 55 |
| 140EL Pro            | 1703      | Compact corded electric                  | –   | –                               | 160 x 188 x 54 |
| A14014V – Air        | A14014V   | Compact air powered                      | –   | –                               | 235 x 46 x 159 |
| <b>53 Series</b>     |           |  |   |                                 |                |
| Z1-53 Kit            | 0856/0889 | Compact, metal and tough                 | –   | –                               | 95 x 160 x 27  |
| Z2 53-13M            | 1218      | Compact, metal and tough                 | –   | –                               | 85 x 158 x 28  |
| Z2-M Kit             | 1219      | Lightweight aluminium                    | –   | –                               | 85 x 158 x 28  |
| Z2 53-13L            | 1727      | Durable, compact and lightweight         | –   | –                               | 85 x 165 x 39  |
| Z2 53-13T            | 1728      | Stylish, compact and lightweight         | –   | –                               | 85 x 165 x 39  |
| Z3-53                | 0808      | Heavyweight professional choice          | –   | –                               | 121 x 193 x 33 |
| Z3 4-in-1            | 1022      | Lightweight firing 4 fastening types     | –   | –                               | 123 x 182 x 33 |
| A19 – Hammer         | 1327      | Taking both 53 and 13 type staples       | –   | –                               | 45 x 278 x 32  |
| Hobby 53-13EL – 4V   | 1563/1564 | Rechargeable via USB                     | 1.5   | 850 – 1000                      | 147 x 47 x 150 |
| 53-13EL – 12V        | 1565/1632 | Removable, rechargeable battery          | 3 – 5   | 3000 – 4000                     | 150 x 50 x 180 |
| Hobby 53EL Kit       | 1038      | Compact corded electric                  | –   | –                               | 135 x 195 x 55 |
| Hobby 53 and 13EL    | 1702      | Compact corded electric                  | –   | –                               | 161 x 188 x 54 |
| <b>Cable Tackers</b> |           |  |   |                                 |                |
| CT-45                | 0320      | Lightweight. High level installation     | –   | –                               | 120 x 185 x 30 |
| CT-60                | 0321      | Lightweight. High level installation     | –   | –                               | 120 x 185 x 30 |
| Z3 CT-45             | 0809      | Heavyweight professional choice          | –   | –                               | 121 x 193 x 33 |
| Combi                | 1153      | All-metal. Takes CT-45 and CT-60 staples | –   | –                               | 114 x 188 x 25 |

| Weight (kg) | Magazine Capacity |                       | Fastener Type/Length     | Minimum Firing Distance From Wall |      |
|-------------|-------------------|-----------------------|--------------------------|-----------------------------------|------|
|             | Nails             | Staples               |                          |                                   |      |
| 0.3         | –                 | 105 (53) 110 (13)     | –                        | 53/4-8mm & 13/4-8mm               | 8mm  |
| 0.3         | –                 | 102 (53) 110 (13)     | –                        | 53/4-8mm & 13/4-8mm               | 8mm  |
| 0.2         | –                 | 105 (53) 110 (13)     | –                        | 53/4-8mm & 13/4-8mm               | 9mm  |
| 0.2         | –                 | 105 (53) 110 (13)     | –                        | 53/4-8mm & 13/4-8mm               | 9mm  |
| 0.4         | 90                | 150                   | 180/15mm & Headless/15mm | 13/6-14mm                         | 5mm  |
| 0.9         | 90                | 150                   | 180/15mm & Headless/15mm | 13/4-14mm                         | 5mm  |
| 0.4         | –                 | 120                   | –                        | 53/6-10mm & 13/6-10mm             | –    |
| 0.6         | 50                | 100                   | 180/10mm                 | 53/6-12mm & 13/6-12mm             | 15mm |
| 0.9         | 85                | 140                   | 180/10mm                 | 53/6-12mm & 13/6-12mm             | 15mm |
| 0.8         | 85                | 145 (53) 150 (13)     | 180(18G)/10-14mm         | 53/8-14mm & 13/8-14mm             | 15mm |
|             |                   |                       |                          |                                   |      |
| 0.3         | –                 | 83                    | –                        | 140/6-8mm                         | 5mm  |
| 0.4         | 90                | 83                    | 180/15mm & Headless/15mm | 140/6-14mm                        | 5mm  |
| 0.9         | 90                | 83                    | 180/15mm & Headless/15mm | 140/4-14mm                        | 5mm  |
| 0.9         | –                 | 150                   | –                        | 140/6-10mm                        | –    |
| 0.9         | –                 | 175                   | –                        | 140/6-12mm                        | –    |
| 0.9         | 85                | 84                    | 180/10mm                 | 140/6-12mm                        | 15mm |
| 0.8         | 90                | 83                    | 180/15mm                 | 140/6-14mm                        | 6mm  |
| 0.8         | 85                | 85                    | 180(18G)/10-14mm         | 140/8-14mm                        | 15mm |
| 0.9         | –                 | 150                   | –                        | 140/4-14mm                        | 16mm |
|             |                   |                       |                          |                                   |      |
| 0.3         | –                 | 125                   | –                        | 53/4-8mm                          | 5mm  |
| 0.3         | –                 | 102 (53) 110 (13)     | –                        | 53/4-8mm & 13/4-8mm               | 8mm  |
| 0.3         | –                 | 102 (53) 110 (13)     | –                        | 53/4-8mm & 13/4-8mm               | 8mm  |
| 0.2         | –                 | 105 (53) 110 (13)     | –                        | 53/4-8mm & 13/4-8mm               | 9mm  |
| 0.2         | –                 | 105 (53) 110 (13)     | –                        | 53/4-8mm & 13/4-8mm               | 9mm  |
| 0.9         | 90                | 125                   | 180/15mm & Headless/15mm | 53/4-14mm                         | 5mm  |
| 0.4         | 85                | 150 (53) 85 (CT-60)   | 180/15mm & Headless/15mm | 53/8-14mm & CT-60/12-14mm         | 5mm  |
| 0.4         | –                 | 120                   | –                        | 53/6-10mm & 13/6-10mm             | –    |
| 0.6         | 50                | 100                   | 180/10mm                 | 53/6-12mm & 13/6-12mm             | 15mm |
| 0.9         | 85                | 140                   | 180/10mm                 | 53/6-12mm & 13/6-12mm             | 15mm |
| 0.8         | 90                | 125                   | 180/15mm                 | 53/6-14mm                         | 6mm  |
| 0.8         | 85                | 145 (53) 150 (13)     | 180(18G)/10-14mm         | 53/8-14mm & 13/8-14mm             | 15mm |
|             |                   |                       |                          |                                   |      |
| 0.4         | –                 | 75                    | –                        | CT-45/8-10mm                      | 5mm  |
| 0.4         | –                 | 75                    | –                        | CT-60/10-14mm                     | 5mm  |
| 0.9         | –                 | 75                    | –                        | CT-45/8-10mm                      | 5mm  |
| 0.8         | –                 | 85 (CT-45) 82 (CT-60) | –                        | CT-45/8-10 & CT-60/10-14mm        | 5mm  |

# Rapesco® Stapling Pliers | Stapling up to 12mm



## RAPESCO® Porpoise ONE

24/8mm

**NEW**



Professional

Code: 1626

Includes: Storage bag, 1000pcs 24 staples

24 Staples 8mm  
(Capacity 150)

45  
Sheets

Bypass  
Staple

Pin

57mm

0.63kg

Plain  
Box

Trade = 6 Units  
Transit = 24 Units

Durable chrome plated, all metal construction. One staple for 2-45 sheets (80gsm paper).  
Adjustable anvil for bypass stapling and pinning. Traditional rear spring loading mechanism.



## RAPESCO®

### Porpoise Classic

24/6-8mm

26/6-8mm

**NEW**

#### Professional

Code: R81000A3



Trade = 10 Units  
Transit = 40 Units

Code: 1298A

Includes: 2 x 5000pcs  
26/8mm staples



Trade = 10 Units  
Transit = 20 Units



26 Staples 6-8mm  
(Capacity 210)

20 Sheets (6mm)  
45 Sheets (8mm)

Staple  
& Pin

59mm

0.37kg

High performance chrome plated, all-metal stapling plier with adjustable anvil for stapling & pinning. Rear spring loading mechanism. Ergonomic design with contoured handle grip.



## RAPESCO®

### Heavy Duty HD-73

73/6-12mm

**NEW**

#### Professional

Code: 1169



Trade = 10 Units  
Transit = 40 Units

Code: 1305

Includes: 2000pcs  
73/10mm staples



Trade = 1 Unit

Code: 1306

Includes: 2000pcs  
73/12mm staples



Trade = 1 Unit

Code: 1213

Includes: 2 x 5000pcs  
73/10mm staples



Trade = 1 Unit

Code: 1199

Includes: 5 x 5000pcs  
73/12mm staples



Trade = 1 Unit



70 Sheets

Staple

65mm

0.48kg

Packaging plier for cardboard and jiffy bags. Chrome plated all-metal with contoured handle grip and rear spring-loading mechanism. Supplied with two anvils: Straight and Sword.



Blunt  
Anvil



Sword  
Anvil

Supplied with interchangeable blunt and pointed anvils.

## Specifications

| Stapling Pliers  | Code                             | Dimensions in mm<br>(H x W x D) | Weight<br>(kg) | Sheet<br>Capacity | Stapling<br>Function | Fastener<br>Type/Length | Throat Depth<br>(mm) |
|------------------|----------------------------------|---------------------------------|----------------|-------------------|----------------------|-------------------------|----------------------|
|                  |                                  |                                 |                |                   |                      |                         |                      |
| Porpoise ONE     | 1626                             | 92 x 22 x 175                   | 0.63           | 45                | Staple & Pin         | 24/8mm                  | 57                   |
| Porpoise Classic | R81000A3 / 1298A                 | 92 x 24 x 175                   | 0.37           | 45                | Staple & Pin         | 24/6-8mm & 26/6-8mm     | 59                   |
| HD-73            | 1169 / 1305 / 1306 / 1213 / 1199 | 98 x 21 x 190                   | 0.48           | 70                | Staple               | 73/6-12mm               | 65                   |

Cordless Nailing & Stapling

Stapling up to 12mm / Nailing up to 10mm



## Cordless 4V

### Lightweight & Convenient

Versatile and lightweight staple & nail guns providing accurate results; the tools in the Tacwise 4V cordless range are rechargeable via USB for convenience. Suitable for a wide range of DIY, hobby and more ambitious tasks at home, in the garden and at school.

# Hobby 53-13EL

Powered by an integrated, rechargeable lithium-ion battery, the Tacwise 4V cordless range delivers precise results without the hassle of cables.



## Hobby 53-13EL Cordless 4V Staple/Nail Gun

53/6-12mm    13/6-12mm    180(18G)/10mm

|              |            |   |
|--------------|------------|---|
| DIY/Semi-Pro | Code: 1564 | Includes: USB charging cable, 2000pcs 53 staples, storage bag |
|              | Code: 1563 | Includes: USB charging cable, 200pcs 53 staples               |

- 53 & 13 Staples 6-12mm (Capacity 100)
- 180 (18G) Nails 10mm (Capacity 50)
- 0.68kg
- LED Work Light
- Storage Bag (1564 only)
- USB Charge Cable
- Hanging Retail Box
- Trade = 1 Units  
Transit = 10 Units

With an on/off LED light for precision and ease-of-use and a bottom loading magazine for switching between staples and nails without any adjustment, these 4V staple/nail guns also feature a safety contact nose, belt hook and staple/nail viewing window. The Hobby 53-13EL comes backed by a 2-year guarantee, but remember to use genuine Tacwise staples and nails as dimensions, tolerances and hardness from other sources are not always to the same Tacwise's exacting standards.

### Storage Bag

Made from the same high quality material as marine dive suits, offering great protection for tools and accessories.




# Cordless Nailing & Stapling

Stapling up to 12mm / Nailing up to 10mm

# Cordless 12V

## For hours of continuous stapling/nailing

Powered by an interchangeable 12V lithium-ion battery, our durable cordless range is ideal for busy trades and enthusiastic DIYers. Both tools in the range include great features such as a work light, safety contact nose and belt hook, as standard. Offering greater power, battery life and user comforts.



### 140-180EL Cordless 12V Staple/Nail Gun 140/6-12mm 180(18G)/10mm

|                          |            |   |
|--------------------------|------------|---|
| <b>Semi-Professional</b> | Code: 1586 | Includes: Battery, UK mains charger, Euro plug adaptor, 200pcs 140 staples, 200pcs 180 nails, storage bag |
|                          | Code: 1603 | Includes: Tool body only  |

**NEW**

- 140 Staples 6-12mm (Capacity 84)
- 180 Nails (18G) 10mm (Capacity 85)
- 0.8kg (Tool Only)
- LED Work Light
- Storage Bag
- UK Charger
- Euro Adaptor
- Hanging Retail Box
- Trade = 1 Units  
Transit = 10 Units

A powerful staple/nail gun firing the heavier 140 gauge staple, preferred by professionals. Which provides excellent holding power on materials such as plastic sheeting and netting. This compact tool delivers consistent results time after time.

### 53-13EL Cordless 12V Staple/Nail Gun 53/6-12mm 13/6-12mm 180(18G)/10mm

|                          |            |   |
|--------------------------|------------|---|
| <b>Semi-Professional</b> | Code: 1565 | Includes: Battery, UK mains charger, Euro plug adaptor, 200pcs 53 staples, 200pcs 13 staples, storage bag |
|                          | Code: 1632 | Includes: Tool body only  |

**NEW**

- 53 & 13 Staples 6-12mm (Capacity 140)
- 180 Nails (18G) 10mm (Capacity 85)
- 0.8kg (Tool Only)
- LED Work Light
- Storage Bag
- UK Charger
- Euro Adaptor
- Hanging Retail Box
- Trade = 1 Units  
Transit = 10 Units

This model offers all the benefits of the 140-180EL tool but fires both 53 and 13 fine wire staples, and a 10mm nail, without any need for adjustment. These finer staples are ideal where a neat/discrete finish is required.







## 12 Volt Li-ion Battery

The fast-charging, interchangeable quick release battery for Tacwise 12V tools uses the most recent lithium-ion technology for the best weight and power delivery.

The mains-supplied DC charger, which works with both UK and Euro plugs, connects directly into the battery, eliminating the need for a charging dock. The battery features an LED charging cycle indicator – red when charging and green when the charge cycle has finished.



Code: 1582

Cordless Nailing & Stapling | Stapling up to 40mm / Nailing up to 50mm

# Cordless 18V

Perfect for a variety of second fix tacks

This 18 volt model boasts a host of user benefits including a direct fast charge system. Ranger EL-PRO carries a powerful slide-on 18-volt battery system.

Tacwise Recoilless Firing Platform




Tacwise Unique Loading System/Magazine


## Versatile


Extremely versatile, firing staples up to 40mm and nails up to 50mm, the Ranger EL-PRO is a heavyweight cordless option. Not to be confused with others on the market, this Tacwise tool enjoys all of the engineering capabilities and know how built from 60 years of experience.


### Ranger EL-PRO 18V Cordless 2-in-1 Staple/Nail Gun 91/19-40mm 180(18G)/20-50mm


|                     |                   |  |
|---------------------|-------------------|--|
| <b>Professional</b> | <b>Code: 1506</b> | Includes: UK mains charger, Euro plug adaptor, hex wrench, 1000pcs 91 staples, 1000pcs 18G nails |
|---------------------|-------------------|--|


- 


91 Staples 19-40mm  
(Capacity 100)  
18G Nails 20-50mm  
(Capacity 100)
- 

3.08kg
- 

LED  
Work Light
- 

UK  
Charger
- 

Euro  
Adaptor
- 

Carry  
Case
- 

Trade = 1 Unit

When firing this tool, even with the longest fastenings, its recoilless action is immediately obvious. Which takes the stress out of simple fixing tasks and becomes a real win, when in continuous use. Heavyweight, well balanced and loaded with great user features as standard... The hallmark of the Tacwise brand.

## Carry Case

The Ranger EL-PRO carry case has been designed to be oversized to conveniently store multiple packs of staples and nails.



Comes with a UK/Euro cable/adaptor.



# Compact Electric Tackers

## Fast, reliable & loaded with features

The new generation of compact electric stapler & nailers, supplied with 5000 staples and 2000 nails. Staple and nail function in one tool with a bottom loading magazine for easy access and simple switching between staples and nails of various leg lengths without any adjustment. Also featuring an LED work light and a long 2m power cord for ease of use.

Designed with safety in mind, these tools have an on/off power switch, trigger lock mechanism and safety contact nose, all of which must be activated for the tool to fire. Both these tools come with an interchangeable plug for UK and Euro power outlets, fitted ready for UK use.

### 140EL Pro 140/8-14mm 180(18G)/10-14mm **NEW**

**Semi-Professional** Code: 1703 Includes: 5000pcs 140 staples & 2000pcs 180 (18G) nails



### Hobby 53 & 13EL 53/8-14mm 13/8-14mm 180(18G)/10-14mm **NEW**

**Semi-Professional** Code: 1702 Includes: 5000pcs 53 staples & 2000pcs 180 (18G) nails





**Interchangeable UK and Euro plug**

The UK plug casing can easily be unscrewed to reveal a Type C Euro 2-Pin plug.



# Compact Electric Tackers

## Small, fast & lightweight

An ideal step-up from manual hand tackers, these compact electric tackers are highly balanced with an ergonomic design that makes repetitive stapling tasks easy and comfortable.


These tackers are designed with minimal parts to enhance reliability and reduce weight. When combined with a sturdy chassis and body materials, the tool delivers optimum performance and durability for repeated fastening.



Personalisation Window

Bottom Loading

Belt Hanger



### DIY/Semi-Pro... 53EL & 140EL

Featuring an all polymer body, these ultra-compact corded tackers boast a host of dynamic and innovative features and are ideal for semi-professional and lightweight applications.

## Hobby 53EL

**Hobby 53EL Tacker Kit** 53/6-14mm 180(18G)/15mm

**Semi-Professional**

Code: 1038

Includes: Staple remover, 4000pcs 53 staples & 2000pcs 180 (18G) nails



53 Staples 6-14mm  
(Capacity 83)  
180 (18G) Nails 15mm  
(Capacity 90)



0.75kg



Retail  
Box



Trade = 1 Unit  
Transit = 10 Units



## 140EL

**140EL** 140/6-14mm 180(18G)/15mm

**Semi-Professional**

Code: 0274

Includes: 1000pcs 140 staples & 1000pcs 180 (18G) nails



140 Staples 6-14mm  
(Capacity 83)  
180 (18G) Nails 15mm  
(Capacity 90)




0.75kg



Retail  
Box



Trade = 1 Unit  
Transit = 10 Units



# 181ELS



## UK's favourite corded nail gun

Suitable for a wide range of second fix and fastening tasks, these electric nailers and staplers achieve great results with minimal effort.

The dedicated nailing version of our top-selling 191EL Pro, the 181ELS is a versatile tool that fires 180 (18G) nails up to 35mm. Feature-rich, the 181ELS is highly practical and lightweight, perfect for repetitive nailing tasks.

### Master Nailer™ 181ELS Pro Electric Nailer 180(18G)/15-35mm

|                          |            |                             |
|--------------------------|------------|-----------------------------|
| <b>Semi-Professional</b> | Code: 1176 | No nails included           |
|                          | Code: 1705 | Includes: 1000pcs 180 nails |
|                          | Code: 1718 | Includes: 5000pcs 180 nails |

**NEW**  
**NEW**

- 180 Nails (18G) 15-35mm (Capacity 100)
- 1.6kg
- Carry Case
- Trade = 1 Unit  
Transit = 4 Units

Extraordinary value for money and a must for every tool bag. Coupling superb performance with user comfort, our Medium Duty electric tackers are extremely fast semi-professional tools capable of firing nails up to 35mm.



# 191EL Pro

## Stapling & nailing

Firing six different lengths of nails and four different lengths of staple. The 191EL Pro is a nailer and stapler that's perfect for a wide range of fixing applications. Versatile, ergonomic and lightweight; the 191EL Pro is perfect for continuous fastening tasks – especially those in difficult to reach areas. Simple, easy to use and the fastest tool of its kind, it's no wonder the 191EL Pro is the UK's favourite nailer/stapler.

### Ultimate Versatility

191EL Pro is a 'must have' for all professional trades tackling any number of second fix tasks as well as precision jobs in the workshop. Hugely popular for flooring including boarding out and soft wood floorboards.







**Master Nailer™ 191EL Pro Electric Nailer/Stapler** 91/15-30mm 180(18G)/15-35mm

**Semi-Professional** Code: 0326 Includes: 500pcs 91 staples & 500pcs 180 (18G) nails

• Whilst stocks last



91 Staples 15-30mm  
(Capacity 100)



1.8kg



Retail  
Box



Trade = 1 Unit  
Transit = 6 Units

180 (18G) Nails 15-35mm  
(Capacity 100)

**Semi-Professional** Code: 0327 Includes: 2000pcs 91 staples & 2000pcs 180 (18G) nails



91 Staples 15-30mm  
(Capacity 100)



1.8kg



Carry  
Case



Trade = 1 Unit  
Transit = 6 Units

180 (18G) Nails 15-35mm  
(Capacity 100)

191EL Pro is the tool everyone should have in their toolbag regardless of which other staple or nail guns they own. The best value, most versatile corded stapler/nailer on the market.

# Duo 35

## Stapling/nailing & loaded with features

A compact tool with tremendous versatility, the Duo 35 combines unrivalled performance with speed and precision. With all-new electronics, enhanced switch-gear and improvements throughout, this nailer and stapler is another great addition to the exciting generation of electric tools from Tacwise.




Watch the Duo 35 video



### Master Nailer™ Duo 35 Electric Nailer/Stapler 91/15-30mm 180(18G)/15-35mm

|                     |                   |
|---------------------|-------------------|
| <b>Professional</b> | Code: 1165        |
|                     | Code: 1167 (EURO) |

- 91 Staples 15-30mm (Capacity 100)
- 180 (18G) Nails 15-35mm (Capacity 100)
- 1.8kg
- Carry Case
- Trade = 1 Unit  
Transit = 4 Units



The Duo 35 is fully loaded with a host of innovative features which include; a flip open nose gate, an all metal professional magazine, a nose safety device, power light and a separate on/off switch.

### Duo 35 Tool Versatility

Perfect for precision as well as demanding fixing jobs. The Duo 35 has been re-designed with the trades in mind, so you can work on flooring, panelling or skirting, architrave and more. The Duo 35 is an essential tool for second fix jobs, compact, durable and affordable.



# Duo 50

## Stapling & nailing

Essential for the trades, these tools will make light work of a range of second fix and 'making good' tasks, including flooring, subflooring and underlay gripper.



Watch the Duo 50 video



### Master Nailer™ Duo 50 Electric Nailer/Stapler 91/20-45mm 180(18G)/20-50mm

**Professional** Code: 1166

- 91 Staples 20-40mm (Capacity 100)
- 180 (18G) Nails 20-50mm (Capacity 100)
- 2.5kg
- Carry Case
- Trade = 1 Unit
- Transit = 4 Units

A high specification tool with an air tool magazine for fast easy loading, a flip open nose gate, a belt hook and a compact nose to get into those hard-to-reach areas.

### Tough Storage/Carry Case

All our heavy duty electric tools come supplied in a sturdy carry case.



Heavy Duty Corded Electrics ■ Nailing up to 50mm

# 400ELS Pro Inclined Nailer

Angled for easy access

Fast and light, this handy angled nailer makes it ideal for tackling fixing tasks where elbow room or access is limited – such as under stairs, behind baths or sanitary ware. Delivering the closest thing to air tool performance in an electric nailer, it fires six lengths of nail up to 40mm, and at speeds of up to 30 nails per minute.

Rifle Butt Style Quick Release



Removeable Wire Stand



Pro Air Tool Magazine/Quick Release Nose Gate



## Master Nailer™ 400ELS Pro Electric Angled Nailer 500/15-40mm

|              |                   |                             |
|--------------|-------------------|-----------------------------|
| Professional | Code: 0733        | No nails included           |
|              | Code: 0876 (Euro) |                             |
|              | Code: 1704        | Includes: 1000pcs 500 nails |

• Whilst stocks last (EURO)

**NEW**



Watch the 400ELS video

## An unrivalled performance

400ELS is a little different from the other Tacwise electrics. The key feature is its angled magazine which makes the tool extremely compact and capable of firing into very tight spaces. It also features a unique, removeable wire stand, which means that the tool is in the upright position 'ready to go' when used in tasks such as securing floor boards and boarding out.



500 (18G) Angled Nails 15-40mm  
(Capacity 100)



1.8kg



Carry Case




Trade = 1 Unit  
Transit = 4 Units

# 18G/50 Nailer

Pro 18G brad nailer

This dedicated nailing tool has a precision air tool construction that will accurately drive 18 gauge brads with little marking to the surface of the timber. Ideal to speed through a wide variety of tasks saving a lot of time and freeing one hand to guide and position the work piece. Also ideal for a temporary fix during glue drying.



Watch the 18G/50 video

## Master Nailer™ 18G/50 Electric Nailer 180(18G)/20-50mm

|                     |            |                             |
|---------------------|------------|-----------------------------|
| <b>Professional</b> | Code: 1183 | No nails included           |
|                     | Code: 1707 | Includes: 1000pcs 180 nails |

**NEW**

-   
 180 (18G) Nails 20-50mm  
 (Capacity 100)
-   
 2.3kg
-   
 Carry Case
-   
 Trade = 1 Unit  
 Transit = 4 Units

Feature rich, this powerful electric nailer boasts a flip open nose gate, a high capacity magazine as well as a useful belt hook. The 18G/50 is capable of firing 18 gauge (type 180) nails from 20 to 50mm in length and delivers precise results on applications including: soft and medium woodwork, flooring and panelling. Features our fast loading system and does not require gas packs or compressors.

### All new magazine

The 18G/50 Nailer has a new style magazine for highly accurate fastening and features two nail viewing windows for user convenience. The rapid release nose gate and simple side loading mechanism are features shared by the new generation of medium and heavy duty Tacwise electrics.



### Features

| Cordless                  | Code           | Description                             | Air vents | Belt hook | Bottom loading magazine | Impact resistant body | LED work light | Long power cord | Metal magazine | Nose protector | Personalisation window | Quick release loading | Quick release nose gate | Rechargeable li-ion battery | Safety contact nose | Safety on/off light | Safety on/off switch | Single shot trigger | Staple/nail viewing window | Trigger safety lock switch | Wide ergonomic grip |
|---------------------------|----------------|---|-----------|-----------|-------------------------|-----------------------|----------------|-----------------|----------------|----------------|------------------------|-----------------------|-------------------------|-----------------------------|---------------------|---------------------|----------------------|---------------------|----------------------------|----------------------------|---------------------|
| Hobby 53-13EL – 4V        | 1563/1564      | Rechargeable via USB                    | •         | •         | •                       | •                     | •              | •               | •              |                |                        |                       |                         | •                           | •                   |                     | •                    | •                   | •                          | •                          | •                   |
| 53-13EL – 12V             | 1565/1632      | Removable, rechargeable battery         | •         | •         | •                       | •                     | •              |                 | •              |                |                        |                       |                         | •                           | •                   |                     | •                    | •                   | •                          |                            | •                   |
| 140-180EL – 12V           | 1586/1603      | Removable, rechargeable battery         | •         | •         | •                       | •                     | •              |                 | •              |                |                        |                       |                         | •                           | •                   |                     | •                    | •                   | •                          |                            | •                   |
| Ranger EL-PRO – 18V       | 1506           | Heavyweight, powerful and versatile     | •         | •         |                         |                       | •              |                 | •              | •              |                        | •                     |                         | •                           | •                   |                     |                      | •                   | •                          |                            | •                   |
| <b>Compact Corded</b>     |                |   |           |           |                         |                       |                |                 |                |                |                        |                       |                         |                             |                     |                     |                      |                     |                            |                            |                     |
| Hobby 53 and 13EL         | 1702           | Compact corded electric                 | •         |           | •                       | •                     | •              | •               | •              |                |                        |                       |                         |                             | •                   |                     | •                    | •                   | •                          | •                          | •                   |
| 140EL PRO                 | 1703           | Compact corded electric                 | •         |           | •                       | •                     | •              | •               | •              |                |                        |                       |                         |                             | •                   |                     | •                    | •                   | •                          | •                          | •                   |
| Hobby 53EL Kit            | 1038           | Compact corded electric                 | •         | •         | •                       | •                     |                |                 |                |                | •                      |                       |                         |                             |                     | •                   | •                    | •                   | •                          | •                          | •                   |
| 140EL                     | 0274/0928      | Compact corded electric                 | •         | •         | •                       | •                     |                |                 |                |                | •                      |                       |                         |                             |                     | •                   | •                    | •                   | •                          | •                          | •                   |
| <b>Medium Duty Corded</b> |                |   |           |           |                         |                       |                |                 |                |                |                        |                       |                         |                             |                     |                     |                      |                     |                            |                            |                     |
| 181ELS                    | 1176/1705/1718 | Compact corded electric                 | •         |           | •                       |                       |                | •               | •              |                | •                      | •                     |                         | •                           |                     | •                   | •                    | •                   | •                          |                            | •                   |
| 191EL Pro                 | 1326/1327      | Compact corded electric                 | •         |           | •                       |                       |                | •               | •              |                | •                      |                       |                         |                             | •                   |                     | •                    | •                   | •                          |                            | •                   |
| <b>Heavy Duty Corded</b>  |                |   |           |           |                         |                       |                |                 |                |                |                        |                       |                         |                             |                     |                     |                      |                     |                            |                            |                     |
| Duo 35                    | 1165           | Versatile, corded for staples and nails | •         |           | •                       |                       | •              | •               | •              |                | •                      | •                     |                         | •                           | •                   | •                   | •                    | •                   | •                          |                            | •                   |
| Duo 50                    | 1166           | Powerful, corded stapling up to 50mm    | •         | •         | •                       |                       | •              | •               | •              | •              | •                      | •                     |                         | •                           | •                   | •                   | •                    | •                   | •                          |                            | •                   |
| 18G/50                    | 1183/1707      | Dedicated corded brad nailer            | •         | •         | •                       |                       | •              | •               | •              | •              | •                      | •                     |                         | •                           | •                   | •                   | •                    | •                   | •                          |                            | •                   |
| 400ELS Pro                | 0733/0876/1704 | Professional angled nailer              | •         |           | •                       |                       | •              | •               | •              |                | •                      | •                     |                         | •                           |                     | •                   | •                    | •                   | •                          |                            | •                   |

### Specifications

| Cordless                       | Code          | Dimensions in mm (H x W x D) | Weight (kg) | Magazine Capacity |                     | Fastener Type/Length    |                       | Min. firing distance from wall |
|--------------------------------|---------------|------------------------------|-------------|-------------------|---------------------|-------------------------|-----------------------|--------------------------------|
|                                |               |                              |             | Nails             | Staples             | Nails                   | Staples               |                                |
| Hobby 53-13EL – 4V             | 1563/1564     | 147 x 47 x 150               | 0.6         | 50                | 100                 | 180(18G)/10mm           | 53/6-12mm & 13/6-12mm | 15mm                           |
| 53-13EL – 12V                  | 1565/1632     | 150 x 50 x 180               | 0.9         | 85                | 140                 | 180(18G)/10mm           | 53/6-12mm & 13/6-12mm | 15mm                           |
| 140-180EL – 12V                | 1586/1603     | 150 x 50 x 180               | 0.9         | 85                | 84                  | 180(18G)/10mm           | 140/6-12mm            | 15mm                           |
| Ranger EL-PRO – 18V            | 1506          | 267 x 85 x 295               | 3.0         | 100               | 100                 | 180(18G)/12-50mm        | 91/19-40mm            | 20mm                           |
| <b>Compact Corded</b>          |               |                              |             |                   |                     |                         |                       |                                |
| Hobby 53EL Kit                 | 1038          | 135 x 195 x 55               | 0.8         | 90                | 125                 | 180(18G) 15mm           | 140/6-14mm            | 6mm                            |
| Hobby 53 and 13EL              | 1702          | 160 x 188 x 54               | 0.8         | 85                | 145 (53) & 150 (13) | 180(18G) 10-14mm        | 53/8-14mm & 13/8-14mm | 15mm                           |
| 140EL                          | 0274          | 135 x 195 x 55               | 0.8         | 90                | 83                  | 180(18G) 15mm           | 140/6-14mm            | 6mm                            |
| 140EL Pro                      | 1703          | 160 x 188 x 54               | 0.8         | 85                | 85                  | 180(18G) 10-14mm        | 140/8-14mm            | 15mm                           |
| <b>Medium Duty Corded</b>      |               |                              |             |                   |                     |                         |                       |                                |
| 181ELS Pro                     | 1176          | 230 x 255 x 68               | 1.6         | 100               | –                   | 180(18G) 15-35mm        | –                     | 25mm                           |
| 191EL Pro                      | 0326/0327     | 230 x 255 x 68               | 1.8         | 100               | 100                 | 180(18G) 15-35mm        | 91/15-30mm            | 25mm                           |
| <b>Heavy Duty Corded</b>       |               |                              |             |                   |                     |                         |                       |                                |
| Duo 35                         | 1165/1167     | 226 x 271 x 66               | 2.1         | 100               | 100                 | 180(18G) 15-35mm        | 91/15-30mm            | 25mm                           |
| Duo 50                         | 1166          | 294 x 275 x 73               | 2.7         | 100               | 100                 | 180(18G) 20-50mm        | 91/20-45mm            | 25mm                           |
| 18G/50 Brad Nailer             | 1183          | 296 x 277 x 80               | 2.3         | 100               | –                   | 180(18G) 20-50mm        | –                     | 25mm                           |
| 400ELS Inclined Nailer         | 0733/0876     | 210 x 290 x 57               | 1.8         | 100               | –                   | 500(18G Angled) 15-40mm | –                     | 15mm                           |
| 181ELS Spare rubber nose (5pk) | 1172 (Black)  | –                            | –           | –                 | –                   | –                       | –                     | –                              |
| 191EL Spare rubber nose (5pk)  | 0849 (Orange) | –                            | –           | –                 | –                   | –                       | –                     | –                              |
| Duo 50 Spare rubber nose (5pk) | 1206 (Black)  | –                            | –           | –                 | –                   | –                       | –                     | –                              |

# Applications

|  | Hobby 53-13EL | 53-13EL | 140-180EL | Ranger EL-PRO | Hobby 53 & 13EL | 140EL PRO | Hobby 53EL Kit | 140EL | 181ELS | 191EL Pro | Duo 35 | Duo 50 | 18G/50 | 400ELS Pro |
|--|---------------|---------|-----------|---------------|-----------------|-----------|----------------|-------|--------|-----------|--------|--------|--------|------------|
| Blinds and awnings                       | •             | •       | •         |               | •               | •         | •              | •     |        |           |        |        |        |            |
| Building membranes                       |               |         | •         |               |                 | •         |                | •     |        |           | •      | •      |        |            |
| Cabinet woodwork assembly                |               |         |           | •             |                 |           |                |       | •      | •         | •      | •      | •      | •          |
| Cabins, mobile homes, caravans           |               |         |           |               |                 |           |                |       | •      | •         | •      | •      |        | •          |
| Cane/rattan furniture                    |               |         |           |               |                 |           |                |       | •      | •         | •      | •      |        | •          |
| Carpeting and underlay                   |               |         | •         |               |                 | •         |                | •     |        |           |        |        |        |            |
| Damp proof coursing                      |               |         | •         |               |                 | •         |                | •     |        |           |        |        |        |            |
| Display/shop fitting                     | •             | •       | •         | •             | •               | •         | •              | •     | •      | •         | •      | •      | •      | •          |
| Door frames and skirting                 |               |         |           | •             |                 |           |                |       | •      | •         | •      | •      | •      | •          |
| Drawer bottoms                           |               |         |           |               |                 |           |                |       | •      | •         | •      | •      | •      | •          |
| Exhibition/shows                         | •             | •       | •         | •             | •               | •         | •              | •     | •      | •         | •      | •      | •      | •          |
| External pelmets                         |               |         |           |               |                 |           |                |       | •      | •         | •      | •      | •      | •          |
| Fabrics and blinds                       | •             | •       | •         |               | •               | •         | •              | •     |        |           |        |        |        |            |
| Fencing                                  |               |         |           |               |                 |           |                |       | •      | •         | •      | •      | •      |            |
| Garden furniture                         |               |         |           |               |                 |           |                |       |        |           | •      | •      | •      | •          |
| Gripper and thresholds                   |               |         |           | •             |                 |           |                |       | •      | •         | •      | •      | •      |            |
| Heavier textiles inc. leather and canvas |               |         |           |               | •               |           | •              |       |        |           |        |        |        |            |
| Hobby crafts                             | •             | •       |           |               | •               |           | •              |       |        |           |        |        |        |            |
| Insulation (roll)                        | •             | •       | •         |               | •               | •         | •              | •     |        |           | •      | •      | •      | •          |
| Light carpentry                          | •             | •       |           |               | •               |           | •              |       |        |           |        |        |        |            |
| Masonite                                 |               |         | •         |               |                 | •         |                | •     |        |           |        |        |        |            |
| Moulding and beading                     | •             | •       | •         | •             |                 | •         |                | •     | •      | •         | •      | •      | •      | •          |
| Netting/wire fencing                     |               |         | •         |               |                 | •         |                | •     |        | •         | •      | •      |        | •          |
| Panelling                                |               |         |           | •             |                 |           |                |       |        |           |        |        |        |            |
| Pet cages, runs and enclosures           |               |         |           |               |                 |           |                |       | •      | •         | •      | •      | •      | •          |
| Picture/mirror framing                   | •             | •       | •         |               | •               | •         | •              | •     | •      | •         | •      | •      | •      | •          |
| Plasterboard                             |               |         |           |               |                 |           |                |       |        | •         | •      | •      |        |            |
| Plastic sheeting                         |               |         | •         |               |                 | •         |                | •     |        | •         | •      | •      | •      | •          |
| Roofing                                  |               |         | •         |               |                 | •         |                | •     |        |           |        |        |        |            |
| Saunas                                   |               |         |           |               |                 |           |                |       | •      | •         | •      | •      |        | •          |
| Sheds and garden buildings               |               |         |           |               |                 |           |                |       | •      | •         | •      | •      |        | •          |
| Shoe repair                              |               |         |           |               |                 |           |                |       |        | •         | •      | •      |        | •          |
| Soft medium wood flooring                |               |         |           |               |                 |           |                |       | •      | •         | •      | •      | •      | •          |
| Staircase/bannister construction         |               |         |           | •             |                 |           |                |       | •      | •         | •      | •      |        | •          |
| Subflooring/boarding out                 |               |         |           |               |                 |           |                |       | •      | •         | •      | •      |        | •          |
| Tacking plasterboard/pre-screwing        |               |         |           |               |                 |           |                |       | •      | •         | •      | •      | •      | •          |
| Tacking with glue applications           |               |         |           |               |                 |           |                |       | •      | •         | •      | •      |        | •          |
| Tarpaulin                                |               |         | •         |               |                 | •         |                | •     |        |           |        |        |        |            |
| Theatre/film scenery                     | •             | •       |           |               | •               |           | •              |       | •      | •         | •      | •      | •      | •          |
| Thinner boards                           | •             | •       | •         |               | •               |           | •              |       |        |           |        |        |        |            |
| Tongue and groove flooring               |               |         |           | •             |                 |           |                |       | •      |           |        |        |        | •          |
| Trellis/panelling                        |               |         | •         |               |                 |           |                |       | •      | •         | •      | •      | •      | •          |
| Underfloor heating                       |               |         | •         |               |                 | •         |                | •     |        |           |        |        |        |            |
| Upholstery                               | •             | •       | •         |               | •               |           | •              |       |        |           |        |        |        |            |
| Weather strips                           | •             | •       |           |               | •               |           | •              |       |        |           |        |        |        |            |
| Window dressing                          | •             | •       |           |               | •               |           | •              |       |        | •         | •      | •      | •      | •          |
| Window frames and beading                |               |         |           | •             |                 |           |                |       |        |           |        |        |        |            |

# Staples


Hand, corded & cordless tackers

Produced from high grade raw materials, our staples are available in a range of finishes and sizes with full coverage of those most commonly used in upholstery, installation and second fix trades. Whatever the stapling task, you'll find a fastening that exceeds expectations.

## 140 staples

NEW  
NEW

| Code | Staple Length/Type     | Box Qty | For Use In  |
|------|------------------------|---------|---|
| 1627 | 140/18G Selection Pack | 7700    | Z3-140, 140-180EL   |
| 1341 | 140 Selection Pack     | 4400    | Z1-140, Z1-140L, Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL            |
| 0350 | 140 Selection Pack     | 4400    | Z1-140, Z1-140L, Z3-140, Z3-140L, A11, A54, 140EL                       |
| 0340 | 140/6mm                | 5000    | Z1-140, Z1-140L, Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL            |
| 0341 | 140/8mm                | 5000    | Z1-140, Z1-140L, Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL, 140EL Pro |
| 0342 | 140/10mm               | 5000    | Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL, 140EL Pro                  |
| 0477 | 140/10mm s/steel       | 5000    |   |
| 0343 | 140/12mm               | 5000    | Z3-140, Z3-140L, A54, 140EL, 140-180EL, 140EL Pro                       |
| 0344 | 140/14mm               | 5000    | Z3-140, Z3-140L, 140EL, 140EL Pro                                       |
| 0345 | 140/6mm                | 2000    | Z1-140, Z1-140L, Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL            |
| 0346 | 140/8mm                | 2000    | Z1-140, Z1-140L, Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL, 140EL Pro |
| 1216 | 140/8mm s/steel        | 2000    |   |
| 0347 | 140/10mm               | 2000    | Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL, 140EL Pro                  |
| 1217 | 140/10mm s/steel       | 2000    |   |
| 0348 | 140/12mm               | 2000    | Z3-140, Z3-140L, A54, 140EL, 140-180EL, 140EL Pro                       |
| 1220 | 140/12mm s/steel       | 2000    |   |
| 0349 | 140/14mm               | 2000    | Z3-140, Z3-140L, 140EL, 140EL Pro                                       |




## 140 staples – Hanging plastic dispenser box

|      |          |      |   |
|------|----------|------|---|
| 1416 | 140/6mm  | 2000 | Z1-140, Z1-140L, Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL            |
| 1417 | 140/8mm  | 2000 | Z1-140, Z1-140L, Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL, 140EL Pro |
| 1418 | 140/10mm | 2000 | Z3-140, Z3-140L, A11, A54, 140EL, 140-180EL, 140EL Pro                  |
| 1419 | 140/12mm | 2000 | Z3-140, Z3-140L, A54, 140EL, 140-180EL, 140EL Pro                       |
| 1420 | 140/14mm | 2000 | Z3-140, Z3-140L, 140EL, 140EL Pro                                       |

## 53 staples

NEW

|      |                       |        |  |
|------|-----------------------|--------|--|
| 1628 | 53/18G Selection Pack | 10,200 | Z3-53, Hobby 53-13EL, 53-13EL  |
| 1095 | 53 Selection Pack     | 6000   | Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, A19, Hobby 53EL, Hobby 53-13EL, 53-13EL  |
| 0331 | 53/6mm                | 5000   |  |
| 0332 | 53/8mm                | 5000   | Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, Z3-4 in 1, A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Z2 Series, Hobby 53 & 13EL |
| 0431 | 53/10mm               | 5000   |  |
| 0450 | 53/12mm               | 5000   | Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL  |
| 0452 | 53/14mm               | 5000   |  |
| 0333 | 53/4mm                | 2000   | Z1-53, Z1-53L, Z1-53T  |
| 0334 | 53/6mm                | 2000   | Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Z2 Series                             |
| 1268 | 53/6mm s/steel        | 2000   |  |
| 0335 | 53/8mm                | 2000   | Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, Z3-4 in 1, A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Z2 Series, Hobby 53 & 13EL |
| 1269 | 53/8mm s/steel        | 2000   |  |
| 0336 | 53/10mm               | 2000   | Z3-53, Z3-53L, Z3-4 in 1, A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL                                   |
| 1270 | 53/10mm s/steel       | 2000   |  |
| 0337 | 53/12mm               | 2000   | Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL  |
| 0338 | 53/14mm               | 2000   |  |




## 53 staples – Hanging plastic dispenser box

|      |         |      |  |
|------|---------|------|--|
| 1476 | 53/6mm  | 2500 | Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Z2 Series                             |
| 1477 | 53/8mm  | 2500 | Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, Z3-4 in 1, A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Z2 Series, Hobby 53 & 13EL |
| 1478 | 53/10mm | 2500 | Z3-53, Z3-53L, Z3-4 in 1, A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL                                   |
| 1479 | 53/12mm | 2500 | Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL, 53-13EL, Hobby 53 & 13EL   |




### CT-45 cable tacker staples – divergent point




| Code | Staple Length/Type         | Box Qty  | For Use In     |
|------|----------------------------|----------|----------------|
| 0980 | CT-45/8mm divergent white  | 5 x 1000 | CT-45, Z3-CT45 |
| 0352 | CT-45/10mm divergent       | 5 x 1000 |                |
| 0353 | CT-45/10mm divergent white | 5 x 1000 |                |

### CT-60 cable tacker staples – divergent point




|      |                            |          |                           |
|------|----------------------------|----------|---------------------------|
| 0354 | CT-60/10mm divergent       | 5 x 1000 | CT-60, Z3-CT60, Z3-4 in 1 |
| 1094 | CT-60/10mm divergent white | 5 x 1000 |                           |
| 0355 | CT-60/12mm divergent       | 5 x 1000 |                           |
| 0356 | CT-60/14mm divergent       | 5 x 1000 |                           |
| 0357 | CT-60/14mm divergent white | 5 x 1000 |                           |

### 13 staples



|      |         |      |   |
|------|---------|------|---|
| 0232 | 13/4mm  | 5000 | Z1-13, Z1-13L, Z2 Series  |
| 0233 | 13/6mm  | 5000 | Z1-13, Z1-13L, Z3-13, Z3-13L, A19, Hobby 13EL, Hobby 53-13EL, 53-13EL, Z2 Series, Hobby 53 & 13EL |
| 0234 | 13/8mm  | 5000 |   |
| 0235 | 13/10mm | 5000 | Z3-13, Z3-13L, A19, Hobby 13EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL                           |
| 0236 | 13/14mm | 5000 | Z3-13, Z3-13L, Hobby 13EL, Hobby 53 & 13EL  |


### 91 staples



NEW  
NEW

|      |                           |      |  |                       |
|------|---------------------------|------|--|-----------------------|
| 1616 | 91/18mm divergent         | 5000 | 191EL/S, Duo 35, Ranger 40 Duo         |                       |
| 1617 | 91/22mm divergent         | 5000 | 191EL/S, Duo 35, Duo 50, Ranger 40 Duo |                       |
| 0204 | 91 Selection Pack         | 2800 |  |                       |
| 0283 | 91/15mm                   | 1000 | 191EL/S, Duo 35, Ranger 40 Duo         |                       |
| 0287 | 91/18mm divergent         | 1000 |  |                       |
| 1069 | 91/18mm divergent s/steel | 1000 |  |                       |
| 0284 | 91/20mm                   | 1000 | 191EL/S, Duo 35, Duo 50, Ranger 40 Duo |                       |
| 0288 | 91/22mm divergent         | 1000 |  |                       |
| 1070 | 91/22mm divergent s/steel | 1000 |  |                       |
| 0285 | 91/25mm                   | 1000 |  |                       |
| 1071 | 91/25mm s/steel           | 1000 |  |                       |
| 0286 | 91/30mm                   | 1000 |  |                       |
| 0289 | 91/30mm divergent         | 1000 |  |                       |
| 0746 | 91/35mm                   | 1000 |  | Duo 50, Ranger 40 Duo |
| 0768 | 91/40mm                   | 1000 |  | Duo 50                |
| 1174 | 91/45mm                   | 1000 |  |                       |

### 71 staples




|      |                 |        |   |
|------|-----------------|--------|---|
| 0365 | 71/4mm          | 20,000 | 71EL, 71ELS, A7116LN, A7116V, A7116P            |
| 1126 | 71/4mm s/steel  | 20,000 |   |
| 0366 | 71/5mm          | 20,000 | 71EL, 71ELS, A7116LN, A7116AUTO, A7116V, A7116P |
| 0367 | 71/6mm          | 20,000 |   |
| 1014 | 71/6mm s/steel  | 20,000 |   |
| 0368 | 71/8mm          | 20,000 |   |
| 1065 | 71/8mm black    | 20,000 |   |
| 0369 | 71/10mm         | 20,000 |   |
| 0373 | 71/10mm black   | 20,000 |   |
| 0375 | 71/10mm s/steel | 20,000 |   |
| 0370 | 71/12mm         | 20,000 |   |
| 0290 | 71/12mm black   | 20,000 |   |
| 0371 | 71/14mm         | 10,000 |   |
| 0374 | 71/14mm black   | 10,000 |   |
| 0372 | 71/16mm         | 10,000 |   |

● Whilst stocks last


### Colour coded

Useful and convenient for quickly selecting the correct fastenings for Tacwise and other popular tools.




# Staples & Nails

Hand, corded & cordless tackers



## 80 staples

| Code | Staple Length/Type | Box Qty | For Use In |
|------|--------------------|---------|------------|
| 0380 | 80/4mm             | 10,000  | 80ELS      |
| 0381 | 80/6mm             | 10,000  |            |
| 0382 | 80/8mm             | 10,000  |            |
| 0383 | 80/10mm            | 10,000  |            |
| 0384 | 80/12mm            | 10,000  |            |
| 0385 | 80/14mm            | 10,000  |            |
| 1141 | 80/16mm            | 10,000  |            |



## 73 staples

| Code | Staple Length/Type       | Box Qty | For Use In                      |
|------|--------------------------|---------|---------------------------------|
| 1227 | 73/8mm divergent s/steel | 5000    | HD-73,<br>All 31 Type<br>Pliers |
| 0456 | 73/10mm                  | 5000    |                                 |
| 0457 | 73/12mm                  | 5000    |                                 |
| 1389 | 73/12mm chisel s/steel   | 5000    |                                 |

## NEW RAPESCO® 26 staples

| Code     | Staple Length/Type | Box Qty | For Use In                             |
|----------|--------------------|---------|--|
| S11662Z3 | 26/6mm             | 5000    | Porpoise<br>& other<br>stapling pliers |
| S11880Z3 | 26/8mm             | 5000    |  |
| S2662MA3 | 26/6mm             | 2000    |  |
| S11661Z3 | 26/6mm             | 1000    |  |

## NEW RAPESCO® 24 staples (22 type)

| Code     | Staple Length/Type   | Box Qty | For Use In                             |
|----------|----------------------|---------|--|
| S24602Z3 | 24/6mm               | 5000    | Porpoise<br>& other<br>stapling pliers |
| S24807Z3 | 24/8mm               | 5000    |  |
| S24607Z3 | 24/6mm               | 1000    |  |
| S24600Z3 | 24/6mm copper plated | 1000    |  |
| 1456     | 24/8mm               | 1000    |  |

## NEW RAPESCO® 73 staples


| Code | Staple Length/Type | Box Qty | For Use In                   |
|------|--------------------|---------|------------------------------|
| 1260 | 73/10mm            | 2000    | HD-73, All 31<br>Type Pliers |
| 1261 | 73/12mm            | 2000    |                              |

The largest range of quality nails in Europe, manufactured from premium grade materials to exacting standards. With an ever increasing range of stainless steel for external applications, our fastenings deliver outstanding results across a range of applications and tools.

## 180 (18G) nails

NEW  
NEW

| Code | Nail Length/Type       | Box Qty | For Use In   |  |
|------|------------------------|---------|--|--|
| 1628 | 18G/53 Selection Pack  | 10,200  | Z3-53, Hobby 53-13EL, 53-13EL  |  |
| 1627 | 18G/140 Selection Pack | 7700    | Z3-140, 140-180EL  |  |
| 0205 | 180 Selection Pack     | 4000    | Z3 Series, 181ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo        |  |
| 0358 | 180/10mm               | 2000    | Hobby 53-13EL, 53-13EL, 140-180EL  |  |
| 0359 | 180/15mm               | 2000    | Z3 Series, 140EL, 181ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo |  |
| 0360 | 180/20mm               | 1000    | 181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo      |  |
| 0361 | 180/25mm               | 1000    |  |  |
| 1066 | 180/25mm s/steel       | 1000    |  |  |
| 0362 | 180/30mm               | 1000    |  |  |
| 1067 | 180/30mm s/steel       | 1000    |  |  |
| 0363 | 180/32mm               | 1000    |  |  |
| 0364 | 180/35mm               | 1000    |  |  |
| 1068 | 180/35mm s/steel       | 1000    |  |  |
| 0747 | 180/40mm               | 1000    |  | 191EL/S, Ranger 2, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo |
| 1156 | 180/50mm               | 1000    |  | 191EL/S, Duo 50, 18G/50, Ranger 2 18G                          |



## 180 nails – Hanging plastic dispenser box


|      |                  |      |  |
|------|------------------|------|--|
| 1509 | 180/15mm s/steel | 2000 | Z3 Series, 140EL, Compact Series, 181ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo |
| 1510 | 180/20mm s/steel | 1000 | 181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo                      |
| 1511 | 180/40mm s/steel | 1000 | 191EL/S, Ranger 2, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo                             |
| 1512 | 180/50mm s/steel | 1000 | 191EL/S, Duo 50, 18G/50, Ranger 2 18G  |

NEW

## 18G brad nails

|      |          |      |   |
|------|----------|------|---|
| 1724 | 18G/14mm | 5000 | Hobby 53 & 13EL, 140EL Pro  |
| 1708 | 18G/15mm | 4000 | Z3 Series, 140EL, Hobby 53EL, 181 ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo |
| 1709 | 18G/20mm | 4000 | 181 EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo                  |
| 1710 | 18G/25mm | 4000 |   |
| 1711 | 18G/30mm | 4000 |   |
| 1712 | 18G/32mm | 4000 |   |
| 1713 | 18G/35mm | 4000 |   |
| 1714 | 18G/40mm | 4000 |   |
| 1715 | 18G/50mm | 4000 | 191EL/S, Duo 50, 18G/50, Ranger 2 18G   |

(actual size)




### 180 headless pins

| Code | Nail Length/Type | Box Qty | For Use In |
|------|------------------|---------|------------|
| 0478 | 180/15mm         | 2000    | Z3 Series  |

### 500 angled nails (18G angled brad nails)

(actual size)

Nail Head = □



|      |                  |      |                      |
|------|------------------|------|----------------------|
| 0823 | 500/20mm         | 5000 | 400EL, 400ELS, 500EL |
| 0824 | 500/25mm         | 5000 |                      |
| 0825 | 500/30mm         | 5000 |                      |
| 0826 | 500/35mm         | 5000 |                      |
| 0827 | 500/40mm         | 5000 |                      |
| 0828 | 500/45mm         | 5000 | 500EL                |
| 0829 | 500/50mm         | 5000 |                      |
| 0479 | 500/20mm         | 1000 | 400EL, 400ELS, 500EL |
| 1131 | 500/20mm s/steel | 1000 |                      |
| 0480 | 500/25mm         | 1000 |                      |
| 0481 | 500/30mm         | 1000 |                      |
| 1132 | 500/30mm s/steel | 1000 |                      |
| 0482 | 500/35mm         | 1000 | 500EL                |
| 1133 | 500/35mm s/steel | 1000 |                      |
| 0483 | 500/40mm         | 1000 |                      |
| 1134 | 500/40mm s/steel | 1000 |                      |
| 0484 | 500/45mm         | 1000 |                      |
| 0485 | 500/50mm         | 1000 |                      |
| 1135 | 500/50mm s/steel | 1000 |                      |

### 160 (16G) stainless steel finish nails

|      |                  |      |                      |
|------|------------------|------|----------------------|
| 1096 | 160/32mm s/steel | 1000 | 16G/45, Ranger 2 16G |
| 1097 | 160/38mm s/steel | 1000 |                      |
| 1098 | 160/50mm s/steel | 1000 | Ranger 2 16G         |

### 16G finish nails

(actual size)

Nail Head = □



|      |          |      |                      |
|------|----------|------|----------------------|
| 0665 | 16G/20mm | 2500 | 16G/45               |
| 0666 | 16G/25mm | 2500 |                      |
| 0293 | 16G/30mm | 2500 |                      |
| 0294 | 16G/32mm | 2500 |                      |
| 0295 | 16G/35mm | 2500 |                      |
| 0296 | 16G/38mm | 2500 | 16G/45, Ranger 2 16G |
| 0319 | 16G/40mm | 2500 | Ranger 2 16G         |
| 0297 | 16G/45mm | 2500 |                      |
| 0298 | 16G/50mm | 2500 |                      |
| 0299 | 16G/55mm | 2500 |                      |
| 0300 | 16G/60mm | 2500 |                      |
| 0301 | 16G/64mm | 2500 |                      |

### 16G angled finish nails

(actual size)



□ = Nail Head

|      |                  |      |  |
|------|------------------|------|--|
| 0769 | 16G/32mm         | 2500 | Ranger 2 16G Inclined,<br>DeWalt™ DC618, DCN660,<br>Paslode® IM250A, IM65A F16 Nailers |
| 1222 | 16G/32mm s/steel | 2500 |  |
| 0770 | 16G/38mm         | 2500 |  |
| 1223 | 16G/38mm s/steel | 2500 |  |
| 0771 | 16G/45mm         | 2500 |  |
| 1224 | 16G/45mm s/steel | 2500 |  |
| 0772 | 16G/50mm         | 2500 |  |
| 1225 | 16G/50mm s/steel | 2500 |  |
| 0773 | 16G/63mm         | 2500 |  |
| 1226 | 16G/63mm s/steel | 2500 |  |

Cordless Glue Guns | Gluing up to 11.75mm

# Cordless 4V

## DIY/Semi-pro glue gun

Lightweight and packed with innovation this entry model is a must have for applications where speed, convenience and precision are the focus.

### H4-7 Cordless 4V Hot Melt Glue Gun

|              |            |   |
|--------------|------------|---|
| DIY/Semi-Pro | Code: 1559 | Includes: USB charging cable, 30pcs hot melt glue sticks, storage bag |
|              | Code: 1558 | Includes: USB charging cable, 6pcs hot melt glue sticks               |

-   
Diameter/Length  
7mm x 150mm
-   
0.24kg
-   
LED  
Work Light
-   
Storage Bag  
(1559 only)
-   
USB Charge  
Cable
-   
Hanging  
Retail Box
-   
Trade = 1 Units  
Transit = 10 Units











# Cordless 12V

## Semi-pro/pro glue gun

Utilising the Tacwise 12V fast charge battery platform, this model carries all the features of the 4V tool but with extra power to deliver more glue with each charge.

### H12-7 Cordless 12V Hot Melt Glue Gun

|                   |            |  |
|-------------------|------------|--|
| Semi-Professional | Code: 1560 | Includes: 12V battery, UK mains charger, Euro plug adaptor, 30pcs glue sticks, storage bag |
|                   | Code: 1604 | Includes: Tool body only   |

-   
Diameter/Length  
7mm x 150mm
-   
0.25kg  
(Tool Only)
-   
LED  
Work Light
-   
Storage  
Bag
-   
UK  
Charger
-   
Euro  
Adaptor
-   
Hanging  
Retail Box
-   
Trade = 1 Units  
Transit = 10 Units

**NEW**



### 12 Volt Li-ion Battery

This fast charging, interchangeable battery can be used in any of our 12V range.

Code: 1582









## High output, performance glue gun

This cordless Lithium-Ion powered glue gun gives you independence and working flexibility and is ideal for frequent tasks that call for accuracy and efficiency. Super-fast 60 second heat up time dispenses glue at a high output of 360g/h. Ergonomically designed, easy to use with a battery-powered base providing a sturdy platform to keep the gun upright eliminating any glue leaks.

### H12-12 Cordless 12V Hot Melt Glue Gun

|                   |            |  |
|-------------------|------------|--|
| Semi-Professional | Code: 1561 | Includes: 12V battery, UK mains charger, Euro plug adapter, 10pcs glue sticks, storage bag |
|-------------------|------------|--|

**NEW**

-   
 Diameter/Length  
 11.75mm x 150mm
-   
 0.43kg
-   
 LED  
 Work Light
-   
 Storage  
 Bag
-   
 UK  
 Charger
-   
 Euro  
 Adaptor
-   
 Hanging  
 Retail Box
-   
 Trade = 1 Units  
 Transit = 10 Units



### Speed and durability

For the hobby and professional alike, Tacwise hot melt glue guns and adhesives deliver quality results and bond a wide variety of materials quickly and efficiently.



Corded Glue Guns | Gluing up to 11.75mm

# Corded 150 & 202 Glue Guns

## For hot and cool melt gluing

Our corded glue guns offer fast, reliable heating, tough polymer housing with ergonomic grips for comfort and an integrated stand for resting the glue gun in between applications.

### 150 Cool Melt Glue Gun

**Semi-Professional** Code: 0465 Includes: 2pcs 7.4mm x 100mm clear glue sticks



Diameter/Length  
7.4mm x 100mm



0.3kg



Retail  
Box



Trade = 12 Units  
Transit = 36 Units

Safe, compact gun, ideal for hobby use, arts and crafts or general low volume applications. Cool melt offers a safer alternative with the adhesive running at a much lower temperature.



Rubber nose  
protector



Illuminated on/off switch  
(model 202)



Pressure touch  
feed system



### 150 & 202 Tool Features

The 150 and 202 models have handy features including insulated rubber nose protectors, on/off switches (illuminated for 202) and pressure touch feed systems for speed and reliability.

### 202 Hot Melt Glue Gun

**Semi-Professional** Code: 0466 Includes: 1pc 11.75mm x 100mm clear glue stick



Diameter/Length  
11.75mm x 100mm



0.5kg



Retail  
Box



Trade = 6 Units  
Transit = 24 Units

A well balanced glue gun for maximum control and an easier output flow of glue.



## Features

| Cordless                              | Code      | Description  | Auto turn off | Ergonomic grip | Fast heating system | Flat base functions as a stand | Heat protector nose | Illuminated on/off switch | Integrated wire stand | LED work light | Long power cord | Multi-finger trigger | On/off switch | Pressure touch feed system | Rechargeable lithium-ion battery | Removable 12V lithium-ion battery | Status indicator light | Tough polymer lightweight body |
|---------------------------------------|-----------|--|---------------|----------------|---------------------|--------------------------------|---------------------|---------------------------|-----------------------|----------------|-----------------|----------------------|---------------|----------------------------|----------------------------------|-----------------------------------|------------------------|--------------------------------|
| H4-7 Cordless 4V Hot Melt Glue Gun    | 1558/1559 | Compact with integrated 4V rechargeable battery      | •             | •              | •                   | •                              | •                   |                           |                       | •              |                 | •                    | •             | •                          | •                                |                                   | •                      | •                              |
| H12-7 Cordless 12V Hot Melt Glue Gun  | 1565/1632 | Interchangeable 12V battery. LED work light          | •             | •              | •                   | •                              | •                   |                           |                       | •              |                 | •                    | •             | •                          | •                                | •                                 | •                      | •                              |
| H12-12 Cordless 12V Hot Melt Glue Gun | 1586/1603 | Versatile and super-fast heat up time                | •             | •              | •                   | •                              | •                   |                           |                       | •              |                 | •                    | •             | •                          | •                                | •                                 | •                      | •                              |
| Corded                                | Code      | Description  | Auto turn off | Ergonomic grip | Fast heating system | Flat base functions as a stand | Heat protector nose | Illuminated on/off switch | Integrated wire stand | LED work light | Long power cord | Multi-finger trigger | On/off switch | Pressure touch feed system | Rechargeable lithium-ion battery | Removable 12V lithium-ion battery | Status indicator light | Tough polymer lightweight body |
| 150 Cool Melt Glue Gun                | 0465      | Compact. Works at a safer lower temperature          |               | •              | •                   |                                | •                   | •                         | •                     | •              | •               | •                    | •             | •                          |                                  |                                   |                        | •                              |
| 202 Hot Melt Glue Gun                 | 0466      | Semi-professional, well balanced for maximum control |               | •              | •                   |                                | •                   | •                         | •                     | •              | •               | •                    | •             | •                          |                                  |                                   |                        | •                              |

## Applications

| Cordless                              | Code      | Description  | Beading/mouldings | Book binding | Carton sealing | Decorative/general DIY | Decorative/intricate crafts | Display/shop fitting | Exhibition/shows | Fixing gripper/thresholds | Floristry | Hobby crafts | Picture/mirror frames | Schools/education | Theatre/film scenery | Toy repairs | Upholstery/re-upholstery | Window dressing |
|---------------------------------------|-----------|--|-------------------|--------------|----------------|------------------------|-----------------------------|----------------------|------------------|---------------------------|-----------|--------------|-----------------------|-------------------|----------------------|-------------|--------------------------|-----------------|
| H4-7 Cordless 4V Hot Melt Glue Gun    | 1558/1559 | Compact with integrated 4V rechargeable battery      |                   | •            | •              | •                      |                             |                      |                  |                           | •         | •            | •                     | •                 |                      | •           | •                        | •               |
| H12-7 Cordless 12V Hot Melt Glue Gun  | 1565/1632 | Interchangeable 12V battery. LED work light          |                   | •            | •              | •                      |                             | •                    | •                |                           | •         | •            | •                     |                   | •                    |             | •                        | •               |
| H12-12 Cordless 12V Hot Melt Glue Gun | 1586/1603 | Versatile and super-fast heat up time                | •                 | •            | •              |                        |                             | •                    | •                |                           | •         | •            | •                     |                   | •                    |             | •                        | •               |
| Corded                                | Code      | Description  | Beading/mouldings | Book binding | Carton sealing | Decorative/general DIY | Decorative/intricate crafts | Display/shop fitting | Exhibition/shows | Fixing gripper/thresholds | Floristry | Hobby crafts | Picture/mirror frames | Schools/education | Theatre/film scenery | Toy repairs | Upholstery/re-upholstery | Window dressing |
| 150 Cool Melt Glue Gun                | 0465      | Compact. Works at a safer lower temperature          |                   |              |                | •                      |                             |                      |                  |                           | •         | •            | •                     |                   |                      |             |                          |                 |
| 202 Hot Melt Glue Gun                 | 0466      | Semi-professional, well balanced for maximum control | •                 |              |                | •                      |                             | •                    | •                |                           | •         | •            | •                     | •                 | •                    | •           | •                        | •               |

## Specifications

| Cordless                              | Code      | Dimensions in mm (H x W x D) | Weight (kg) | Glue Diameter/Length (mm) | Voltage | Capacity (Ah) | Charge Time (Hrs) | Consumables per charge (continuous use) |
|---------------------------------------|-----------|------------------------------|-------------|---------------------------|---------|---------------|-------------------|---|
| H4-7 Cordless 4V Hot Melt Glue Gun    | 1558/1559 | 157 x 165 x 42               | 0.43        | 7 x 150mm                 | 4V      | 1.3           | 1.5               | Up to 6 glue sticks                     |
| H12-7 Cordless 12V Hot Melt Glue Gun  | 1560/1604 | 200 x 160 x 52               | 0.24        | 7 x 150mm                 | 12V     | 1.3           | 3-5               | Up to 16 glue sticks                    |
| H12-12 Cordless 12V Hot Melt Glue Gun | 1561      | 205 x 176 x 52               | 0.28        | 11.75 x 150mm/300mm       | 12V     | 1.3           | 3-5               | 8 (150mm) /4 (300mm)                    |
| Corded                                | Code      | Dimensions in mm (H x W x D) | Weight (kg) | Glue Diameter/Length (mm) | Voltage | Capacity (Ah) | Charge Time (Hrs) | Consumables per charge (continuous use) |
| 150 Cool Melt Glue Gun                | 0465      | 117 x 127 x 24               | 0.3         | 7.4 x 100mm               | -       | -             | -                 | -                                       |
| 202 Hot Melt Glue Gun                 | 0466      | 157 x 187 x 32               | 0.5         | 11.75 x 300mm             | -       | -             | -                 | -                                       |

## Glue Sticks Specifications

| Hot Melt Glue               | Code | Dimensions in mm (H x W x D) | Pack Quantity  | Pack Style  | For Use In:       |
|-----------------------------|------|------------------------------|----------------|-------------|-------------------|
| Clear Hot Melt Glue Sticks  | 1562 | 7 x 150mm                    | 100 Sticks     | Plain Box   | H4-7, H12-7       |
| Clear Hot Melt Glue Sticks  | 0470 | 11.75 x 300mm                | 16 Sticks      | Retail Box  | H12-12, 202 & 207 |
| Clear Hot Melt Glue Sticks  | 0471 | 11.75 x 300mm                | 5kg/160 Sticks | Carton      | H12-12, 202 & 207 |
| Tan Hot Melt Glue Sticks    | 0472 | 11.75 x 300mm                | 5kg/160 Sticks | Carton      | H12-12, 202 & 207 |
| Cool Melt Glue              | Code | Dimensions in mm (H x W x D) | Pack Quantity  | Pack Style  | For Use In:       |
| Clear Cool Melt Glue Sticks | 0476 | 7.4 x 100mm                  | 12 Sticks      | Retail Card | 150               |

# Air Nailing & Stapling

35 quality, high performance tools

We believe that design and manufacturing innovation is the key to success and we continue to refine our designs to bring you the very best tools within their class. Our aim is to develop new standards of performance utilising the most advanced aluminium, magnesium and titanium materials, to define products that do more than simply function – but that perform better and last longer.





## Built for the professional

Tacwise is committed to creating the ultimate fastening product range from hand, corded, cordless and air powered equipment, combined together to provide the widest quality tools and consumables programme in Europe.

## Loaded with features

Each with their own powerful features, Tacwise air tools are carefully designed for user safety, convenience and durability.



Many tools include a flip open quick release nose gate for clearance of a fastener, in the unlikely event of a jam.




Reload indicators and rubber noses to avoid damaging softer timbers. Easy reference serial numbering makes re-ordering consumables and replacement parts easy.



Handy and easy to use controls for depth adjustment make precision tasks simple.



This small lever allows the user to quickly switch between single shot and contact trip (bump fire).



Quick release magazines of different styles mean ultra fast re-loading.

# General Purpose & Upholstery Staple Guns

Fast and lightweight

Unrivalled quality and performance from our top selling upholstery and general purpose air staplers. From the fastest to the lightest, we have a programme that covers all applications. Tacwise has continued to refine its programme of upholstery and general stapling tools after many years of industry experience.



## Extra Long Nose 71 Staple Tacker 71/4-16mm

Production Line Code: A7116LN **BEST VALUE**

-  71 Staples 4-16mm
-  60-100
-  1.1kg
-  Carry Case
-  Trade = 1 Unit  
Transit = 6 Units

Magnesium bodied stapler with an extended 50mm nose to allow for stapling into awkward areas. Lightweight and compact with rear exhaust, this tool is a firm favourite in the re-upholstery trade.

## Extra Long Nose 80 Staple Tacker 80/4-16mm

Production Line Code: A8016LN **BEST VALUE**

-  80 Staples 4-16mm
-  60-100
-  1kg
-  Carry Case
-  Trade = 1 Unit  
Transit = 6 Units

Magnesium bodied stapler with an extended 50mm nose to allow for stapling into awkward areas. Lightweight and compact with rear exhaust, this tool is a firm favourite in the re-upholstery trade.

## 71 Automatic Staple Tacker 71/5-16mm

Production Line Code: A7116AUTO



71 Staples 5-16mm



70-100



0.9kg




Retail  
Box



Trade = 1 Unit  
Transit = 10 Units

Easy to switch between single and continuous fire with a variable speed control. Quick reloading makes for rapid stapling on large jobs with minimum downtime. This tool is powerful yet lightweight and will happily run from a small compressor.



## 71 Upholstery Staple Tacker 71/4-16mm

|                 |              |                                 |
|-----------------|--------------|---------------------------------|
| Production Line | Code: A7116V | BEST VALUE                      |
|                 | Code: 1190   | Includes: 120,000pcs 71 staples |

NEW



71 Staples 4-16mm



60-100



0.9kg



Carry  
Case



Trade = 1 Unit  
Transit = 10 Units

Fast, reliable and the first choice for many professional upholsterers. Incorporating every essential feature our users have asked for. Quiet, reliable and extremely quick to load.

## Premium 71 Staple Tacker 71/4-16mm

Production Line Code: A7116P



71 Staples 4-16mm



60-100



0.8kgs



Retail  
Box



Trade = 1 Unit  
Transit = 10 Units

This model is fast and well balanced. Designed for the production line environment. Incorporating every essential feature our users have asked for. Quiet, reliable and extremely quick to reload.



## 80 Upholstery Staple Tacker 80/4-16mm

|                 |              |            |
|-----------------|--------------|------------|
| Production Line | Code: A8016V | BEST VALUE |
|-----------------|--------------|------------|



80 Staples 4-16mm



60-100



0.9kg



Carry  
Case



Trade = 1 Unit  
Transit = 10 Units

Fast, reliable and the ultimate first choice for many professional upholsterers. Ideal for production line use. The wide 80 series staple provides additional fastening strength for materials such as plastic sheeting. Especially popular with our European users.



### 140 Staple Tacker 140/4-14mm

Professional

Code: A14014V

BEST VALUE



140 Staples 4-14mm



60-100



0.9kg



Carry Case



Trade = 1 Unit  
Transit = 10 Units

This professional tool handles the 140 (T-50 Type) staple, commonly used in hand and electric tackers. Ideal for hand tool users tackling volume stapling tasks with standard and stainless steel staples. 140 staples listed on page 48.






Watch the A14014V video



#### 71 staples

| Code | Staple Length/Type | Box Qty | For Use In  |
|------|--------------------|---------|---|
| 0365 | 71/4mm             | 20,000  | 71 EL, 71 ELS, A7116LN, A7116V, A7116P            |
| 1126 | 71/4mm s/steel     | 20,000  |   |
| 0366 | 71/5mm             | 20,000  | 71 EL, 71 ELS, A7116LN, A7116AUTO, A7116V, A7116P |
| 0367 | 71/6mm             | 20,000  |   |
| 1014 | 71/6mm s/steel     | 20,000  |   |
| 0368 | 71/8mm             | 20,000  |   |
| 1065 | 71/8mm black       | 20,000  |   |
| 0369 | 71/10mm            | 20,000  |   |
| 0373 | 71/10mm black      | 20,000  |   |
| 0375 | 71/10mm s/steel    | 20,000  |   |
| 0370 | 71/12mm            | 20,000  |   |
| 0290 | 71/12mm black      | 20,000  |   |
| 0371 | 71/14mm            | 10,000  | 80ELS   |
| 0374 | 71/14mm black      | 10,000  |   |
| 0372 | 71/16mm            | 10,000  |   |



#### 80 staples

|      |         |        |
|------|---------|--------|
| 0380 | 80/4mm  | 10,000 |
| 0381 | 80/6mm  | 10,000 |
| 0382 | 80/8mm  | 10,000 |
| 0383 | 80/10mm | 10,000 |
| 0384 | 80/12mm | 10,000 |
| 0385 | 80/14mm | 10,000 |
| 1141 | 80/16mm | 10,000 |

#### 1400 staples

|      |           |        |
|------|-----------|--------|
| 0378 | 1400/10mm | 10,000 |
| 0379 | 1400/12mm | 10,000 |

Haubold® Type Tackers

● Whilst stocks last

# Narrow Crown Staplers

## 3 of the best production line models

Our narrow crown programme offers outstanding performance and versatility. The C9725V is compact and fast. The D9040V is versatile, reliable and its many stand-out features puts it at the top of the class in cabinet making and garden furniture applications.

### 25mm Narrow Crown Stapler 97/10-25mm

|                 |              |            |
|-----------------|--------------|------------|
| Production Line | Code: C9725V | BEST VALUE |
|-----------------|--------------|------------|

- 97 Staples 10-25mm
- 60-100
- 1.2kg
- Carry Case
- Trade = 1 Unit  
Transit = 6 Units

Built to last, this performance stapler copes easily with high volume stapling. Narrow quick release nose gate and safety. Top multi-directional exhaust and recessed magazine release.



### 32mm Narrow Crown Stapler 90/12-32mm

|                 |              |            |
|-----------------|--------------|------------|
| Production Line | Code: C9032V | BEST VALUE |
|-----------------|--------------|------------|

- 90 Staples 12-32mm
- 60-100
- 1.2kg
- Carry Case
- Trade = 1 Unit  
Transit = 6 Units

Magnesium bodied stapler offering tremendous versatility and speed of use. Top selling model with excellent performance. Narrow quick release nose gate with protector and safety. Top multi-directional exhaust and recessed magazine release.



### 40mm Narrow Crown Stapler 90/15-40mm


|                 |              |            |
|-----------------|--------------|------------|
| Production Line | Code: D9040V | BEST VALUE |
|-----------------|--------------|------------|

- 90 Staples 15-40mm
- 70-120
- 3kg
- Carry Case
- Trade = 1 Unit  
Transit = 5 Units

With contact trip (bump fire) & sequential firing adjustment this fast and versatile 90 series tool comes with soft nose protector and quick release nose gate with safety. Top multi-directional exhaust.


# Staples

## Narrow & Wide Crown Staples & Corrugated Fastener




### 97 narrow crown staples

| Code | Staple Length/Type | Box Qty | For Use In       |
|------|--------------------|---------|------------------|
| 0302 | 97/10mm            | 5000    | C9725V, C9725VHH |
| 0303 | 97/15mm            | 5000    |                  |
| 0304 | 97/20mm            | 5000    |                  |
| 0305 | 97/25mm            | 5000    |                  |




### 90 narrow crown staples

|      |                         |      |  |
|------|-------------------------|------|--|
| 0306 | 90/15mm                 | 5000 | C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH, 1326 |
| 0312 | 90/18mm divergent point | 5000 |  |
| 0307 | 90/20mm                 | 5000 |  |
| 0313 | 90/22mm divergent point | 5000 |  |
| 0308 | 90/25mm                 | 5000 |  |
| 0309 | 90/30mm                 | 5000 | D9040V, C9040LHH, DNS50PHH, 1326                   |
| 1144 | 90/32mm                 | 5000 |  |
| 0310 | 90/35mm                 | 5000 |  |
| 0311 | 90/40mm                 | 5000 |  |




### 14 heavy duty staples galv. coated

|      |         |        |  |
|------|---------|--------|--|
| 0179 | 14/19mm | 15,000 | F1440L, G1450V, F1450M, F1440LHH, G1450MHH |
| 0180 | 14/25mm | 15,000 |  |
| 0173 | 14/32mm | 10,000 |  |
| 0174 | 14/35mm | 10,000 |  |
| 0175 | 14/38mm | 10,000 |  |
| 0176 | 14/45mm | 10,000 | G1450V, F1450M, G1450MHH                   |
| 0177 | 14/50mm | 10,000 |  |




### 17 wide crown staples

|      |         |        |                  |
|------|---------|--------|------------------|
| 0780 | 17/19mm | 10,000 | G1738XHH, G1738V |
| 0386 | 17/25mm | 10,000 |                  |
| 0387 | 17/32mm | 10,000 |                  |



### 32 carton closing staples

|      |                           |      |  |
|------|---------------------------|------|--|
| 0186 | 32/15mm (copper coloured) | 2000 | Standard carton top and bottom sealers |
| 0187 | 32/18mm (copper coloured) | 2000 |  |



### Corrugated fasteners

|      |           |      |          |
|------|-----------|------|----------|
| 0447 | CF9 9mm   | 2000 | FCF15XCB |
| 0448 | CF12 12mm | 1750 |          |
| 0449 | CF15 15mm | 1500 |          |

360° Adjustable Exhaust Port



# Heavy Duty & Wide Crown Staplers

Fast and reliable

Outstanding power and speed from our range of heavy duty and wide crown staplers. Rugged tools which are highly reliable.

Depth Control Adjuster



Single Shot/Contact Trip



## 50mm Heavy Duty Stapler 14/19-50mm

|                 |              |            |
|-----------------|--------------|------------|
| Production Line | Code: G1450V | BEST VALUE |
|-----------------|--------------|------------|



14 Staples 19-50mm



70-120



2kg



Carry Case




Trade = 1 Unit  
Transit = 4 Units

Preferred throughout the bedding and furniture industry, this durable framing tool is a first choice. Loaded with features including firing variations, depth control and a quick release nose gate in the unlikely event of a staple jam.

# Air Stapler/Corrugated Fastener/Inclined Nailer



G1450V – Quick release nose gate



Easy top loading



Single shot – contact trip



Depth control adjustment



## 50mm Heavy Duty Stapler

Production Line Code: F1450M



14 Staples 19-50mm



70-120



1.9kg



Retail Box



Trade = 1 Unit  
Transit = 2 Units

Lightweight, compact and powerful this 50mm tool delivers an impressive performance. Beautifully balanced and highly reliable. Well established in many 'blue chip' furniture factories. Can be supplied without the quick release nose gate.

## Heavy Duty Wide Crown Stapler

Production Line Code: G1738V



17 Staples 16-38mm



70-100



2.4kg



Carry Case



Trade = 1 Unit  
Transit = 5 Units

Primarily used for attaching packaging materials to wooden pallets, this quality wide crown stapler is a work horse that's loaded with features. Tough and reliable, it boasts a magazine stabilising bar, a depth adjuster and a flip open quick release nose gate for the clearance of staples in the unlikely event of a jam.



Firing Wide Crown Staples



# Corrugated Fastener

## Premium 15mm Corrugated Fastener

Production Line Code: FCF15XCB



Corrugated Fasteners  
9-15mm



75-110



2.6kg



Retail Box



Trade = 1 Unit  
Transit = 4 Units

Powerful fastening tool, capable of countersinking 15mm fasteners. Easy bottom loading of any size with minor adjustment. Ideal for butt joints in cabinet/furniture frames and for door and window sash manufacturers.



# Nailers & Pinners

Wide assortment of quality tools

Covering fine pins of just 12mm length up to 64mm finish nails.  
Meeting all your requirements.

**64mm Inclined Air Nailer** 15G/32-64mm

**NEW**

Production Line

Code: GDA64V2

BEST VALUE



15G 'D' Head Inclined  
Finish Nails 32-64mm



70-120



2kg



Carry  
Case



Trade = 1 Unit  
Transit = 4 Units



# Air Pin, Brad & Finish Nailers

Nailing up to 64mm / Stapling up to 40mm



## 23G Headless Pinner

Production Line Code: A6422V BEST VALUE

 23G 'A64' 12-22mm 
  60-100 
  0.8kg 
  Carry Case 
  Trade = 1 Unit  
Transit = 10 Units

Built for industrial use, featuring an auto adjusting magazine with a 100 pin capacity. This model also boasts a moveable exhaust top cap, safety trigger lock mechanism and because it operates between 60-100 PSI, only a small compressor is needed.

## 35mm Headless Pinner

Production Line Code: A6435


 23G 'A64' 12-35mm 
  60-100 
  0.9kg 
  Retail Box 
  Trade = 1 Unit  
Transit = 10 Units

This quality, lightweight tool is perfect for fixing fine beading. Ultra slim nose for accurate pin placement. No adjustment is required to fire pins of different lengths. Rear exhaust, double trigger safety system and high durability driver.



## 32mm Brad Nailer 180/10-32mm 18G/10-32mm

Production Line Code: C1832V BEST VALUE

 180 (18G) Nails 10-32mm 
  60-100 
  1.1kg 
  Carry Case 
  Trade = 1 Unit  
Transit = 6 Units

This hugely popular lightweight tool is accurate and reliable and offers tremendous value. Compact and versatile it can be bump fired with its contact trip valve. Fires up to 5 shots per second.

## 50mm Brad Nailer 180/20-50mm 18G/20-50mm

|                   |              |                             |
|-------------------|--------------|-----------------------------|
| Semi-Professional | Code: DGN50V | BEST VALUE                  |
|                   | Code: 1716   | Includes: 1000pcs 180 nails |

 180 (18G) Nails 20-50mm 
  60-100 
  1.2kg 
  Carry Case 
  Trade = 1 Unit  
Transit = 6 Units

All professional fully featured tool including a depth adjuster. Comfortable fast and lightweight. Specified by trade professionals throughout Europe, this model is already a Tacwise best seller.

NEW



### 50mm Finish Nailer

15G/15-50mm 160/15-50mm 16G/15-50mm

Production Line Code: EHS50V BEST VALUE

15G Hard Steel & 160 (16G) Nails 15-50mm  
 70-120 2.4kg Carry Case Trade = 1 Unit  
 Transit = 4 Units

Firing both hardened 15G and any 16G (160) straight finish nails from 15-50mm, this specialist nailer is one of a kind. Featuring a convenient depth adjustment wheel and quick release nose gate, it will drive fasteners into wood and concrete surfaces with speed. With a rubber handle grip and handy adjustable exhaust cap, this finish nailer is comfortable and easy to use.



### 50mm Finish Nailer 160/20-50mm 16G/20-50mm

Production Line Code: DFN50V BEST VALUE

160 (16G) Nails 20-50mm 70-120 1.8kg Carry Case Trade = 1 Unit  
 Transit = 5 Units

Offering excellent value and widely used in the furniture manufacturing industry, this ergonomic model delivers peak performance. Fast and accurate, this finish nailer comes with a flush, quick release nose gate designed to avoid obstructing tool access in tight spaces. With essential user features it's reliable and demanded for volume nailing tasks.



### 50mm Combi Nailer/Stapler

180/20-50mm 18G/20-50mm 90/15-40mm

Production Line Code: 1326 BEST VALUE

180 (18G) Nails 20-50mm 70-120 1.7kg Carry Case Trade = 1 Unit  
 90 Staples 15-40mm Transit = 6 Units

A fast and versatile air nailer/stapler firing both 18G nails and 90 type narrow crown staples. Comes with a quick release nose gate, depth adjuster and 360° adjustable exhaust port as standard. This high-quality air-powered nailer/stapler is ideal for a huge range of tasks.



Watch the GFN64V video

### 64mm Finish Nailer 160/20-64mm 16G/20-64mm

Production Line Code: GFN64V BEST VALUE


160 (16G) Nails 20-64mm 70-100 1.8kg Carry Case Trade = 1 Unit  
 Transit = 4 Units

Versatility at its best. Uses 20-64mm nails without requiring any magazine adjustment. Features a nailing depth control and a special front opening jam clearance system to keep 'downtime' to a minimum.




A comprehensive programme of accurate and reliable fine nailing tools and fastenings designed to satisfy the demands of a huge range of woodworking applications.

## 180 (18G) nails



| Code | Nail Length/Type        | Box Qty | For Use In   |
|------|-------------------------|---------|--|
| 0205 | 180(18G) selection pack | 4000    | C1832V, DGN50V, DGN50LHH, DGN50VHH                     |
| 0358 | 180(18G)/10mm           | 2000    | C1832V   |
| 0359 | 180(18G)/15mm           | 2000    |  |
| 0360 | 180(18G)/20mm           | 1000    | C1832V, DGN50V, DGN50LHH, DGN50VHH, 1326               |
| 0361 | 180(18G)/25mm           | 1000    | C1832V, DGN50V, DGN50LHH, DGN50VHH, Ranger 2 18G, 1326 |
| 1066 | 180(18G)/25mm s/steel   | 1000    |  |
| 0362 | 180(18G)/30mm           | 1000    |  |
| 1067 | 180(18G)/30mm s/steel   | 1000    | C1832V, DGN50V, DGN50LHH, DGN50VHH, 1326               |
| 0363 | 180(18G)/32mm           | 1000    |  |
| 0364 | 180(18G)/35mm           | 1000    | DGN50V, DGN50LHH, DGN50VHH, Ranger 2 18G, 1326         |
| 1068 | 180(18G)/35mm s/steel   | 1000    |  |
| 0747 | 180(18G)/40mm           | 1000    |  |
| 1156 | 180(18G)/50mm           | 1000    |  |

## 18G brad nails



NEW

NEW

NEW

NEW

NEW


NEW

NEW

NEW

|      |          |      |                              |
|------|----------|------|------------------------------|
| 0392 | 18G/10mm | 5000 | C1832V                       |
| 0393 | 18G/13mm | 5000 |                              |
| 1724 | 18G/14mm | 5000 |                              |
| 0394 | 18G/15mm | 5000 | C1832V, DGN50V               |
| 0395 | 18G/20mm | 5000 |                              |
| 0396 | 18G/25mm | 5000 | C1832V, DGN50V, Ranger 2 18G |
| 0397 | 18G/30mm | 5000 |                              |
| 0398 | 18G/32mm | 5000 | DGN50V, Ranger 2 18G         |
| 0399 | 18G/35mm | 5000 |                              |
| 0400 | 18G/40mm | 5000 | C1832V                       |
| 0401 | 18G/50mm | 5000 |                              |
| 1708 | 18G/15mm | 4000 | C1832V, DGN50V, 1326         |
| 1709 | 18G/20mm | 4000 |                              |
| 1710 | 18G/25mm | 4000 | DGN50V, 1326                 |
| 1711 | 18G/30mm | 4000 |                              |
| 1712 | 18G/32mm | 4000 | DGN50V, 1326                 |
| 1713 | 18G/35mm | 4000 |                              |
| 1714 | 18G/40mm | 4000 |                              |
| 1715 | 18G/50mm | 4000 |                              |

## 18G angled brad nails (500 Series)



|      |                  |      |                   |
|------|------------------|------|-------------------|
| 0823 | 500/20mm         | 5000 | BeA SKAM 350-226C |
| 0824 | 500/25mm         | 5000 |                   |
| 0825 | 500/30mm         | 5000 |                   |
| 0826 | 500/35mm         | 5000 |                   |
| 0827 | 500/40mm         | 5000 |                   |
| 0828 | 500/45mm         | 5000 |                   |
| 0829 | 500/50mm         | 5000 |                   |
| 1131 | 500/20mm s/steel | 1000 |                   |
| 1132 | 500/30mm s/steel | 1000 |                   |
| 1133 | 500/35mm s/steel | 1000 |                   |
| 1134 | 500/40mm s/steel | 1000 |                   |
| 1135 | 500/50mm s/steel | 1000 |                   |

● Whilst stocks last




### 160 (16G) stainless steel finish nails

| Code | Nail Length/Type      | Box Qty |
|------|-----------------------|---------|
| 1096 | 160/(16G)32mm s/steel | 1000    |
| 1097 | 160/(16G)32mm s/steel | 1000    |
| 1098 | 160/(16G)32mm s/steel | 1000    |

#### For Use In

DFN50V, FFN64LHH, GFN64V, FCT50LHH, Ranger 2 16G



### 16G finish nails

|      |          |      |
|------|----------|------|
| 0665 | 16G/20mm | 2500 |
| 0666 | 16G/25mm | 2500 |
| 0293 | 16G/30mm | 2500 |
| 0294 | 16G/32mm | 2500 |
| 0295 | 16G/35mm | 2500 |
| 0296 | 16G/38mm | 2500 |
| 0319 | 16G/40mm | 2500 |
| 0297 | 16G/45mm | 2500 |
| 0298 | 16G/50mm | 2500 |
| 0299 | 16G/55mm | 2500 |
| 0300 | 16G/60mm | 2500 |
| 0301 | 16G/64mm | 2500 |

DFN50V, FFN64LHH, GFN64V, FCT50LHH, ESH50V


DFN50V, FFN64LHH, GFN64V, FCT50LHH, Ranger 2 16G, ESH50V

FFN64LHH, GFN64V, Ranger 2 16G

### 16G angled finish nails

|      |                  |      |
|------|------------------|------|
| 0769 | 16G/32mm         | 2500 |
| 1222 | 16G/32mm s/steel | 2500 |
| 0770 | 16G/38mm         | 2500 |
| 1223 | 16G/38mm s/steel | 2500 |
| 0771 | 16G/45mm         | 2500 |
| 1224 | 16G/45mm s/steel | 2500 |
| 0772 | 16G/50mm         | 2500 |
| 1225 | 16G/50mm s/steel | 2500 |
| 0773 | 16G/63mm         | 2500 |
| 1226 | 16G/63mm s/steel | 2500 |

DeWalt® DC618 & DCN660,  
Paslode® IM250A & IM65A F16 Nailers,  
Ranger 2 16G Inclined




### 15G 'D' head inclined finish nails

|      |           |      |
|------|-----------|------|
| 0402 | DA13/25mm | 4000 |
| 0403 | DA15/32mm | 4000 |
| 0404 | DA17/38mm | 4000 |
| 0405 | DA19/44mm | 4000 |
| 0406 | DA21/50mm | 4000 |
| 0407 | DA25/64mm | 4000 |

FBA50VCB

FBA50VCB, GDA64V, GBA64LHH, GDA64V2

GDA64V, GBA64LHH, GDA64V2



**NEW**

### 15G nails

|      |          |      |
|------|----------|------|
| 1530 | 15G/30mm | 1500 |
| 1531 | 15G/35mm | 1500 |
| 1532 | 15G/40mm | 1500 |
| 1533 | 15G/45mm | 1500 |
| 1534 | 15G/50mm | 1500 |

EHS50V

# 11 High performance coil nailers

## Unrivalled

Most Tacwise coil nailers fire 4+ nails per second and can be used single-handedly. This is because lightweight magnesium is used to manufacture many of the tool bodies and triple hardened internal parts facilitate rapid firing and excellent durability. Ergonomic design provides great balance and comfort. Neat touches, such as external top cap crash bars help to ensure less downtime than other nailers.

## Versatility

Popular for traditional nailing applications such as building sheds, fence panels and pallets. Coil nailers are a brilliant time-saving solution for any number of nailing applications where speed and efficiency are desirable. High capacity magazines contain a large volume of nails and offer continuous effective operation.

Increasingly demanded within the construction industry, the ability to fire up to 400 nails without re-loading increases productivity and makes coil nailing the preferred option compared to strip nailers, which only load around 100 nails at a time.

All Tacwise coil nailers up to 90mm are light enough for single-handed operation.



# Coil Nailers

## Serious About Coil Nailing

Tacwise places a great deal of focus on this important product category, with an extensive range covering most major and niche applications. We also have a comprehensive fastening programme to meet the demands of our dealer network and their largest users.





## 50mm Mini Coil Nailer

**Production Line** Code: DCN50LHH2

-  2.1 Conical Coil Nails 27-50mm
-  70-120
-  1.5kg
-  Retail Box
-  Trade = 1 Unit  
Transit = 5 Units

An exceptional tool for 2.1 diameter round head nails. Weighing 1.5kg it will still countersink a 45mm ring shank nail. Compact design with a single or bump fire trigger. Very popular in the fencing, shed and flooring industry. Will also load plastic collated coil nails 27-50mm. Tool now supplied in silver colour and not orange.

## 50mm Coil Nailer

**Production Line** Code: FCN50LHH2

-  2.1 Flat & Conical Coil Nails 22-50mm
-  60-120
-  2kg
-  Retail Box
-  Trade = 1 Unit  
Transit = 2 Units

Weighing only 2kg, this tool offers exceptional speed and will take 27-50mm flat head nails and 22-50mm conical head nails making it ideal for fencing and shed manufacture. Single or bump fire trigger. Tool now supplied in silver colour and not orange.



## 55mm Coil Nailer

**Production Line** Code: FCN55V **BEST VALUE**

-  2.1-2.5 Flat & Conical Coil Nails 25-57mm
-  70-120
-  2.4kg
-  Carry Case
-  Trade = 1 Unit  
Transit = 4 Units

The FCN55V Coil Nailer allows you to change between both conical and flat top coils, without the need for adjustment. Supplied with a newly improved lightweight magazine, offering extra strength and reliability. Lightweight at just 2.4kg, this tool can fire up to 57mm nails with ease.

## 57mm Coil Nailer

**Production Line** Code: GCN57P **BEST VALUE**

-  2.1-2.3 Flat Coil Nails 25-57mm
-  70-120
-  2.7kg
-  Carry Case
-  Trade = 1 Unit  
Transit = 4 Units

An extremely heavy duty workhorse, this tough production line tool has a highly developed construction and specification, firing approximately 400 nails without reloading. Contact trip trigger. Suitable for exhibition, pallet, crate and packaging industries.







### 70mm Coil Nailer

|                 |              |            |
|-----------------|--------------|------------|
| Production Line | Code: GCN70V | BEST VALUE |
|-----------------|--------------|------------|

-  2.3-2.9 Flat Coil Nails 40-70mm
-  70-120
-  3.7kg
-  Carry Case
-  Trade = 1 Unit  
Transit = 2 Units

This tough production line tool has a highly developed construction and specification, firing up to 300 nails without reloading. Contact trip trigger. Tool ideal for the pallet and packaging industries.

### 83mm Coil Nailer

|                 |              |            |
|-----------------|--------------|------------|
| Production Line | Code: HCN83P | BEST VALUE |
|-----------------|--------------|------------|

-  2.5-3.3 Flat Coil Nails 40-83mm
-  70-120
-  3.9kg
-  Carry Case
-  Trade = 1 Unit  
Transit = 2 Units

Robust traditional tool for reliable and tough continuous nailing. Especially hardened working parts ensure a long and productive life. Developed for the rugged pallet and case industries in particular.



### 90mm Air Coil Nailer

|                 |              |            |
|-----------------|--------------|------------|
| Production Line | Code: JCN90V | BEST VALUE |
|-----------------|--------------|------------|

**NEW**

-  2.5-3.3 Flat Coil Nails 50-90mm
-  70-120
-  3.5kg
-  Carry Case
-  Trade = 1 Unit  
Transit = 2 Units

Extremely versatile, this tool accepts a wide range of nail diameters and lengths, firing up to 275 nails in a single or bump firing mode. Super lightweight magnesium alloy body for the ultimate power to weight ratio. Constructed for a range of heavy-duty and manufacturing applications.

# Air Coil Nailers

Nailing up to 65mm

High Durability Driver Blade

Counter Sinking Adjustment

Drives 22 Different Nails Without Adjustment

## 65mm Coil Nailer

Production Line Code: HCN65P BEST VALUE



2.3-2.9 Flat Coil Nails 32-65mm



70-120



2.5kgs



Carry Case



Trade = 1 Unit  
Transit = 4 Units

Outstanding power to weight ratio. Sinking a 65mm ring nail, this tough production line tool accepts both reduced head and standard (7mm diameter) head nails. Fires up to 350 nails without reloading.



### Put to the test


We admit it; we're tough on our products. We have to be when they're used in busy industrial environments. They need to be able to withstand the toughest treatment, which is why we painstakingly stress test every new item and why we then manually test every single tool

### Outstanding Quality and Performance

Sophisticated progressive tooling, intelligent electronic engineering and a commitment to precision and detail, create the greatest air tacker programme available worldwide. Our dedication to quality begins in the initial stages of design with every component machined to extraordinary precision for years of trouble-free use.

# High Performance Coil Nails

Increasingly demanded within the construction industry, the ability to fire up to 400 nails without re-loading increases productivity.




| Point Varieties |       | Shank Varieties                        |            |             | Nail Surface Treatments                     |  | Euro code 5 CE Service class 2 (CE2/12+)   |
|-----------------|-------|--|------------|-------------|---|--|--|
|                 |       |  |            |             | <b>Bright:</b><br>Untreated<br>(no coating) | <b>Galvanised (Galv.)</b><br>Electroplated zinc coating<br>approx. 6-8 microns | <b>Extra Galvanised (Extra Galv.)</b><br>Rust protected by electroplated<br>zinc coating 12+ microns |
| Diamond         | Blunt | Smooth Shank -<br>smooth plain surface | Ring Shank | Screw Shank |   |  |  |

# Coil Nails/Strip Nailer | Nailing up to 90mm

## Coil nails wire collated flat top

| Code | Nail Length/Type                    | Box Qty | For Use In   |
|------|-------------------------------------|---------|--|
| 1229 | 2.1 25mm galv., ring                | 14,400  | GCN57P, FCN55V   |
| 0993 | 2.1 30mm bright, ring               | 14,400  | FCN50LHH2, GCN57P, FCN55V                                |
| 1230 | 2.1 32mm galv., ring                | 14,400  | FCN50LHH2, GCN57P, FCN55V, FCN65V, HCN65P                |
| 0994 | 2.1 35mm bright, ring               | 14,400  |  |
| 1518 | 2.1 35mm galv., ring blunt          | 14,400  |  |
| 0995 | 2.1 40mm bright, ring               | 14,400  |  |
| 0996 | 2.1 40mm galv, ring                 | 14,400  |  |
| 0997 | 2.1 45mm bright, ring               | 14,400  |  |
| 0998 | 2.1 45mm galv, ring                 | 14,400  |  |
| 0999 | 2.1 50mm bright, ring               | 14,400  |  |
| 0495 | 2.1 50mm galv., ring                | 14,400  |  |
| 0279 | 2.3 50mm bright, ring               | 9000    |  |
| 0421 | 2.5 45mm bright, ring               | 9000    | FCN55V, HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH         |
| 0422 | 2.5 50mm bright, ring               | 9000    | FCN55V, HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH, JCN90V |
| 0423 | 2.5 50mm galv., ring                | 9000    |  |
| 0424 | 2.5 55mm bright, ring               | 9000    |  |
| 0425 | 2.5 60mm bright, ring               | 9000    |  |
| 0427 | 2.5 64mm bright, ring               | 9000    |  |
| 1074 | 2.5 64mm bright, smooth             | 9000    | HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH, JCN90V         |
| 0428 | 2.5 64mm galv., ring                | 9000    |  |
| 1548 | 2.5 64mm s/steel, ring              | 9000    |  |
| 1093 | 2.5 70mm bright, smooth             | 9000    |  |
| 0429 | 2.7 64mm bright, ring               | 6000    | HCN65P, GCN70V, HCN83P, JCN90XHH, JCN90V                 |
| 0430 | 2.7 75mm bright, ring               | 6000    | HCN83P, JCN90XHH, JCN90V                                 |
| 0777 | 2.8 50mm CE2/12+ micron galv., ring | 4000    | HCN65P, GCN70V, HCN83P, JCN90XHH, JCN90V                 |
| 0964 | 2.8 64mm CE2/12+ micron galv., ring | 4000    |  |
| 0965 | 2.8 83mm bright, ring               | 4000    | HCN83P, JCN90XHH, JCN90V                                 |
| 0433 | 3.1 90mm CE2/12+ micron galv., ring | 4000    | JCN90XHH, LCN130V, JCN90V                                |
| 1021 | 3.1 90mm bright., ring              | 4000    |  |
| 1036 | 3.3 65mm CE2/12+ micron galv., ring | 4000    | HCN83P, JCN90XHH, JCN90V                                 |
| 1035 | 3.3 75mm CE2/12+ micron galv., ring | 4000    | HCN83P, JCN90XHH, LCN130V, JCN90V                        |
| 1154 | 3.3 98mm bright ring                | 4000    | LCN130V  |
| 1155 | 3.8 130mm bright screw              | 1500    |  |


(actual size)



## Coil nails wire collated conical top

|      |                              |        |                                      |
|------|------------------------------|--------|--------------------------------------|
| 1128 | 2.1 22mm galv., ring blunt   | 14,400 | FCN50LHH2                            |
| 1000 | 2.1 27mm galv., ring blunt   | 14,400 | DCN50LHH2, FCN50LHH2, FCN55V         |
| 1001 | 2.1 32mm bright, ring        | 14,400 | DCN50LHH2, FCN50LHH2, FCN55V, FCN65V |
| 1002 | 2.1 32mm galv., ring         | 14,400 |                                      |
| 1545 | 2.1 32mm s/steel, ring       | 14,000 |                                      |
| 1003 | 2.1 32mm galv., ring blunt   | 14,400 |                                      |
| 1516 | 2.1 35mm galv., ring         | 14,400 |                                      |
| 1517 | 2.1 35mm galv., ring conical | 14,400 |                                      |
| 1004 | 2.1 38mm bright, ring        | 14,400 |                                      |
| 1005 | 2.1 38mm galv., ring         | 14,400 |                                      |
| 1546 | 2.1 38mm s/steel, ring       | 14,400 |                                      |
| 1006 | 2.1 38mm galv., ring blunt   | 14,400 |                                      |
| 1008 | 2.1 45mm bright, smooth      | 14,400 |                                      |
| 1009 | 2.1 45mm galv., ring         | 14,400 |                                      |
| 1547 | 2.1 45mm s/steel, ring       | 14,400 |                                      |
| 1010 | 2.1 45mm galv., ring blunt   | 14,400 |                                      |
| 1011 | 2.1 50mm bright, ring        | 14,400 |                                      |
| 1012 | 2.1 50mm galv., ring         | 14,400 |                                      |

(actual size)



● Whilst stocks last

# Strip Nailers

Perfect for roofing and framing

The ultimate range of angled strip nailers, offering sheer power, outstanding performance and reliability. An essential for all those tough jobs.

## 90mm 34° Angled Strip Nailer

Professional

Code: KDH90V

BEST VALUE



2.8-3.7mm diameter  
34° Paper Collated 'D'  
Head Strip Nail/50-90mm



70-120



3.8kg



Carry Case



Trade = 1 Unit  
Transit = 2 Units

Extremely powerful, reliable and with virtually no recoil this 34° 'D' head strip nailer is very popular with timber frame house builders and is perfect for a wide variety of first fix roofing applications.

Air Flow Technology



Open (Viewable) Magazine System



# Strip Nailer/Strip Nails | Nailing up to 90mm

## 90mm 21° Angled Strip Nailer

Production Line

Code: KSN90V

BEST VALUE

NEW

2.9-3.3mm Diameter  
21° Plastic Collated  
Strip Nails 50-90mm



70-120



3.7kg



Carry Case




Trade = 1 Unit  
Transit = 2 Units

Heavy-duty 21° inclined strip nailer, with a single or bump firing mode. Designed to bring power and reliability to a wide variety of structural first fix joinery and framing applications. The lightweight angled magazine provides easy access in all frame construction applications day in, day out.




# Strip Nails



### Strip nails plastic collated (22° inclined round head)

| Code | Nail Length/Type                      | Box Qty | For Use In                  |
|------|---------------------------------------|---------|-----------------------------|
| 0435 | 2.9 50mm CE2/12+ micron galv., screw  | 3000    | JSN90MHH2, JSN00LHH, KSN90V |
| 0436 | 3.1 90mm CE2/12+ micron galv., screw  | 3000    |                             |
| 0437 | 3.3 65mm CE2/12+ micron galv., screw  | 3000    |                             |
| 0438 | 3.3 75mm CE2/12+ micron galv., screw  | 3000    |                             |
| 0439 | 3.4 100mm CE2/12+ micron galv., screw | 3000    | JSN00LHH                    |



### Strip nails paper collated (34° inclined 'D' head)


|      |                                      |      |                            |
|------|--------------------------------------|------|----------------------------|
| 1124 | 2.8 50mm CE2/12+ micron galv., ring  | 3300 | KDH90V, KDH90XHH, JDH90FHH |
| 1125 | 2.8 65mm CE2/12+ micron galv., ring  | 3300 |                            |
| 1120 | 3.1 65mm CE2/12+ micron galv., ring  | 2200 |                            |
| 1121 | 3.1 75mm CE2/12+ micron galv., ring  | 2200 |                            |
| 1122 | 3.1 90mm CE2/12+ micron galv., plain | 2200 |                            |
| 1123 | 3.1 90mm CE2/12+ micron galv., ring  | 2200 |                            |
| 1721 | 3.1 65mm CE2/12+ micron galv., ring  | 1600 |                            |
| 1722 | 3.1 75mm CE2/12+ micron galv., ring  | 1600 |                            |
| 1723 | 3.1 90mm CE2/12+ micron galv., ring  | 1600 |                            |

NEW

NEW

NEW

● Stock arriving May 2023



### Positive placement nails paper collated (34° inclined round head)

|      |                                    |      |          |
|------|------------------------------------|------|----------|
| 0984 | 3.75 38mm CE/12 micron galv., ring | 3000 | FRH38THH |
|------|------------------------------------|------|----------|

## Variations of air tool triggers

Any tool likely to be used to fire higher volumes of fasteners at speed will almost always be capable of bump firing or (in the case of very small upholstery type tools) require no additional safety system other than the standard single or double trigger. A sequential or single shot trigger will usually be fitted where exact placement of the fastener is most important.



### Sequential firing

This system also requires the nose safety to be depressed against the surface. However, this **MUST** be done prior to activating the trigger or the tool will not fire. This means that even if the trigger is held up, the tool will not fire if the safety contacts a surface either accidentally or on purpose.

With a sequential safety it is possible for the tool to continue to be fired all the time the nose safety is depressed against the work surface. Once released the exact same sequence (hence sequential firing) must be repeated in order to fire any additional fastenings.

For speed firing, you may choose to leave the nose pressed against the work surface with the nose safety depressed and slide the tool along the work piece whilst activating the trigger.



### Safety trigger

This is purely a safety locking device whereby the main trigger cannot be activated until the secondary trigger is depressed.

### Single shot firing

This safety mechanism will only ever allow one fastener to be fired at a time. To fire the next fastener, the nose safety needs to be lifted from the work surface and the trigger allowed to reset.

### Contact trip (bump firing)

This allows a fastener to be fired whenever both the nose safety trip and trigger are activated simultaneously. Consequently, fasteners can be fired at speed by holding up the trigger and repeatedly bumping the nose against the workpiece (referred to as bump firing). Effectively the tool drives a fastener each time it is 'bumped'.

The contact trip (nose safety) still prevents a fastener from being fired if it is not depressed against the work surface, however, if the trigger is activated and the nose safety trip accidentally touches against an object or person, a fastener will be fired. Therefore, **UNDER NO CIRCUMSTANCES** should an operator hold or carry a tool around with the trigger depressed.

Unless reasonable downward pressure is maintained on the nose safety after firing, it is possible for certain tools to recoil back from the work surface and then fire again on re-contact (only if the operator continues to hold up the trigger).

To prevent this from happening, these tools should be allowed to recoil far enough to release the contact trip and avoid a repeat cycle of the driver, which fires a fastener. It is possible to purchase a single shot trigger (usually red) for most contact trip tools in the Tacwise range – please contact our service department for details.

## Choosing the correct fastening length

The type and thickness of the material you are using will determine the length of staple or nail that is needed.

### General Rule

When stapling and nailing, the fastener should be 3 times longer than the material to be fixed. If you are nailing, a further 5mm should be added to the length of the nail.



### Hardwood/Material

When stapling and nailing into hardwood, a staple that is twice the depth of the material you are fixing will be adequate. If you are nailing make sure that the nail is 3 times the length of the material.



### Thin Material/Fabric

When stapling into thin material or fabric, a staple that is 4mm longer than the material is perfect. When nailing, choose a nail that is 6mm longer than the material.



## Specifications

|                        | Stapling Machines<br>General Purpose & Upholstery |        |           |         |        |         |         | Narrow<br>Crown |        |        | Heavy Duty, Wide<br>Crown & Corr. Fastener |        |        |          |
|------------------------|---|--------|-----------|---------|--------|---------|---------|-----------------|--------|--------|--|--------|--------|----------|
|                        | A7116LN   | A7116V | A7116AUTO | A7116P  | A8016V | A8016LN | A14014V | C9725V          | C9032V | D9040V | G1450V                                     | F1450M | G1738V | FCF15XCB |
| Depth (mm)             | 230   | 218    | 216       | 218     | 218    | 230     | 235     | 248             | 273    | 302    | 368  | 360    | 330    | 300      |
| Width (mm)             | 45  | 43     | 38        | 43      | 43     | 45      | 46      | 55              | 67     | 88     | 97   | 78     | 80     | 87       |
| Height (mm)            | 220   | 150    | 149       | 152     | 150    | 220     | 159     | 192             | 231    | 253    | 290  | 272    | 252    | 270      |
| Weight (kg)            | 1.1   | 0.9    | 0.9       | 0.8     | 0.9    | 1.1     | 0.9     | 1.2             | 1.2    | 1.7    | 2.0  | 1.9    | 2.4    | 2.6      |
| Takes staple/nail type | 71  | 71     | 71        | 71      | 80     | 80      | 140     | 97              | 90     | 90     | 14   | 14     | 17     | CF       |
| Fasteners length (mm)  | 4-16  | 4-16   | 5-16      | 4-16    | 4-16   | 4-16    | 4-14    | 10-25           | 12-32  | 15-40  | 19-50                                      | 19-50  | 16-38  | 9-15     |
| Capacity               | 180   | 180    | 150       | 180     | 150    | 150     | 150     | 125             | 100    | 100    | 150  | 150    | 140    | 80       |
| Max dBA sound/noise    | 77  | 77     | 77        | 77      | 77     | 77      | 77      | 86              | 88     | 88     | 90   | 85     | 86     | 80       |
| PSI                    | 60-100  | 60-100 | 60-100    | 60-100  | 60-100 | 60-100  | 60-100  | 60-100          | 60-100 | 60-100 | 70-120                                     | 70-120 | 70-120 | 65-115   |
| Trigger                | SS  | SS     | SS/Auto   | SS/Auto | SS     | SS      | SS      | CT              | CT     | CT/S   | CT/S                                       | CT     | CT     | CT       |

## Features

|                                     |   |   |   |   |   |   |   |   |   |   |   |   |   |   |
|-------------------------------------|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360° adjustable exhaust port        |   |   |   |   |   |   |   |   | • | • | • |   | • |   |
| Bottom loading                      | • | • | • | • | • | • | • |   |   |   |   |   |   |   |
| Depth control countersinking        |   |   |   |   |   |   |   |   | • | • | • |   |   |   |
| Double power cylinder system        |   |   |   |   |   |   |   |   |   |   | • | • | • |   |
| Double safety trigger               |   | • | • |   | • |   | • |   |   |   |   |   |   |   |
| Easy top loading system             |   |   |   |   |   |   |   |   |   |   | • | • | • |   |
| Extra long nose                     | • |   |   |   |   | • |   |   |   |   |   |   |   |   |
| High capacity magazine/nail drum    | • | • | • | • | • | • | • | • | • | • | • | • | • |   |
| High durability driver blade system | • | • | • | • | • | • | • | • | • | • | • | • | • | • |
| Neat rear exhaust system            | • | • | • | • | • | • |   |   |   |   |   | • |   |   |
| Non marking nose                    |   |   |   |   |   |   |   |   | • | • | • | • |   |   |
| Open (viewable) magazine system     |   |   |   |   |   |   |   | • | • | • | • | • |   |   |
| Protective bumper                   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |
| Quick release nose gate             |   |   |   |   |   |   |   | • | • | • | • |   | • |   |
| Quick release reloading system      |   | • | • | • | • |   | • |   |   |   |   |   |   |   |
| Safety yoke to avoid slippage       |   |   |   |   |   |   |   |   |   |   |   |   |   |   |
| Side quick release loading system   |   |   |   |   |   |   |   |   | • | • |   |   | • |   |
| Single shot trigger                 | • | • | • |   | • | • | • | • |   |   |   |   |   |   |
| Slender length nose                 | • | • | • | • | • | • | • | • | • | • |   |   |   |   |
| Soft rubber safety grip             | • | • | • | • | • | • | • | • | • | • | • | • | • | • |
| Staple/nail refill window           |   |   |   |   |   |   |   |   |   |   |   |   |   |   |
| Variable speed control              |   |   | • |   |   |   |   |   |   |   |   |   |   |   |

ST Safety Trigger  
 CT Contact Trip (Bump Fire)  
 SE Sequential  
 SS Single Shot  
 SS/CT Single Shot/Contact Trip  
 CT/S Contact Trip/Sequential  
 SS/Auto Single Shot/Auto

**BEST VALUE**



**Nailers & Pinners**

**Coil Nailers**

**Strip Nailers**

| A6422V       | A6435        | C1832V      | DGN50V      | EHS50V     | DFN50V      | 1326       | GDA64V2    | GFN64V      | DCN50LHH2  | FCN50LHH2   | FCN55V      | GCN57P      | HCN65P      | GCN70V      | HCN83P      | JCN90V      | LCN130V     | KDH90V      | KSN90V        |
|--------------|--------------|-------------|-------------|------------|-------------|------------|------------|-------------|------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|---------------|
| 205          | 240          | 273         | 273         | 321        | 302         | 266        | 340        | 292         | 260        | 305         | 305         | 380         | 305         | 330         | 305         | 360         | 370         | 470         | 530           |
| 45           | 44           | 67          | 67          | 91         | 88          | 67         | 100        | 88          | 108        | 128         | 130         | 130         | 130         | 132         | 132         | 127         | 165         | 150         | 124           |
| 170          | 162          | 228         | 249         | 290        | 270         | 262        | 315        | 295         | 284        | 294         | 302         | 290         | 312         | 308         | 340         | 362         | 479         | 364         | 364           |
| 0.8          | 0.9          | 1.1         | 1.2         | 2.4        | 1.7         | 1.7        | 2          | 1.8         | 1.5        | 2.0         | 2.4         | 2.7         | 2.5         | 3.7         | 3.9         | 3.5         | 6.5         | 3.8         | 3.7           |
| 23G/<br>0.64 | 23G/<br>0.64 | 18G/<br>180 | 18G/<br>180 | 15G        | 16G/<br>160 | 18G/<br>90 | 15G        | 16G/<br>160 | 2.1        | 2.1-<br>2.5 | 2.1-<br>2.5 | 2.1-<br>2.3 | 2.3-<br>2.9 | 2.3-<br>2.9 | 2.5-<br>3.3 | 2.5-<br>3.3 | 3.1-<br>3.8 | 2.8-<br>3.7 | 2.87-<br>3.33 |
| 12-<br>22    | 12-<br>35    | 10-<br>32   | 20-<br>50   | 15-<br>50  | 20-<br>50   | 15-<br>50  | 32-<br>64  | 20-<br>64   | 22-<br>50  | 27-<br>50   | 25-<br>57   | 25-<br>57   | 32-<br>65   | 40-<br>70   | 38-<br>83   | 50-<br>90   | 75-<br>130  | 50-<br>90   | 50-<br>90     |
| 100          | 170          | 100         | 100         | 100        | 100         | 100        | 100        | 100         | 400        | 400         | 300-<br>400 | 300-<br>400 | 250-<br>350 | 250-<br>350 | 250-<br>300 | 225-<br>275 | 225-<br>300 | 75-<br>95   | 65-<br>70     |
| 77           | 77           | 81          | 86          | 82         | 86          | 91         | 99.5       | 89          | 83         | 96          | 96          | 96          | 96          | 83          | 95          | 108         | 98          | 86          | 106           |
| 60-<br>100   | 60-<br>100   | 60-<br>100  | 60-<br>100  | 65-<br>120 | 70-<br>120  | 60-<br>100 | 70-<br>120 | 70-<br>120  | 70-<br>120 | 60-<br>120  | 70-<br>120  | 60-<br>120  | 70-<br>120  | 70-<br>120  | 70-<br>120  | 70-<br>120  | 70-<br>100  | 70-<br>120  | 70-<br>120    |
| SE           | ST           | CT          | CT          | CT         | CT          | CT         | CT/S       | CT/S        | SS/CT      | SS/CT       | CT/S        | CT          | CT/S        | CT          | CT          | CT/S        | SS          | CT/S        | CT/S          |
| •            |              | •           | •           | •          | •           | •          | •          | •           | •          | •           | •           | •           | •           |             | •           | •           |             | •           | •             |
|              |              | •           | •           | •          |             | •          | •          |             | •          | •           | •           |             | •           |             |             | •           |             | •           | •             |
|              |              |             |             | •          |             | •          |            |             |            |             |             |             |             |             |             |             |             |             |               |
|              |              |             |             |            |             | •          |            |             |            |             |             |             |             |             |             |             |             |             |               |
|              |              |             |             |            |             | •          |            |             |            |             |             |             |             |             |             |             |             |             |               |
|              | •            | •           | •           | •          | •           |            |            | •           | •          | •           | •           | •           | •           | •           | •           | •           | •           | •           | •             |
| •            | •            | •           | •           | •          | •           | •          | •          | •           | •          | •           | •           | •           | •           | •           | •           | •           | •           | •           | •             |
|              | •            | •           | •           |            |             | •          | •          | •           | •          | •           | •           |             | •           |             |             | •           |             | •           | •             |
|              |              |             |             |            |             |            |            |             |            |             |             |             |             |             |             |             |             |             |               |
|              |              |             |             |            |             |            |            |             |            |             |             |             |             |             |             |             |             |             |               |
|              | •            | •           | •           |            |             |            |            | •           | •          | •           | •           |             | •           |             |             |             | •           | •           | •             |
| •            | •            | •           | •           | •          | •           | •          | •          | •           | •          | •           | •           | •           | •           | •           | •           | •           | •           | •           | •             |
|              | •            |             | •           | •          |             | •          | •          |             |            |             |             |             |             |             |             | •           |             |             | •             |

| Applications                    | Stapling Machines<br>General Purpose & Upholstery |        |           |        |        |         | Narrow<br>Crown |        |        | Heavy Duty, Wide<br>Crown & Corr. Fastener |        |        |        |          |
|---------------------------------|---|--------|-----------|--------|--------|---------|-----------------|--------|--------|--|--------|--------|--------|----------|
|                                 | A7116LN   | A7116V | A7116AUTO | A7116P | A8016V | A8016LN | A14014V         | C9725V | C9032V | D9040V                                     | G1450V | F1450M | G1738V | FCF15XCB |
| Attaching mesh netting to wood  | •   | •      | •         | •      | •      | •       | •               | •      | •      | •  |        |        |        |          |
| Bed frames                      |   |        |           |        |        |         |                 |        |        |  | •      | •      |        |          |
| Cabins, mobile homes, caravans  |   |        |           |        |        |         |                 | •      | •      | •  | •      | •      | •      | •        |
| Cane/rattan furniture           |   |        |           |        |        |         |                 | •      | •      | •  |        |        |        |          |
| Carpet/underlay/gripper         |   |        |           |        |        |         | •               |        |        |  |        |        |        |          |
| Coffin linings                  | •   | •      | •         | •      | •      | •       | •               |        |        |  |        |        |        |          |
| Coffin manufacture              |   |        |           |        |        |         | •               | •      | •      | •  | •      | •      | •      | •        |
| Drawer/cabinet bottoms          |   |        |           |        |        |         |                 | •      | •      | •  |        |        |        |          |
| Exhibition/show construction    |   |        |           |        |        |         | •               | •      | •      | •  |        |        |        |          |
| Exhibition/show upholstery      | •   | •      | •         | •      | •      | •       | •               |        |        |  |        |        |        |          |
| Fencing                         |   |        |           |        |        |         |                 |        |        |  | •      | •      |        |          |
| Fixing underlayment             |   |        |           |        |        |         | •               |        | •      | •  |        |        |        |          |
| Furniture frames                |   |        |           |        |        |         |                 |        |        |  | •      | •      |        |          |
| Insulation and lining           | •   | •      | •         | •      | •      | •       | •               |        |        |  |        |        |        |          |
| Kitchen and bedroom furniture   |   |        |           |        |        |         |                 | •      | •      | •  | •      | •      |        |          |
| Office screens                  | •   | •      | •         | •      | •      | •       | •               |        |        |  |        |        |        |          |
| Pallet/packing case manufacture |   |        |           |        |        |         |                 |        |        |  | •      | •      | •      |          |
| Panelling                       |   |        |           |        |        |         |                 | •      | •      | •  |        |        |        |          |
| Pelmets, blinds and awnings     | •   | •      | •         | •      | •      | •       | •               |        |        |  |        |        |        |          |
| Pet cages, runs and enclosures  |   |        |           |        |        |         | •               | •      | •      | •  |        |        |        |          |
| Plasterboard                    |   |        |           |        |        |         |                 |        | •      | •  |        |        |        |          |
| Presentation boxes              |   |        |           |        |        |         |                 | •      | •      | •  |        |        |        |          |
| Roofing felt                    |   |        |           |        | •      | •       | •               |        |        |  |        |        |        |          |
| Sheds and garden buildings      |   |        |           |        |        |         | •               |        |        |  | •      | •      |        |          |
| Shoe repair                     |   |        |           |        |        |         |                 | •      | •      | •  |        |        |        |          |
| Sign manufacture                |   |        |           |        | •      | •       |                 |        |        | •  | •      | •      | •      |          |
| Staircases and banisters        |   |        |           |        |        |         |                 |        | •      | •  | •      | •      |        |          |
| Subflooring and plywood         |   |        |           |        |        |         |                 |        | •      | •  |        |        |        |          |
| Theatre and film scenery        | •   | •      | •         | •      | •      | •       | •               | •      | •      | •  | •      | •      |        | •        |
| Trellis work                    |   |        |           |        |        |         |                 |        |        | •  |        |        |        |          |
| Tubs and barrels                |   |        |           |        |        |         |                 |        |        |  | •      | •      | •      |          |
| Upholstery and re-upholstery    | •   | •      | •         | •      | •      | •       | •               |        |        |  |        |        |        |          |
| Window display/shop fitting     | •   | •      | •         | •      | •      | •       | •               | •      |        |  | •      | •      | •      |          |
| Window frames and beading       |   |        |           |        |        |         |                 |        |        |  |        |        |        | •        |


**BEST VALUE**

|                                   | Nailers & Pinners |       |        |        |        |        |      |         |        | Coil Nailers |           |        |        |        |        |        | Strip Nailers |         |        |        |
|-----------------------------------|-------------------|-------|--------|--------|--------|--------|------|---------|--------|--------------|-----------|--------|--------|--------|--------|--------|---------------|---------|--------|--------|
|                                   | A642V             | A6435 | C1832V | DGN50V | EHS50V | DFN50V | 1326 | GDA64V2 | GFN64V | DCN50LHH2    | FCN50LHH2 | FCN55V | GCN57P | HCN65P | GCN70V | HCN83P | JCN90V        | LCN130V | KDH90V | KSN90V |
| Beading and picture/mirror frames |                   | •     | •      | •      |        |        | •    |         | •      |              |           |        |        |        |        |        |               |         |        |        |
| Boat building                     |                   |       |        | •      |        |        |      | •       | •      |              |           |        |        |        |        |        |               |         | •      |        |
| Cabins, mobile homes, caravans    | •                 | •     |        | •      |        |        |      | •       | •      | •            | •         | •      | •      | •      | •      |        |               |         | •      |        |
| Cable drums and steel skids       |                   |       |        |        |        |        |      |         |        |              |           |        |        |        |        |        |               | •       |        |        |
| Cane/rattan furniture             |                   |       |        | •      |        |        |      |         |        |              |           |        |        |        |        |        |               |         |        |        |
| Coffin manufacture                |                   | •     | •      | •      |        |        | •    | •       | •      |              |           |        |        |        |        |        |               |         |        |        |
| Construction                      |                   |       |        |        | •      |        |      |         |        |              |           |        |        | •      | •      | •      | •             | •       | •      | •      |
| Decking                           |                   |       |        |        |        |        |      | •       | •      | •            | •         | •      |        |        | •      | •      |               |         | •      |        |
| Display and shop fitting          | •                 | •     | •      | •      | •      | •      | •    | •       | •      |              | •         |        |        |        |        |        |               |         |        |        |
| Door frames and skirting          |                   |       | •      | •      | •      | •      | •    | •       | •      |              | •         |        |        |        |        |        |               |         |        |        |
| Exhibition/show construction      |                   |       | •      | •      | •      | •      | •    | •       | •      | •            | •         |        |        |        | •      |        |               |         |        |        |
| Fencing                           |                   |       | •      | •      |        | •      |      | •       | •      | •            | •         | •      | •      | •      | •      |        | •             | •       | •      | •      |
| Fire surrounds                    | •                 |       | •      | •      | •      |        |      |         |        |              |           |        |        |        |        |        |               |         |        |        |
| Fixing gripper and thresholds     |                   |       |        |        | •      | •      |      |         |        |              | •         |        |        |        |        |        |               |         |        |        |
| Furniture/woodwork assembly       | •                 |       | •      | •      |        |        | •    | •       | •      |              |           |        |        |        |        |        |               |         |        |        |
| Insulation and lining             |                   |       |        |        |        |        |      |         | •      |              |           |        |        |        |        |        |               |         |        |        |
| Kitchen and bedroom furniture     | •                 | •     | •      | •      |        | •      | •    | •       | •      |              | •         |        |        |        |        |        |               |         |        |        |
| Pallet/packing case manufacture   |                   |       |        |        |        |        |      | •       |        | •            | •         | •      | •      | •      | •      | •      | •             | •       |        | •      |
| Panelling                         |                   |       | •      | •      | •      | •      | •    | •       | •      |              | •         |        |        |        |        |        |               |         |        |        |
| Pet cages, runs and enclosures    |                   |       | •      | •      |        |        | •    | •       | •      | •            |           |        |        |        |        |        |               |         |        |        |
| Pine furniture manufacture        |                   | •     | •      | •      |        | •      | •    | •       | •      |              | •         |        |        |        |        |        |               |         |        |        |
| Presentation boxes                | •                 | •     | •      | •      |        |        |      |         | •      |              |           |        |        |        |        |        |               |         |        |        |
| Saunas                            |                   |       | •      | •      |        | •      |      | •       | •      |              | •         |        |        |        |        |        |               |         |        |        |
| Sheds and garden building         |                   |       | •      | •      |        | •      |      | •       | •      | •            | •         | •      | •      | •      | •      | •      | •             |         |        | •      |
| Shoe repair                       |                   |       | •      | •      |        |        |      |         |        |              |           |        |        |        |        |        |               |         |        |        |
| Skirting boards/dado to masonry   |                   |       |        |        | •      | •      |      |         |        |              | •         |        |        |        |        |        |               |         |        |        |
| Soft and medium wood floors       | •                 |       |        | •      |        | •      | •    | •       | •      |              | •         |        |        |        |        |        | •             |         |        |        |
| Staircases and banisters          |                   |       | •      | •      |        | •      | •    | •       | •      |              | •         |        |        |        |        |        |               |         |        |        |
| Subflooring/boarding out          |                   |       |        | •      | •      |        | •    |         |        | •            |           |        |        | •      | •      |        |               |         |        |        |
| Suspended ceilings                |                   |       |        |        |        | •      |      |         |        |              | •         |        |        |        |        |        |               |         |        |        |
| Theatre and film scenery          |                   |       | •      | •      | •      |        | •    | •       | •      |              |           |        |        |        | •      |        |               |         |        |        |
| Timber framing                    |                   |       |        |        |        |        |      |         |        |              |           |        |        | •      | •      | •      | •             | •       | •      | •      |
| Tongue and groove flooring        |                   |       |        | •      | •      |        |      | •       | •      |              |           |        |        |        |        |        |               |         |        |        |
| Toy manufacture                   | •                 | •     | •      | •      |        |        | •    |         |        |              |           |        |        |        |        |        |               |         |        |        |
| Trellis work                      |                   |       |        |        |        |        |      |         |        | •            |           |        |        | •      |        |        |               |         |        |        |
| Window frames and beading         | •                 | •     | •      | •      |        |        |      | •       | •      |              |           |        |        |        |        |        |               |         |        |        |

# Packing Tape Dispensers

For easy sealing of boxes and cartons

The Rapesco Packing Tape Dispenser makes light work of all heavy duty and packaging type jobs. Available with a choice of tapes and a handy cutter, this tough dispenser has steel construction and an easy-to-use impact resistant contoured handle with an ergonomic pistol grip. Compatible with tape rolls up to 50mm x 66m.



**RAPESCO®**  
**Packing Tape Dispenser** **NEW**

Production Line Code: TD9600A1



Up to 50mm / 66m Length



Germ-Savvy®




Retail Box



Trade = 1 Unit  
Transit = 24 Units

Tape dispenser for 50mm wide packing and parcel tape. Steel construction with impact resistant ergonomic handle and built-in Germ-Savvy® antibacterial protection – ISO 22196:2011. Adjustable tension control. Serrated cutting blade with safety cover when not in use.





**NEW**

**RAPESCO®**  
**Packing Tape Dispenser with Tapes & Cutter**



| Production Line |  |  |  |                                      |
|-----------------|--|--|--|--------------------------------------|
| Code: 1683      |  | Includes: Dispenser + 1 Brown Tape               |  | Trade = 1 Unit<br>Transit = 24 Units |
| Code: 1556      |  | Includes: Dispenser + 2 Brown Tapes + Cutter     |  | Trade = 1 Unit<br>Transit = 20 Units |
| Code: 1557      |  | Includes: Dispenser + 2 Clear Tapes + Cutter     |  | Trade = 1 Unit<br>Transit = 20 Units |
| Code: 1618      |  | Includes: Dispenser + 2 'Fragile' Tapes + Cutter |  | Trade = 1 Unit<br>Transit = 20 Units |
| Code: 1581      |  | Includes: Dispenser + 5 Brown Tapes + Cutter     |  | Trade = 1 Unit<br>Transit = 12 Units |
| Code: 1682      |  | Includes: Dispenser + 5 'Fragile' Tapes + Cutter |  | Trade = 1 Unit<br>Transit = 12 Units |

- Up to 50mm / 66m Length
- Germ-Savvy®
- Plain Box

Tape dispenser for 50mm wide packing and parcel tape. Steel construction with impact resistant ergonomic handle and built-in Germ-Savvy® antibacterial protection – ISO 22196:2011. Adjustable tension control. Serrated cutting blade with safety cover when not in use.

**Knife:** 9mm snap-off retractable cutter with metal inner channel Suitable for use with replacement blades (RCK003A1).



# Packing Tapes & Knives


For sealing and opening boxes

Our range of packing tapes are suitable for a variety of uses and are all compatible with our packing dispenser. Brown tape for all-purpose use, clear tape for sealing packages without covering anything important from view and 'fragile' tapes with eye-catching red lettering, indicating that the package contents are delicate and should be handled with care. We also offer 9mm & 18mm snap-off knives, ideal for opening packages.



## RAPESCO® 50mm Strong Packing Tape

**NEW**

| Production Line |   |
|-----------------|---|
| Code: 1696      |   |
| Code: 1697      |  |



50mm Width / 50m Length



Plain Box



Trade = 1 Unit  
Transit = 24 Units

Perfect for all your needs from shipping, moving or storing. Pack of 2 packaging tapes available in brown or clear. Strong 50-micron adhesive tape. Compatible with all Rapesco 960 Packaging Tape Dispensers (TD9600A1, 1556, 1557, 1581, 1618, 1682, 1683).

## RAPESCO® Packing Tape Variety Pack

**NEW**

| Production Line | Code: 1687 |
|-----------------|------------|
|-----------------|------------|



50mm Width / 50m Length



Plain Box



Trade = 1 Unit  
Transit = 12 Units

Perfect for all your needs from shipping, moving or storing. Pack of 6 packaging tapes: 2 x Brown rolls, 2 x Clear rolls, 2 x 'FRAGILE' rolls. Strong 50-micron adhesive tape. Compatible with all Rapesco 960 Packaging Tape Dispensers (TD9600A1, 1556, 1557, 1581, 1618, 1682, 1683).








**RAPESCO<sup>®</sup>**  
**Snap-Off Knives**

**NEW**



| Production Line       |   |
|-----------------------|---|
| Code: RCK001A1 – 9mm  |  |
| Code: RCK002A1 – 18mm |  |



  
Hanging  
Retail Card

  
Trade = 10 Units  
Transit = 200 Units

Retractable knife with stainless steel channel and high impact polymer parts. Smooth slider push button with audible 'click'. Blade segments snap-off using the integrated end-cap tool providing a new, sharp cutting point. Supplied with 1 preloaded blade.

**RAPESCO<sup>®</sup>**  
**Snap-Off Replacement Blades**

**NEW**

| Production Line       |   |
|-----------------------|---|
| Code: RCK003A1 – 9mm  |  |
| Code: RCK004A1 – 18mm |  |

  
Trade = 20 Units  
Transit = 200 Units

Stainless steel spare snap-off blades.  
Pack = 10 blades in sturdy plastic storage tube.



Underlay & Carpeting



Cabinetry & Assembling

# Browse By Project

Find the right tool with ease

Search on Tacwise.com and whether you're an enthusiastic DIYer or a professional tradesperson, our 'browse by project' categories make finding the right tool for the job quick and easy.

From carpet underlay and upholstery to woodwork assembly, roofing, framing and DIY, Tacwise probably has the perfect tool for every application.



Shed & Garden Building





DIY/Hobby



Upholstery



Packaging



Flooring & Decking










Construction & Manufacturing






Roofing, Sheeting & Insulation

## Key

|   |   |   |   |   |   |   |
|---|---|---|---|---|---|---|
|  |  |  |  |  |  |  |
| PSI value   | Weight of tool  | Staple type   | Pin/nail type   | Strip/coil type   | Packaging type  | Number of units   |

|  |  |  |  |
|--|--|--|--|
| <b>DIY/Semi-Pro</b>                                    | <b>Semi Professional</b>                               | <b>Professional</b>                                      | <b>Production Line</b>                                     |
| A quality, affordable tool designed for occasional use | A quality tool but not for continuous, repetitive work | Versatile and durable tool for frequent stapling/nailing | Offers speed and reliability for tough and repetitive work |

 Safety Trigger    
  Contact Trip (Bump Fire)    
  Sequential    
  Single /Shot    
  Single Shot/Contact Trip    
  Contact Trip/Sequential

## Inch/mm Conversion Chart

|        |      |      |     |      |     |     |      |     |       |       |     |       |     |    |       |       |       |       |       |        |       |    |        |       |       |        |       |    |       |       |     |       |
|--------|------|------|-----|------|-----|-----|------|-----|-------|-------|-----|-------|-----|----|-------|-------|-------|-------|-------|--------|-------|----|--------|-------|-------|--------|-------|----|-------|-------|-----|-------|
| mm     | 4    | 5    | 6   | 8    | 10  | 12  | 14   | 16  | 17    | 18    | 19  | 20    | 22  | 25 | 28    | 30    | 32    | 35    | 38    | 40     | 45    | 50 | 55     | 60    | 64    | 65     | 70    | 75 | 83    | 90    | 100 | 130   |
| Inches | 5/32 | 3/16 | 1/4 | 5/16 | 3/8 | 1/2 | 9/16 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | 7/8 | 1  | 1 1/8 | 1 1/4 | 1 1/8 | 1 1/2 | 1 1/2 | 1 9/16 | 1 3/4 | 2  | 2 3/16 | 2 3/8 | 2 1/2 | 2 9/16 | 2 3/4 | 3  | 3 1/4 | 3 3/8 | 4   | 5 1/8 |





DESIGN



QUALITY



REPAIR, REUSE, RECYCLE



TRUST

**Tacwise Group Plc**

**tacwise.com**

**sales@tacwise.com**

Copyright © Tacwise Group Plc.  
All rights reserved. Errors and Omissions Excepted.

Every attempt has been made to give accurate information, but it is our policy to continually improve our products therefore we reserve the right to withdraw or amend the product specification in any way. Under such circumstances wherever possible an alternative or substitute product may be offered.

