

## RefLED Retro Superia ES50 DIMMABLE

RefLED Sup RT ES50 V2 345 DIM 830 36d SL

0028550



### Product features

- Premium performance professional LED GU10 range with the same look and feel of traditional halogen GU10 lamp
- Recreates backlight effect similar to halogen dichroic lamps
- Full glass design - means no colours clashing between lamp and fixture
- Very long lifetime of up to 25,000 hours
- COOLFIT functionality - ensures overheat and over temperature protection
- High switching cycles: >100,000
- High colour rendering: CRI80
- Dimmable on approved dimmers
- Warranty: 5 Years



### PRODUCT OVERVIEW

Product name	RefLED Sup RT ES50 V2 345 DIM 830 36d SL
Technology	LED
Watt (Rated) (W)	4.5
Cap/Base	GU10
Fixture rating	Open
General application	Education, Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC001959
E-number FI	4740849
Warranty	5 years
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Consistency (SDCM)	6
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	36
Wattage (W)	4.5
Product Voltage (V)	230
Average life (Nominal) (h)	25000
Product EAN number	5410288285504

### DATA TABLE

#### General data

Product name	RefLED Sup RT ES50 V2 345 DIM 830 36d SL
Technology	LED
Watt (Rated) (W)	4.5
Cap/Base	GU10
Fixture rating	Open
General application	Education, Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
Performance ambient temperature Tq (°C)	25

## RefLED Retro Superia ES50 DIMMABLE

RefLED Sup RT ES50 V2 345 DIM 830 36d SL

0028550

ETIM Class	EC001959
E-number FI	4740849
Warranty	5 years

### Optical data

Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Consistency (SDCM)	6
Colour Variation Initial (SDCM)	SDCM6
Luminous Intensity (cd)	700
Beam Angle (°)	36
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	4.5
Equivalent watt (W)	50
Starting time (max) (s)	<0.5
Warm-up time to 60% of full light (max) (s)	<1
Product Voltage (V)	230
Lamp power factor	0.7
No. Of switching cycles before premature failures	>100000
Inrush Current (A)	0.55
Nominal Frequency (Hz)	50Hz
Max. Luminaires per 10A C Breaker	73
Max. Luminaires per 16A C Breaker	115
Max. Luminaires per 20A C Breaker	145

### Lifetime data

Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000

### Physical data

Nominal Product Length (mm)	54
Nominal Product Diameter (mm)	50
Weight (kg)	0.055

### Packaging

Single packaging type	Carton
Product EAN number	5410288285504
Packaging single length / height (cm)	6.7
Packaging single width (cm)	5.1
Packaging single depth (cm)	5.1
DUN14 (inner)	25410288285508
Units per inner package	6
Packaging inner length / height (cm)	7.5
Packaging inner width (cm)	16.5

## RefLED Retro Superia ES50 DIMMABLE

RefLED Sup RT ES50 V2 345 DIM 830 36d SL  
0028550

Packaging inner depth (cm)	11.0
DUN14 (outer)	15410288285501
Units per outer package	60
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	58.0
Packaging outer depth (cm)	17.8

### Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Dimmable with approved dimmers

### PHOTOMETRY

