

Rigid ladder with steps



Execution:

- step-strut connections made of high-strength ZARGES quality flanging
- Steps and rails made of extruded aluminium profiles
- Replaceable 2-component plastic end caps which fit securely on the rail and ensure that the ladder does not slip
- rungs feature ZARGES Safer Step Technology, 80 mm deep
- wear-resistant anodised rails
- external width: 420 mm



Art. no.	50260 622
Brand	ZARGES
Manufacturer Part Number	41360
Working height	3.85 m
Number of steps	1 x 10
Length	3.06 m
Step distance	265 mm
Weight	8.8 kg
Length stabiliser bar	0.8 m
Step depth	80 mm
Rail height	68 mm
Material	Aluminium
Max. load capacity	150 kg
With Safer Step technology	Yes
Accessibility	One-sided
Anodised	Yes
Width	420 mm
ESD-capable	No
Transport width	420 mm
Transport height	73 mm
Transport length	3050 mm
Gross Weight	8.800 kg
Product Group	5AK

EAN

4003866413607