

pneumatic spiral hose

With eSafe safety coupling



Application:

for connection to compressed-air tools and compressed-air machines.

Execution:

- With eSafe safety coupling and nipple
- ends and rotary joint axially offset on both sides
- max. pressure: 10 bar

Advantage:

- Coupling and nipple (DN 7.6) pre-installed for immediate use
- Lightweight and flexible
- Long life with excellent ageing properties
- The ventilation function of the eSafe safety coupling reduces the noise level and prevents accidents caused by the whiplash effect



Art. no.	75055 051
Brand	CEJN
Manufacturer Part Number	19 958 9707
Hose length	6 m
Outer diameter of hose	12 mm
Inner hose diameter	8 mm
Max. operating pressure	10 bar
Gross Weight	0.778 kg
Product Group	7AI

EAN

7391390134356