

For pneumatic hand belt sander HB 12 S

300 watt



Application:

For finer and flat grinding applications.

Version:

- Air discharge to the rear
- For holding interchangeable sanding arms.

Delivery:

Without hose unit, without grinding arm



Art. no.	75068 021
Model	HB 12 S
Max. idle speed	20000 rpm
Power input	300 W
Air consumption	500 l/min
Diameter of housing	38 mm
Connection thread	G 1/8 inch
Length	330 mm
Inner hose diameter	7 mm
Min. sanding belt width	6 mm
Max. sanding belt width	12 mm
Weight	1.47 kg