



MSR Gold™ MiniFastFit (DJ/Club)

MSR Gold™ 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Product data

General Information		Operating and Electrical	
Cap-Base	PGJX28 [PGJX28]	Power (Rated) (Nom)	300 W
Operating Position	UNIVERSAL [Any or Universal (U)]	Lamp Current (Nom)	3.75 A
Main Application	Entertainment	Ignition Supply Voltage (Min)	207 V
Life to 50% Failures (Nom)	750 h	Controls and Dimming	
System Description	MiniFastFit	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	2	Cap-Base Information	PGJX28
Luminous Flux (Min)	19170 lm	Luminaire Design Requirements	
Luminous Flux (Nom)	21300 lm	Bulb Temperature (Max)	950 °C
Chromaticity Coordinate X (Nom)	288	Pinch Temperature (Max)	500 °C
Chromaticity Coordinate Y (Nom)	306	Product Data	
Correlated Color Temperature (Nom)	9300 K	Full product code	87182912211100
Luminous Efficacy (Rated) (Min)	64 lm/W	Order product name	MSR Gold™ 300/2 MiniFastFit 1CT/4
Luminous Efficacy (rated) (Nom)	71 lm/W		
Color Rendering Index (Nom)	80		

MSR Gold™ MiniFastFit (DJ/Club)


EAN/UPC - Product	8718291221111
Order code	928177105115
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Material Nr. (12NC)	928177105115
Net Weight (Piece)	0.062 kg

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm
MiniFastFit 1CT/4						

MSR GOLD 300/2 MiniFastFit

