

## Schraubendreher SoftFinish®



### ⊖ Schlitz mit kurzer Rundklinge, Stubby

302SY

Best.-Nr.	⊖	↔	⊖	●	mm	↔	🏠
26964	4,0	25	0,8	4,0	81	34	10
26965	5,5	25	1,0	5,5	81	34	10
26966	6,5	25	1,2	6,5	81	34	10
26967	8,0	25	1,2	8,0	81	34	10

### ⊕ Phillips mit kurzer Rundklinge, Stubby

311SY

Best.-Nr.	⊕	↔	●	mm	↔	🏠
26968	PH1	25	4,5	81	34	10
26969	PH2	25	6,0	81	34	10
26970	PH3	25	8,0	81	34	10

### ⊗ Pozidriv mit kurzer Rundklinge, Stubby

313SY

Best.-Nr.	⊗	↔	●	mm	↔	🏠
26971	PZ1	25	4,5	81	34	10
26972	PZ2	25	6,0	81	34	10
26973	PZ3	25	8,0	81	34	10

## Schraubendreher SoftFinish®



### ⊖ Schlitz mit Sechskantklinge und Sechskantansatz

308

Best.-Nr.	⊖	↔	⊖	●	⬡	mm	↔	🏠
00731	3,5	75	0,6	4,0	-	186	10	10
00732	4,5•	90	0,8	4,0	-	201	10	10
00733	5,5	100	1,0	5,0	8	213	10	10
00734	6,5	125	1,2	6,0	10	238	10	10
00735	7,0•	125	1,1	6,0	10	238	10	10
00736	8,0	150	1,2	8,0	13	268	10	10
00737	9,0•	150	1,4	8,0	13	268	10	10
00738	10,0	175	1,6	8,0	13	293	10	10
00739	12,0	200	2,0	10,0	16	318	10	10
00740	14,0•	250	2,5	10,0	16	368	10	10

• Ergänzungsgröße zu DIN-Abmessungen

### ⊕ Phillips mit Sechskantklinge und Sechskantansatz

312

Best.-Nr.	⊕	↔	●	⬡	mm	↔	🏠
00764	PH1	80	5,0	8	186	30	10
00765	PH2	100	6,0	10	213	36	10
00766	PH3	150	8,0	13	268	41	10
00767	PH4	200	10,0	16	318	41	10

### ⊗ Pozidriv mit Sechskantklinge und Sechskantansatz

314

Best.-Nr.	⊗	↔	●	⬡	mm	↔	🏠
00776	PZ1	80	5,0	8	186	30	10
00777	PZ2	100	6,0	10	213	36	10
00778	PZ3	150	8,0	13	268	41	10
00779	PZ4	200	10,0	16	318	41	10

## Aufreiber



### ■ mit Vierkantspitze und Kunststoffgriff

300

Best.-Nr.	■	↔	mm	↔	🏠
00679	6,0	100	185	34	10

## Vorstecher Kunststoffgriff



### ● mit Rundspitze und Kunststoffgriff

301

Best.-Nr.	●	↔	mm	↔	🏠
00683	6,0	100	185	34	10