

## SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE


0...230V PG9

Form A (18 mm) for pressure switch  
24...230 V AC/DC  
without components  
PG 9



Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration



stay connected



Height: 41 mm

Product may differ from Image

### Approvals



### Form

29421

### Technical Data

Operating voltage	0...230 V AC/DC
Operating current per contact	max. 10 A
Sealing range (cable diameter)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	PG 9; (PG11, NPT 1/2" on request)
Protection	IP65 inserted and tightened (EN 60529), with gland

### General data

Temperature range	-20...+60 °C
-------------------	--------------

### Commercial data

country of origin	CZ
customs tariff number	85366990
minimum order quantity	1