


M12 MALE ON REAR OF MSUD VALVE PLUG FORM BI 11MM


Form BI (11 mm) – M12, connector at the rear
LED and suppression
3-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



stay connected

Product may differ from Image

Approvals



Form

42081

Technical Data

| | |
|-------------------------------|--|
| Operating voltage | 24 V AC $\pm 20\%$ / DC $\pm 25\%$ |
| Operating current per contact | max. 4 A |
| Configuration | 2 contacts + PE |
| Switch off peak | max. 55 V |
| Current consumption | max. 15 mA |
| Protection | IP67 inserted and tightened (EN 60529) |
| Locking of ports | M3/M12 \times 1 mm (recommended torque 0.4/0.6 Nm) |

General data

| | |
|-------------------|--------------|
| Temperature range | -25...+85 °C |
|-------------------|--------------|

Commercial data

| | |
|------------------------|----------|
| country of origin | CZ |
| customs tariff number | 85369010 |
| minimum order quantity | 1 |